

DeltaV™ Alliance Product Program

Beijer Product List - Date 08/28/20

Product Category	Partner Name	Product Part Number	Product Description
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 extreme 7	Touch operator panel, 7" iX Rugged HMI, 800x480, CPU Dual Core 800MHz, 2GB RAM, 2GB eMMC, 1xLAN, 1x9pin DSUB, USB, SD, 24VDC, -30 to +70C, IP66, CE/FCC, UL, Hazardous, Marine
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 extreme 7 – HP	Touch operator panel, 7" iXRugged HMI, 800x480 HighBright, CPU Quad Core 1GHz, 2GB RAM, 4GB eMMC, 2xLAN, 2x9pin DSUB, USB, SD, 24VDC, -30 to +70C, IP66, CE/FCC, UL, Hazardous, Marine
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 extreme 12	Touch operator panel, 12,1" iX Rugged HMI, 1280x800, CPU Dual Core 800MHz, 2GB RAM, 2GB eMMC, 1xLAN, 1x9pin DSUB, USB, SD, 24VDC, -30 to +70C, IP66, CE/FCC, UL, Hazardous, Marine
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 extreme 12 – HP	Touch operator panel, 12,1", 1280x800 High Bright, CPU Quad Core 1GHz, 2GB RAM, 4GB eMMC, 2xLAN, 2x9pin DSUB, USB, SD, 24VDC, -30 to +70C, IP66, CE/FCC, UL, Hazardous, Marine
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 extreme 15	Touch operator panel, 15,4" iX Rugged HMI, 1280x800, CPU Dual Core 800MHz, 2GB RAM, 2GB eMMC, 1xLAN, 1x9pin DSUB, USB, SD, 24VDC, -30 to +70C, IP66, CE/FCC, UL, Hazardous, Marine
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 extreme 15 – HP	Touch operator panel, 15,4", 1280x800 High Bright, CPU Quad Core 1GHz, 2GB RAM, 4GB eMMC, 2xLAN, 2x9pin DSUB, USB, SD, 24VDC, -30 to +70C, IP66, CE/FCC, UL, Hazardous, Marine
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 pro 7 - B2	Touch operator panel, 7" iX HMI, 800x480, CPU Single Core 1GHz, 512MB RAM, 2GB eMMC, 1xLAN, 1x9pin DSUB, USB, SD, 24VDC, -10 to +60C, IP65, CE/FCC, Marine, UL
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 pro 10 - B2	Touch operator panel, 10.1" iX HMI, 1024x600, CPU Dual Core 1GHz, 1GB RAM, 2GB eMMC, 2xLAN, 1x9pin DSUB, USB, SD, 24VDC, -10 to +60C, IP65, CE/FCC, Marine, UL
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 pro 12 - B2	Touch operator panel, 12,1" iX HMI, 1280x800, CPU Dual Core 1GHz, 1GB RAM, 2GB eMMC, 2xLAN, 1x9pin DSUB, USB, SD, 24VDC, -10 to +60C, IP65, CE/FCC, Marine, UL
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 pro 15 - B2	Touch operator panel, 15,4" iX HMI, 1280x800, CPU Dual Core 1GHz, 1GB RAM, 2GB eMMC, 2xLAN, 1x9pin DSUB, USB, SD, 24VDC, -10 to +60C, IP65, CE/FCC, Marine, UL

DeltaV™ Alliance Product Program

Beijer Product List - Date 08/28/20

HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 pro 21 - B2	Touch operator panel, 21,5" iX HMI, 1920x1080, CPU Quad Core 1GHz, 2GB RAM, 2GB eMMC, 2xLAN, 1x9pin DSUB, USB, SD, 24VDC, 0 to +50C, IP65, CE/FCC, UL
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 base 5 - F2	Touch operator panel, 5" iX HMI, 800x480, CPU ARM9 400MHz, 128MB RAM, 256 MB Flash, 1xLAN, 1xUSB, 2x9pin DSUB, -10 to +50C, IP65, CE/FCC, UL
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 base 7 - F2	Touch operator panel, 7" iX HMI, 800x480, CPU ARM9 400MHz, 128MB RAM, 256 MB Flash, 1xLAN, 1xUSB, 2x9pin DSUB, -10 to +50C, IP65, CE/FCC, UL
HMI, Thin Client, Industrial Monitors & PC	Beijer Electronics	X2 base 10 - F2	Touch operator panel, 10" iX HMI, 800x480, CPU ARM9 400MHz, 128MB RAM, 256 MB Flash, 1xLAN, 1xUSB, 2x9pin DSUB, -10 to +50C, IP65, CE/FCC, UL