

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Product Category	Partner Name	Product Part Number	Product Description
Safety Barriers	Weidmuller	SCS 24VDC P1SIL3DS M	SIL 3 - Safety Relays - Safe switch-off with monitoring
Safety Barriers	Weidmuller	SCS 24VDC P1SIL3DS	SIL 3 - Safety Relays - Safe switch-off without monitoring
Safety Barriers	Weidmuller	SCS 24VDC P2SIL3DSES	SIL 3 - Safety Relays - Emergency Shut-off for fuel supply to a furnace within a boiler plant
Safety Barriers	Weidmuller	SCS 24VDC P1SIL3DS I	SIL 3 - Safety Relays - Suitable for use with Emerson DeltaV DCS systems
Connector	Weidmuller	AP WMF2.5	End plate (terminals), 87.25 mm x 1.5 mm, Beige
Connector	Weidmuller	BFSC M5X8 Schlitz	Mounting screw (Terminal)
Connector	Weidmuller	LS 2.8 WDU2.5-10	Shield bus
Connector	Weidmuller	Q WDU10-2.5 SET	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 7.00, Insulated: No, Silver grey
Connector	Weidmuller	WAD 20 GE WSD	Terminal marking, Pitch, in mm: 18.00, Printed characters: Symbols, Yellow
Connector	Weidmuller	WAD 4 GE BED	Terminal cover, PA 66, Yellow, Height: 19.8 mm, Width: 4.5 mm, Depth: 9.6 mm
Connector	Weidmuller	WAH 120	Terminal cover, Polyamide 66, Beige, Height: 110.25 mm, Width: 41 mm, Depth: 34.5 mm
Connector	Weidmuller	WAH 185/300 BE	Terminal cover, Polyamide 66, Beige, Height: 139 mm, Width: 54 mm, Depth: 43.9 mm
Connector	Weidmuller	WAH 35	Terminal cover, Polyamide 66, Beige, Height: 63.5 mm, Width: 26 mm, Depth: 22.6 mm
Connector	Weidmuller	WAH 70 BE	Terminal cover, Polyamide 66, Beige, Height: 85 mm, Width: 31 mm, Depth: 29.9 mm
Connector	Weidmuller	WAP 16+35 WTW 2.5-10	End and partition plate for terminals, End plate, 56 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP 16+35 WTW 2.5-10 BL	End and partition plate for terminals, End plate, 56 mm x 1.5 mm, Blue
Connector	Weidmuller	WAP 2.5-10	End plate (terminals), 56 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP 2.5-10 BL	End plate (terminals), 56 mm x 1.5 mm, Blue
Connector	Weidmuller	WAP 2.5-10 GR	End plate (terminals), 56 mm x 1.5 mm, Grey
Connector	Weidmuller	WAP 2.5-10 SW	End plate (terminals), 56 mm x 1.5 mm, Black
Connector	Weidmuller	WAP WDK 2.5N/TR-DU	End plate (terminals), 80.35 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP WDK2.5	End plate (terminals), 69 mm x 1.5 mm, Dark Beige

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WAP WDK2.5 BL	End plate (terminals), 69 mm x 1.5 mm, Blue
Connector	Weidmuller	WAP WDK2.5/4 N	End plate (terminals), 60 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP WDK2.5/4 N BL	End plate (terminals), 60 mm x 1.5 mm, Blue
Connector	Weidmuller	WAP WDU2.5N/4N	End plate (terminals), 44 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP WDU2.5N/4N BL	End plate (terminals), 44 mm x 1.5 mm, Blue
Connector	Weidmuller	WAP WTL6/1	End plate (terminals), 65 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP WTL6/4FF	End plate (terminals), 1.5 mm, Dark Beige
Connector	Weidmuller	WAP WTR2.5/ZZ	End plate (terminals), 60.3 mm x 1.5 mm, Dark Beige
Connector	Weidmuller	WAP WTR2.5/ZZ BL	End plate (terminals), 60.3 mm x 1.5 mm, Blue
Connector	Weidmuller	WDK 2.5	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 24 A, Number of levels: 2, Dark Beige
Connector	Weidmuller	WDK 2.5 2D 1.A	Component terminal block, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 10 A, Diode 1N 4007, Diode 1N 4007, TS 35, Dark Beige
Connector	Weidmuller	WDK 2.5 BL	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 24 A, Number of levels: 2, Blue
Connector	Weidmuller	WDK 2.5 OR	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 24 A, Number of levels: 2, Orange
Connector	Weidmuller	WDK 2.5 ZQV	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 24 A, Number of levels: 2, Dark Beige
Connector	Weidmuller	WDK 2.5/D	Component terminal block, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 10 A, TS 35, Dark Beige
Connector	Weidmuller	WDK 2.5/D/3	W-Series, Component terminal, Rated cross-section: 2.5 mm <sup>2</sup> , Screw connection
Connector	Weidmuller	WDK 2.5/TR-DU	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> , 690 V, 24 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WDK 2.5N	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of levels: 2, Dark Beige
Connector	Weidmuller	WDK 2.5N PE	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , Number of levels: 2, green / yellow
Connector	Weidmuller	WDK 2.5N V	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of levels: 2, Dark Beige
Connector	Weidmuller	WDK 2.5N V BL	#N/A

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WDK 2.5N V SW	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of levels: 2, Black
Connector	Weidmuller	WDK 2.5PE	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , Number of levels: 2, green / yellow
Connector	Weidmuller	WDK 2.5V	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 24 A, Number of levels: 2, Dark Beige
Connector	Weidmuller	WDK 2.5V BL	Multi-tier modular terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 24 A, Number of levels: 2, Blue
Connector	Weidmuller	WDK 4N	Multi-tier modular terminal, Screw connection, 4 mm <sup>2</sup> , 800 V, 32 A, Number of levels: 2, Dark Beige
Connector	Weidmuller	WDK 4N PE	Multi-tier modular terminal, Screw connection, 4 mm <sup>2</sup> , Number of levels: 2, green / yellow
Connector	Weidmuller	WDS 2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 5.00, Insulated: Yes, 22 A, Dark Beige
Connector	Weidmuller	WDTR 2.5 BL	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> , 400 V, 10 A, Pivoting, Cross-disconnect: without, Integral test socket: Yes, TS 35, Blue
Connector	Weidmuller	WDU 10	Feed-through terminal block, Screw connection, 10 mm <sup>2</sup> , 1000 V, 57 A, Number of connections: 2
Connector	Weidmuller	WDU 10 BL	Feed-through terminal block, Screw connection, 10 mm <sup>2</sup> , 1000 V, 57 A, Number of connections: 2
Connector	Weidmuller	WDU 10 SL	Feed-through terminal block, Screw connection, 10 mm <sup>2</sup> , 630 V, 57 A, Number of connections: 2
Connector	Weidmuller	WDU 120/150	Feed-through terminal block, Screw connection, 120 mm <sup>2</sup> , 1000 V, 269 A, Number of connections: 2
Connector	Weidmuller	WDU 16	Feed-through terminal block, Screw connection, 16 mm <sup>2</sup> , 1000 V, 76 A, Number of connections: 2
Connector	Weidmuller	WDU 16 BL	Feed-through terminal block, Screw connection, 16 mm <sup>2</sup> , 1000 V, 76 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5 BL	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WDU 2.5 GN	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5 GR	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5 OR	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5 SW	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5/TC TYP J	Thermocouple terminal, Screw connection, 2.5, Dark Beige
Connector	Weidmuller	WDU 2.5/TC TYP K	Thermocouple terminal, Screw connection, 2.5, Dark Beige
Connector	Weidmuller	WDU 2.5N	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 500 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 2.5N BL	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 500 V, 24 A, Number of connections: 2
Connector	Weidmuller	WDU 240	Feed-through terminal block, Screw connection, 240 mm <sup>2</sup> , 1000 V, 415 A, Number of connections: 2
Connector	Weidmuller	WDU 35	Feed-through terminal block, Screw connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Number of connections: 2
Connector	Weidmuller	WDU 35 BL	Feed-through terminal block, Screw connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Number of connections: 2
Connector	Weidmuller	WDU 35N	Feed-through terminal block, Screw connection, 35 mm <sup>2</sup> , 500 V, 125 A, Number of connections: 2
Connector	Weidmuller	WDU 35/ZA	Feed-through terminal, Screw connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Dark Beige
Connector	Weidmuller	WDU 35/ZA BL	Feed-through terminal, Screw connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Blue
Connector	Weidmuller	WDU 70/95 BL	Feed-through terminal, Screw connection, 95 mm <sup>2</sup> , 1000 V, 232 A, Blue
Connector	Weidmuller	WDU 4	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 800 V, 32 A, Number of connections: 2
Connector	Weidmuller	WDU 4 BL	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 800 V, 32 A, Number of connections: 2
Connector	Weidmuller	WDU 4 GE/SW	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 800 V, 32 A, Number of connections: 2
Connector	Weidmuller	WDU 4 SL	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 630 V, 32 A, Number of connections: 2

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WDU 4 SL BL	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 630 V, 32 A, Number of connections: 2
Connector	Weidmuller	WDU 4N	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 500 V, 32 A, Number of connections: 2
Connector	Weidmuller	WDU 4N BL	Feed-through terminal block, Screw connection, 4 mm <sup>2</sup> , 500 V, 32 A, Number of connections: 2
Connector	Weidmuller	WDU 50N	Feed-through terminal block, Screw connection, 50 mm <sup>2</sup> , 1000 V, 150 A, Number of connections: 2
Connector	Weidmuller	WDU 6	Feed-through terminal block, Screw connection, 6 mm <sup>2</sup> , 800 V, 41 A, Number of connections: 2
Connector	Weidmuller	WDU 6 BL	Feed-through terminal block, Screw connection, 6 mm <sup>2</sup> , 800 V, 41 A, Number of connections: 2
Connector	Weidmuller	WDU 6 SL	Feed-through terminal block, Screw connection, 6 mm <sup>2</sup> , 630 V, 41 A, Number of connections: 2
Connector	Weidmuller	WDU 70/95	Feed-through terminal block, Screw connection, 95 mm <sup>2</sup> , 1000 V, 232 A, Number of connections: 2
Connector	Weidmuller	WDU 70N/35	Feed-through terminal block, Screw connection, 70 mm <sup>2</sup> , 1000 V, 192 A, Number of connections: 2
Connector	Weidmuller	WDU 95N/120N	Feed-through terminal block, Screw connection, 120 mm <sup>2</sup> , 1000 V, 269 A, Number of connections: 2
Connector	Weidmuller	WDUL 4/1K	Component terminal block, Screw connection, 4 mm <sup>2</sup> , 120 mA, Resistor 1 kΩ, TS 35, Dark Beige
Connector	Weidmuller	WF 6	Stud terminal, Threaded stud connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Number of connections: 1, M 6, TS 35, Dark Beige
Connector	Weidmuller	WFF 120	Stud terminal, Threaded stud connection, 120 mm <sup>2</sup> , 1000 V, 269 A, Number of connections: 2, M 10, TS 35, Dark Beige
Connector	Weidmuller	WFF 120/AH	Stud terminal, Threaded stud connection, 120 mm <sup>2</sup> , 1000 V, 269 A, Number of connections: 2, M 10, TS 35, Dark Beige
Connector	Weidmuller	WFF 185	Stud terminal, Threaded stud connection, 185 mm <sup>2</sup> , 1000 V, 353 A, Number of connections: 2, M 12, TS 35, Dark Beige
Connector	Weidmuller	WFF 185/AH	Stud terminal, Threaded stud connection, 185 mm <sup>2</sup> , 1000 V, 353 A, Number of connections: 2, M 12, TS 35, Dark Beige
Connector	Weidmuller	WFF 300	Stud terminal, Threaded stud connection, 300 mm <sup>2</sup> , 520 A, Number of connections: 2, M16, TS 35, Dark Beige

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WFF 300/AH	Stud terminal, Threaded stud connection, 300 mm <sup>2</sup> , 1000 V, 520 A, Number of connections: 2, M16, TS 35, Dark Beige
Connector	Weidmuller	WFF 35	Stud terminal, Threaded stud connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Number of connections: 2, M 6, TS 35, Dark Beige
Connector	Weidmuller	WFF 35/AH	Stud terminal, Threaded stud connection, 35 mm <sup>2</sup> , 1000 V, 125 A, Number of connections: 2, M 6, TS 35, Dark Beige
Connector	Weidmuller	WFF 70	Stud terminal, Threaded stud connection, 70 mm <sup>2</sup> , 1000 V, 192 A, Number of connections: 2, M 8, TS 35, Dark Beige
Connector	Weidmuller	WFF 70/AH	Stud terminal, Threaded stud connection, 70 mm <sup>2</sup> , 1000 V, 192 A, Number of connections: 2, M 8, TS 35, Dark Beige
Connector	Weidmuller	WMF 2.5	Feed-through terminal block, Screw connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, Number of connections: 2
Connector	Weidmuller	WMF 2.5 DI	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> , 500 V, 20 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WMF 2.5 DI PE	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> , 500 V, 20 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WMF 2.5 FU SW	Fuse terminal, Screw connection, Fuse isolator, for plug-in cross-connector, One end without connector, Screw connection, 2.5 mm <sup>2</sup> , 500 V, 6.3 A, G-Si. 5 x 20, Black
Connector	Weidmuller	WPD 109 1X185/2X35+3X25+4X16 GY	Potential distributor terminal, Screw connection, 353 A, No. of poles: 1, TS 35, Light Grey
Connector	Weidmuller	WPE 10	PE terminal, Screw connection, 10 mm <sup>2</sup> , 1000 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 120/150	PE terminal, Screw connection, 120 mm <sup>2</sup> , 1000 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 16	PE terminal, Screw connection, 16 mm <sup>2</sup> , 1000 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 2.5	PE terminal, Screw connection, 2.5 mm <sup>2</sup> , 800 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 2.5N	PE terminal, Screw connection, 2.5 mm <sup>2</sup> , 500 V, Number of connections: 2, Number of levels: 1, green / yellow



## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WPE 35	PE terminal, Screw connection, 35 mm <sup>2</sup> ; 800 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 4	PE terminal, Screw connection, 4 mm <sup>2</sup> ; 800 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 4N	PE terminal, Screw connection, 4 mm <sup>2</sup> ; 500 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 50N	PE terminal, Screw connection, 50 mm <sup>2</sup> ; 1000 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 6	PE terminal, Screw connection, 6 mm <sup>2</sup> ; 800 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 70N/35	PE terminal, Screw connection, 70 mm <sup>2</sup> ; 1000 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WPE 95N/120N	PE terminal, Screw connection, 95 mm <sup>2</sup> ; 1000 V, Number of connections: 2, Number of levels: 1, green / yellow
Connector	Weidmuller	WQB 240/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 5.10, Insulated: Yes, Silver grey
Connector	Weidmuller	WQB 240/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 5.10, Insulated: Yes, Silver grey
Connector	Weidmuller	WQB A/24	Cross-connector (terminal), Screwed, No. of poles: 24, Pitch, in mm: 5.10, Insulated: Yes, Black
Connector	Weidmuller	WQB B/24	Cross-connector (terminal), Screwed, No. of poles: 24, Pitch, in mm: 5.10, Insulated: Yes, Black
Connector	Weidmuller	WQB-PEN 10	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 10.00, Insulated: No, Silver grey
Connector	Weidmuller	WQL 2 WFF120	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 42.00, Insulated: No, 269 A, Grey
Connector	Weidmuller	WQL 2 WFF185	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 55.00, Insulated: No, 353 A, Grey
Connector	Weidmuller	WQL 2 WFF300	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 55.00, Insulated: No, 520 A, Grey
Connector	Weidmuller	WQL 2 WFF35	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 27.00, Insulated: No, 125 A, Grey
Connector	Weidmuller	WQL 2 WFF70	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 32.00, Insulated: No, 192 A, Grey

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WQL 3 WF6	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 22.00, Insulated: No, 125 A, Grey
Connector	Weidmuller	WQL 3 WFF120	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 42.00, Insulated: No, 269 A, Grey
Connector	Weidmuller	WQL 3 WFF35	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 27.00, Insulated: No, 125 A, Grey
Connector	Weidmuller	WQL 3 WFF70	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 32.00, Insulated: No, 192 A, Grey
Connector	Weidmuller	WQV 10/10	Cross-connector (terminal), Screwed, No. of poles: 10, Pitch, in mm: 9.90, Insulated: Yes, 63 A, Yellow
Connector	Weidmuller	WQV 10/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 9.90, Insulated: Yes, 76 A, Yellow
Connector	Weidmuller	WQV 10/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 9.90, Insulated: Yes, 63 A, Yellow
Connector	Weidmuller	WQV 10/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 9.90, Insulated: Yes, 63 A, Yellow
Connector	Weidmuller	WQV 10/5	Cross-connector (terminal), Screwed, No. of poles: 5, Pitch, in mm: 9.90, Insulated: Yes, 63 A, Yellow
Connector	Weidmuller	WQV 120/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 32.00, Insulated: No, 269 A, Silver grey
Connector	Weidmuller	WQV 120/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 32.00, Insulated: No, 292 A, Silver grey
Connector	Weidmuller	WQV 16/10	Cross-connector (terminal), Screwed, No. of poles: 10, Pitch, in mm: 11.90, Insulated: Yes, 101 A, Yellow
Connector	Weidmuller	WQV 16/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 11.90, Insulated: Yes, 101 A, Yellow
Connector	Weidmuller	WQV 16/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 11.90, Insulated: Yes, 101 A, Yellow
Connector	Weidmuller	WQV 16/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 11.90, Insulated: Yes, 101 A, Yellow
Connector	Weidmuller	WQV 16-2.5	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 11.90, Insulated: Yes, 76 A, Yellow
Connector	Weidmuller	WQV 2.5/10	Cross-connector (terminal), Screwed, No. of poles: 10, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow



## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WQV 2.5/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow
Connector	Weidmuller	WQV 2.5/20	Cross-connector (terminal), Screwed, No. of poles: 20, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow
Connector	Weidmuller	WQV 2.5/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow
Connector	Weidmuller	WQV 2.5/30	Cross-connector (terminal), Screwed, No. of poles: 30, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow
Connector	Weidmuller	WQV 2.5/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow
Connector	Weidmuller	WQV 2.5/5	Cross-connector (terminal), Screwed, No. of poles: 5, Pitch, in mm: 5.10, Insulated: Yes, 32 A, Yellow
Connector	Weidmuller	WQV 35/10	Cross-connector (terminal), Screwed, No. of poles: 10, Pitch, in mm: 16.00, Insulated: Yes, 112 A, Yellow
Connector	Weidmuller	WQV 35/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 16.00, Insulated: Yes, 138 A, Yellow
Connector	Weidmuller	WQV 35/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 16.00, Insulated: Yes, 112 A, Yellow
Connector	Weidmuller	WQV 35/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 16.00, Insulated: Yes, 112 A, Yellow
Connector	Weidmuller	WQV 4/10	Cross-connector (terminal), Screwed, No. of poles: 10, Pitch, in mm: 6.10, Insulated: Yes, 41 A, Yellow
Connector	Weidmuller	WQV 4/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 6.10, Insulated: Yes, 41 A, Yellow
Connector	Weidmuller	WQV 4/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 6.10, Insulated: Yes, 41 A, Yellow
Connector	Weidmuller	WQV 4/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 6.10, Insulated: Yes, 41 A, Yellow
Connector	Weidmuller	WQV 50N/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 18.50, Insulated: No, 150 A, Silver grey
Connector	Weidmuller	WQV 50N/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 18.50, Insulated: No, 150 A, Silver grey
Connector	Weidmuller	WQV 6/10	Cross-connector (terminal), Screwed, No. of poles: 10, Pitch, in mm: 8.00, Insulated: Yes, 57 A, Yellow

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WQV 6/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 8.00, Insulated: Yes, 57 A, Yellow
Connector	Weidmuller	WQV 6/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 8.00, Insulated: Yes, 57 A, Yellow
Connector	Weidmuller	WQV 6/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 8.00, Insulated: Yes, 57 A, Yellow
Connector	Weidmuller	WQV 6/6	Cross-connector (terminal), Screwed, No. of poles: 6, Pitch, in mm: 8.00, Insulated: Yes, 57 A, Yellow
Connector	Weidmuller	WQV 70N/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 20.50, Insulated: No, 192 A, Silver grey
Connector	Weidmuller	WQV 70N/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 20.50, Insulated: No, 192 A, Silver grey
Connector	Weidmuller	WQV 70N/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 20.50, Insulated: No, 192 A, Silver grey
Connector	Weidmuller	WQV 95N/120N/2	Cross-connector (terminal), Screwed, No. of poles: 2, Pitch, in mm: 27.00, Insulated: No, 269 A, Silver grey
Connector	Weidmuller	WQV 95N/120N/3	Cross-connector (terminal), Screwed, No. of poles: 3, Pitch, in mm: 27.00, Insulated: No, 269 A, Silver grey
Connector	Weidmuller	WQV 95N/120N/4	Cross-connector (terminal), Screwed, No. of poles: 4, Pitch, in mm: 27.00, Insulated: No, 269 A, Silver grey
Connector	Weidmuller	WSI 25/1 10x38	Fuse terminal, Screw connection, Fuse cartridge, closed, Screw connection, 25 mm <sup>2</sup> , 690 V, 32 A, max. 3W for gG/gL max. 1.2W for aM, Dark Beige
Connector	Weidmuller	WSI 25/1 10x38/LED 690V	Fuse terminal, Screw connection, Fuse cartridge, with LED, closed, Screw connection, 25 mm <sup>2</sup> , 690 V, 32 A, max. 3W for gG/gL max. 1.2W for aM, Dark Beige
Connector	Weidmuller	WSI 4	Fuse terminal, Screw connection, Fuse isolator, closed, Screw connection, 4 mm <sup>2</sup> , 250 V, 6.3 A, G-Si. 5 x 20, Black
Connector	Weidmuller	WSI 4/2/LD 10-36V AC/DC	Fuse terminal, Screw connection, Fuse isolator, with LED, One end without connector, Screw connection, 4 mm <sup>2</sup> , 36 V, 6.3 A, 6.3 x 32 mm (1/4 x 1 1/4"), Black
Connector	Weidmuller	WSI 6	Fuse terminal, Screw connection, Fuse isolator, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> , 250 V, 6.3 A, G-Si. 5 x 20, Dark Beige

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WSI 6/2/LD 10-36V DC/AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 36 V, 6.3 A, G-Si. 1 x 1/4, Dark Beige
Connector	Weidmuller	WSI 6/2/LD 250AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 250 V, 6.3 A, G-Si. 1 x 1/4, Dark Beige
Connector	Weidmuller	WSI 6/2/LD 60-150VDC/AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 150 V, 6.3 A, G-Si. 1 x 1/4, Dark Beige
Connector	Weidmuller	WSI 6/LD 10-36V DC/AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 36 V, 6.3 A, G-Si. 5 x 20, Dark Beige
Connector	Weidmuller	WSI 6/LD 10-36V LLC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 36 V, 6.3 A, G-Si. 5 x 20, Dark Beige
Connector	Weidmuller	WSI 6/LD 250AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 250 V, 6.3 A, G-Si. 5 x 20, Dark Beige
Connector	Weidmuller	WSI 6/LD 30-70V DC/AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 70 V, 6.3 A, G-Si. 5 x 20, Dark Beige
Connector	Weidmuller	WSI 6/LD 60-150V DC/AC	Fuse terminal, Screw connection, Fuse isolator, with LED, for screwable cross-connection, One end without connector, Screw connection, 6 mm <sup>2</sup> ;, 150 V, 6.3 A, G-Si. 5 x 20, Dark Beige
Connector	Weidmuller	WTA 6 WTR2.5	Test adapter (terminal), 1.5 mm <sup>2</sup> ;, 250 V, 6 A
Connector	Weidmuller	WTL 4	Test-disconnect terminal, Screw connection, 4 mm <sup>2</sup> ;, 500 V, 32 A, sliding, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WTL 6/1 STB RU	#N/A
Connector	Weidmuller	WTL 6/1/STB	Test-disconnect terminal, Screw connection, 6 mm <sup>2</sup> ;, 630 V, 41 A, sliding, Cross-disconnect: without, Integral test socket: Yes, TS 35, Dark Beige

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WTL 6/2	Test-disconnect terminal, Screw connection, 6 mm <sup>2</sup> ; 500 V, 41 A, sliding, Cross-disconnect: without, Integral test socket: Yes, TS 35, Dark Beige
Connector	Weidmuller	WTL 6/4 FF	Test-disconnect terminal, Screw connection, 6 mm <sup>2</sup> ; 800 V, 41 A, sliding, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WTR 2.5	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> ; 500 V, 24 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WTR 2.5 BL	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> ; 500 V, 24 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Blue
Connector	Weidmuller	WTR 2.5 GR	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> ; 500 V, 24 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Grey
Connector	Weidmuller	WTR 2.5 STB2.3	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> ; 500 V, 24 A, Pivoting, Cross-disconnect: without, Integral test socket: Yes, TS 35, Dark Beige
Connector	Weidmuller	WTR 2.5 STB2.3 BL	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> ; 800 V, 14 A, Pivoting, Cross-disconnect: without, Integral test socket: Yes, TS 35, Blue
Connector	Weidmuller	WTR 2.5/SI	Fuse terminal, Screw connection, Fuse isolator, for plug-in cross-connector, One end without connector, Screw connection, 2.5 mm <sup>2</sup> ; 250 V, 6.3 A, G-Si. 5 x 20, Dark Beige
Connector	Weidmuller	WTR 2.5/SI LD 36V	W-Series, Fuse terminal, Rated cross-section: 2.5 mm <sup>2</sup> , Screw connection
Connector	Weidmuller	WTR 2.5/ZZ	Test-disconnect terminal, Screw connection, 2.5 mm <sup>2</sup> ; 400 V, 16 A, Pivoting, Cross-disconnect: without, Integral test socket: Yes, TS 35, Dark Beige
Connector	Weidmuller	WTR 4	Test-disconnect terminal, Screw connection, 4 mm <sup>2</sup> ; 400 V, 32 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige

## DeltaV™ Alliance Product Program

### Weidmuller Product List - Date 05/20/20

Connector	Weidmuller	WTR 4 SL	Test-disconnect terminal, Screw connection, 4 mm <sup>2</sup> , 630 V, 32 A, Pivoting, Cross-disconnect: without, Integral test socket: No, TS 35, Dark Beige
Connector	Weidmuller	WTW EN	Partition plate (terminal), Intermediate plate, 86 mm x 62 mm, Dark Beige
Connector	Weidmuller	WTW WF6	Partition plate (terminal), End and intermediate plate, 101.8 mm x 58.45 mm, Dark Beige
Connector	Weidmuller	WTW WFF120	Partition plate (terminal), End and intermediate plate, 230 mm x 80 mm, Dark Beige
Connector	Weidmuller	WTW WFF185/300	Partition plate (terminal), End and intermediate plate, 287 mm x 90 mm, Dark Beige
Connector	Weidmuller	WTW WFF35	Partition plate (terminal), End and intermediate plate, 140 mm x 63 mm, Dark Beige
Connector	Weidmuller	WTW WFF70	Partition plate (terminal), End and intermediate plate, 190 mm x 71 mm, Dark Beige
Connector	Weidmuller	WZAD 240	Auxiliary connection (terminal), 10 mm <sup>2</sup> , Number of connections: 1
Connector	Weidmuller	WZAD 50N	Auxiliary connection (terminal), 6 mm <sup>2</sup> , Number of connections: 1
Connector	Weidmuller	WZAD 70/95	Auxiliary connection (terminal), Number of connections: 1
Connector	Weidmuller	WZAD 70N	Auxiliary connection (terminal), 6 mm <sup>2</sup> , Number of connections: 1
Connector	Weidmuller	WZAD 95N/120N	Auxiliary connection (terminal), 6 mm <sup>2</sup> , Number of connections: 1