



CERTIFICATION RECORD – CANADA / USA

FILE NUMBER: LR1443

Applicant: Biffi Italia s.r.l.
Localita Caselle San Pietro
Fiorenzuola d'Arda, Piacenza, 29017
ITALY

Manufacturer: Biffi Italia s.r.l.
Localita Caselle San Pietro
Fiorenzuola d'Arda, Piacenza, 29017
ITALY

Factory/Labeling Location: Biffi Italia s.r.l.
Localita Caselle San Pietro
Fiorenzuola d'Arda, Piacenza, 29017
ITALY

PRODUCT CATEGORY: Electric Valve Actuators

LR1443-1R2 – May 21, 2019 - Electric Valve Actuators, maximum ambient 60 °C, duty cycle 1 min ON/ 5 min OFF, CSA Enclosure types 4, 4X and 6.

MODELS

- F02_063, F02_125, F02_250, F02_500, F02_1000 & F02_2000 (BIFFI; F02 Series);
- EPI2_E006, EPI2_E013, EPI2_E025, EPI2_E051, EPI2_E091 & EPI2_E171 (KEYSTONE; EPI2 Series);
- EPI2_063, EPI2_125, EPI2_250, EPI2_500, EPI2_1000 & EPI2_2000 (KEYSTONE; EPI2 Series); and
- SCE300_063, SCE300_125, SCE300_250, SCE300_500, SCE300_1000 & SCE300_2000 (BETTIS; SCE300 Series)

Notes:

- field wiring connections shall be made by using certified crimp-on ring terminals as per manufacturer's instruction manual
- with optional OM3-F02 Local Interface Module (all models)
- with optional OM13-F02-EPI2 3 wires module (models rated 100-240 Vac 1ph only)
- with optional OM1-F02 modulating input/output module (all models)
- with optional OM9-F02 Profibus DPV1 interface module (all models)
- with optional OM11-F02 DeviceNet interface module (all models)



CERTIFICATION RECORD – CANADA / USA

FILE NUMBER: LR1443

LR1443-1R3 – January 28, 2020 - Electric Valve Actuators, ambient -40°C - +60 °C, duty cycle 1 min ON/ 5 min OFF, CSA Enclosure types 4, 4X and 6.

Increase temperature range from -25°C to -40°C for all listed models

MODELS: all listed models