

AVENTICS GmbH
Ulmer Straße 4
30880 Laatzen, GERMANY
Phone +49 (0) 5 11-21 36-0
Fax: +49 (0) 511-21 36-2 69
www.aventics.com
info@aventics.com

AVENTICS 

AVENTICS 

Montageanleitung | Assembly instructions | Instructions de montage | Istruzioni di montaggio | Instrucciones de montaje | Monteringsanvisning

Montage Druckschalter
Pressure switch assembly
Montage du manostat
Montaggio del pressostato
Montaje del presostato
Montering tryckkvakt

NL2 / NL4 / NL6

R412015406/04.2016,
Replaces: 04.2014, DE/EN/FR/IT/ES/SV

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The given information does not release the user from the obligation of own judgement and verification. It must be remembered that our products are subject to a natural process of wear and aging.

An example configuration is depicted on the title page. The delivered product may thus vary from that in the illustration.

Translation of the original operating instructions. The original operating instructions were created in the German language.

R412015406-BAL-001-AC/04.2016 Subject to modifications. © All rights reserved by AVENTICS GmbH, even and especially in cases of proprietary rights applications. It may not be reproduced or given to third parties without its consent.

