



2 ALL MEANS ARE IN MILLIMETER.
1 MATERIAL: SELECTED BY THE MANUFACTURER.

| POS | ITEM DESCRIPTION | QTY | REMARK |
|-----|---|-----|----------------|
| 08 | SCREW AND NUT FOR INSTALLATION OF ITEM 04 | 4 | M10x70 |
| 07 | REFLECTOR PLATE | 3 | T=3 L=780 |
| 06 | SIDE REFLECTOR PLATE | 2 | T=3 L=780 |
| 05 | ADJUSTMENT FEET ON LEGS | 4 | L=100 |
| 04 | LEGS | 4 | 40x40x2 L=500 |
| 03 | LEG RESTS | 4 | 50x50x3 L=100 |
| 02 | SHORT FRAME SQUARE BARS | 2 | 40x40x2 L=700 |
| 01 | LONG FRAME SQUARE BARS | 2 | 40x40x2 L=1200 |

| | | | | |
|--|------------|---|--------------------|--|
| ISSUED BY EMe-PB | | DRAWN WEEK 1810 | PRODUCT CODE - |  LAYOUTVÄGEN 1, 435 33 MÖLNLYCKE, SWEDEN |
| APPROVED BY - | | APP'D WEEK - | DOCUMENT TYPE 0 | |
| ORIGINAL DRAWING NO. D9261020-132 | SIZE A3 | 1 ST ANGLE  | SCALE - | INSTALLATION DRAWING TITLE REFLECTOR PLATE |
| CAD MAINTAINED, (PRO/E) | | DO NOT SCALE PRINT | | DRAWING NO. D9261020-132 |
| <small>THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN</small> | | | | ISSUE 02 |
| | | | | SHEET 1/1 |

2018-04-17 Electronic Master - Printed Copies Uncontrolled - Emerson Proprietary