



SIZE	OVERALL END TO END	ELECTRONICS CENTER TO BODY END	DIAMETER OF FLANGE	CENTER OF HOUSING TO TOP OF ELECTRONIC MOUNT BRACKET		SHROUD LENGTH	APPROXIMATE WEIGHT W. T. (LBS)	CENTER OF HOUSING TO	
				A	B			C	D
4"	4+2 & 4+1	44.50	22.25	9.94	12.25	19.50	1150	6.59	-
6"	4+2 & 4+1	49.00	24.50	12.40	13.25	21.60	1600	7.59	-
8"	4+4	33.25	18.82	15.00	13.88	24.98	1050	7.91	-
8"	4+2 & 4+1	35.25	17.32	15.00	13.88	24.98	1150	7.91	-
10"	4+4	33.75	18.40	17.50	14.94	24.98	1250	8.91	-
10"	4+2 & 4+1	39.75	18.57	17.50	14.88	24.98	1550	8.91	-
12"		36.50	19.82	20.50	15.94	26.83	1600	-	10.25
16"		37.50	18.75	25.50	17.44	30.18	2050	-	12.75
20"		42.75	21.38	30.50	19.69	34.18	3150	-	15.25
24"		47.50	23.75	36.00	21.94	40.18	4600	-	18.00
30"		44.50	23.82	43.00	25.07	48.33	4950	-	21.50
36"		46.50	24.82	50.00	28.19	53.30	6200	-	25.00

SALES ORDER NO.: _____
 CUSTOMER: _____
 CUSTOMER P.O. NO.: _____
 CERTIFIED CORRECT - MICRO MOTION INC.
 DATE: _____ BY _____

TAG EQUIPMENT NUMBER	SIZE	BORE ("F")

SINGLE SHELL SHROUD 4", 6", 8", 10", 12", 30" & 36"
 DOUBLE SHELL SHROUD 16", 20", 24"

REV	DATE	BY	DESCRIPTION	CHKD	APPD
AG	02/15/23	PH	CA: 1214444	BP	KG
AF	09/27/19	SC	CA: 1126534	BP	RG
AE	08/06/18	PN	CA: 1088481	GS	RG
D	12/13/16	PN	ECO: DMC-2080	GS	RG
C	10/27/16	PN	ECO: DMC-2025	GS	RG
B	04/07/16	SS	ECO: DMC-1767	GS	RG
A	09/24/15	SS	RELEASED	RG	RG

EMERSON
 OUTLINE & DIMENSIONAL
 ULTRASONIC FLOW METER 3415-3416-3417 W/ 60 DEGREE PORT ANGLE
 8"-36" & W/45 DEGREE PORT ANGLE FOR 4"-6" 300 PRESSURE CLASS
 R.F. FLG, J/K MOUNT

TITLE: _____
 Dwg. No. **DMC-010181**
 SHEET 1 OF 1

ALL LINEAR DIMENSIONS ARE IN INCHES.

THIS DOCUMENT IS CONFIDENTIAL, CONTAINS PROPRIETARY INFORMATION, AND SHOULD NOT BE DISTRIBUTED, COPIED OR OTHERWISE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF MICRO MOTION, INC.