



| ANSI 300 RF | OVERALL END TO END | CENTER TO END | DIAMETER OF FLANGE | CENTER OF HOUSING TO TOP OF JUNCTION BOX | CENTER OF HOUSING TO EDGE OF TRANSDUCER CONNECTOR | APPROXIMATE WEIGHT | CLEARANCE REQUIRED FOR SHROUD REMOVAL |
|-------------|--------------------|---------------|--------------------|--|---|--------------------|---------------------------------------|
| SIZE | A | B | C | D | E | W.T. (LBS) | G |
| 4" | 13.78 | 6.89 | 10.00 | 6.26 | 4.16 | 131 | 6.62 |
| 6" | 14.00 | 7.00 | 12.50 | 7.42 | 5.03 | 178 | 9.50 |
| 8" | 16.00 | 8.00 | 15.00 | 8.39 | 5.88 | 245 | 11.25 |
| 10" | 19.69 | 9.84 | 17.50 | 9.39 | 6.72 | 335 | 13.00 |

SALES ORDER NO.: _____
 CUSTOMER: _____
 CUSTOMER P.O. NO.: _____
 CERTIFIED CORRECT - MICRO MOTION INC.:
 DATE: _____ BY _____

| | | |
|----------------------|------|-----------|
| TAG EQUIPMENT NUMBER | SIZE | BORE (F") |
| | | |

NOTES:
 1) 2 INCH DIAMETER PIPE IS REQUIRED FOR REMOTE MOUNTING

| | | | | | | | |
|-----|----------|-----|-------------|------|------|--|--|
| | | | | | | | |
| BA | 02-15-23 | PH | CA:1213843 | BP | KG | TITLE 3812 LIQUID ULTRASONIC REMOTE MOUNT METER 4" - 10" 300 ANSI RF FLG | |
| B | 03-13-12 | MOD | ECO SP1564 | MOD | MM | DWN CV DATE 09/17/11 DWG NO. DMC-006362 | |
| A | 09/17/11 | CV | RELEASED | MOD | CV | CHKD MOD DATE 09/17/11 SHEET 1 OF 1 | |
| REV | DATE | DWN | DESCRIPTION | CHKD | APPD | APPD KGD DATE 09/17/11 | |

THIS DOCUMENT IS CONFIDENTIAL, CONTAINS PROPRIETARY INFORMATION, AND SHOULD NOT BE DISTRIBUTED, COPIED OR OTHERWISE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF MICRO MOTION, INC.