

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

| REVISIONS |     |                       |       |      |      |      |
|-----------|-----|-----------------------|-------|------|------|------|
| REV       | ECN | DESCRIPTION OF CHANGE | DRAWN | CHKD | APVD | DATE |

D

D



## Transmitter:

3700

3700  
IS TERMINAL  
(BLUE)

4-WIRE IS Cable  
1000 ft [300 m]  
(maximum cable length)

CUSTOMER SUPPLIED CABLE  
MAXIMUM LENGTH:  
1000 ft (300m) OF 18 AWG(0.8 mm<sup>2</sup>)  
300 ft (100m) OF 22 AWG(0.35 mm<sup>2</sup>)




9-WIRE Remote Core Processor  
(supplied with transmitter)

## J-Box Terminals:

Sensor Type:

DS600S\*\*\*\*M


## Sensor Junction Box



9-WIRE IS Cable  
60 ft [18 m]  
(maximum cable length)

NOTE:  
Prepare IS Cable per the  
instructions provided with  
the cable.

VALID FOR APPROVAL CODES:  
- Micro Motion Standard General Purpose



A

A

| ITEM  | DESCRIPTION               | PART OR REF. NO. | MATL. OR MFR                            | QTY.                              |
|-------|---------------------------|------------------|-----------------------------------------|-----------------------------------|
|       |                           |                  | MICRO MOTION, INC.<br>BOULDER, COLORADO |                                   |
|       | THIRD ANGLE<br>PROJECTION |                  | WIRING,<br>DS600 JBOX TO 3700           |                                   |
| DRAWN | NAME                      | DATE             | SIZE                                    | DWG. NO.                          |
| CHKD. | JLA                       | 1/5/04           | D                                       | EW-20001942                       |
| APVD. | JLA                       | 1/5/04           | SCALE NONE                              | DO NOT SCALE DRAWING SHEET 1 OF 1 |

COPYRIGHT 2004 MICRO MOTION, INC.  
ALL RIGHTS RESERVED

8

7

6

5

4

3

2

1