


Features and Benefits

- For gas pilot and gas burner control on industrial atmospheric and forced draught burners, also used in kilns and furnaces in process industries
- All valves have been type tested to EN 161 and satisfy the Regulation (EU) 2016/426 on gas appliances
Certificate of conformity BSI: No. CE 688365
- All valves are for class A group 2 service and cover gas family 1, 2 and 3
- All valves are suitable to withstand 150 mbar back pressure
- Direct lift valves with resilient soft seating for tight shut-off



General

Differential pressure

See «SPECIFICATIONS» [1 bar = 100 kPa]

Response time

1 s max.

Fluids (*)	Temperature range (TS)	Seal materials (*)
combustible gas	0°C to +60°C	NBR (nitrile)

Materials of components in contact with fluid


(*) Ensure that compatibility of materials in contact with fluids is verified.

Body	Brass
Shading coil	Copper
Core tube	Stainless steel, AISI 305
Core and plugnut	Stainless steel, AISI 430F
Springs	Stainless steel, AISI 302
Seal	NBR
Disc	NBR

Electrical characteristics

Coil insulation class	F
Connector	Spade plug (cable Ø 6-10 mm)
Connector specification	ISO 4400 / EN 175301-803, form A
Electrical safety	IEC 335
Electrical enclosure protection	Moulded IP65 (EN 60529)
Standard voltages	AC (~) : 24V - 48V - 115V - 230V/50 Hz
(Other voltages and 60 Hz on request)	

Operator ambient temperature range (TS) (°C)	Power ratings			Replacement coil ~
	Inrush ~ (VA)	Holding ~ (VA) (W)		
0 to +60	24	16	8.1	230 V/50 Hz 515488-059



Options

- Connector with visual indication and peak voltage suppression or with cable length of 2 m

For Low Pressure Gas, EN 161 | Direct Operated, 1/8" or 1/4" threaded



Specifications


Pipe size	Orifice size (mm)	Flow (m ³ /h) (l/min)		Operating pressure differential (bar)		Power coil (W)	Thread type	Dimensions / Type ⁽¹⁾	15-DIGIT PRODUCT CODE									
				Min.	Max (PS) Gas (*)				Basic code	Voltage code								
										~	~	24 V/50 Hz	48 V/50 Hz	115 V/50 Hz	230 V/50 Hz	.	.	
Without manual operator																		
NC - Normally closed																		
1/8"	3.2	0.41	6.83	0	2.76	8.1	G	01	G262K002S1NG0		FL	FR	FT	F8	-	-		
1/4"	7.1	1.12	18.67	0	2.1	8.1	G*	01	E262K090S1NG0									


⁽¹⁾ For dimensions, see drawing(s) for each construction type on the following page(s).

(*) Ensure that compatibility of materials in contact with fluids is verified.

Gaz Flow Chart



		Spare parts kits no.	
		AC (-)	
			NBR
	G262K002S1NG0	M200001	NG0
	E262K090S1NG0		

		Accessories code
	Mounting bracket Steel version (AISI 1010 / 1.1121)	M200094A00
	Mounting bracket Stainless steel version (AISI 304 / 1.4301)	M200095A00

Installation


- The solenoid valves can be mounted in any position without affecting operation
- Solenoid valves have 2 mounting holes in body
- Thread connection “E” applicable for 1/4” have standard thread according to ISO 228/1 and ISO 7/1. Thread connection “G” applicable for 1/8”, have standard thread according to ISO 228/1
- Installation/maintenance instructions in multiple languages are available on our website

Dimensions (mm), Weight (kg)

Configurator - CAD Files




TYPE 01
Electrical interface "S1"
Epoxy moulded
IEC 335 / ISO 4400
IP65



Type	Pipe size	A	B	C	D	E	F	G	H	X	Weight ⁽¹⁾
01	1/8"	88	51	30	30	43	62	71	88	26	0.30
	1/4"	88	51	30	40	43	65	75	92	30	0.42

⁽¹⁾ Incl. coil(s) and connector(s).

① 2 mounting holes:
M5 dia., depth 6.5 mm (1/8")
M5 dia., depth 7.5 mm (1/4")



Mounting bracket
Steel or stainless steel

M200094A00 / M200095A00

