


Configuration Data Sheet

Date: _____	Service: _____
Customer: _____	Tag: _____
Address: _____	
Attention: _____	Department: _____
Telephone: _____	Fax: _____
Order Number: _____	Project: _____
Quantity: _____	Delivery Date: _____



$D_1 =$ _____ $D_2 =$ _____
 $L_2 =$ _____ $L_1 =$ _____

Key
L_2 = Maximum level
L_1 = Minimum level
D_2 = Distance between taps
D_1 = Distance between transmitter and high pressure tap.

PROCESS DATA

Working Pressure: Max. _____ Min. _____

Minimum (Vacuum) Pressure: _____

Process Temperature (High Side):Max. _____ Min. _____

Process Temperature (Low Side):Max. _____ Min. _____

Ambient Temperature (High Side):Max. _____ Min. _____

Ambient Temperature (Low Side):Max. _____ Min. _____

Describe Vessel Cleaning Process: _____

Process Fluid:Specific Gravity: _____

Name of Application: _____

Required Response Time: _____

Required percent of Span Accuracy: _____

Other:

Notes:

HIGH PRESSURE SIDE

Industry Standard: _____ (ANSI, DIN, JIS)

Seal Type: _____ Process Connection Type: _____

Process Connection Size: _____ Gasket Surface Type: _____

Materials Type: _____

Other:

LOW PRESSURE SIDE

Industry Standard: _____ (ANSI, DIN, JIS)

Seal Type: _____ Process Connection Type: _____

Process Connection Size: _____ Gasket Surface Type: _____

Materials Type: _____

Other: