



## KEYSTONE BREWSEAL BUTTERFLY VALVES

### WAFER AND LUGGED

Resilient seated butterfly valves DN 40 - 300 wafer and lugged versions, optimized for the food and beverage industry



### FEATURES

- Top bushing absorbs actuator side thrust loads.
- Dirtscraper prevents moisture penetrating into the shaft area.
- Actuator flange acc. ISO 5211.
- High solid, glossy, silicone free, paint system ensuring excellent corrosion resistance.
- Body locating holes ease installation and centering between the flanges.
- Sealed body splits prevent moistures from penetrating behind the seat.
- Rounded polished disc edge gives full concentric sealing, lower torques, longer seat life and bubble-tight shut-off.
- The seat is field replaceable and fully isolates the body and stem from the flow.
- Primary stem sealing exceeds the pressure rating of the valve and prevents leakage through shaft area to atmosphere.
- A secondary shaft sealing provides back-up safety.
- A molded-in O-ring in the seat for flange sealing eliminates the need for gaskets.
- The thin disc provides the very minimum obstruction to flow.
- Relief hole drains possible fluids from the top plate recess space.
- Wafer and lugged body design, acc. ISO 5752/5 short (DIN 3202, Part 3/K1).
- All valves are conform Pressure Equipment Directive (97/23/EU) Module H.
- Available approvals: CE Marking, FDA.
- Special XP-EPDM seat for specific brewery applications such as hot and cold wort.

### GENERAL APPLICATIONS

The disc and seat materials used in the BrewSeal are specifically suited for food and beverage applications including brew houses, pasteurization and filling areas.

### NOTE

Valve in foreground shown with innovative composite handle and throttling plate.


### TECHNICAL DATA

|                       |                      |
|-----------------------|----------------------|
| Pressure (bar):       | 10                   |
| Temperature (°C):     | -30 +150             |
| Sizes (DN):           | 40 - 300             |
| Flange accommodation: | PN 10/16<br>ASME 150 |



# KEYSTONE BREWSEAL BUTTERFLY VALVES

## WAFER AND LUGGED



### VALVE DIMENSIONS (mm)

| DN  | A   | B   | C   | U     |        | D  | H   | Q   | YY  | F  | Shaft    |                     | Actuator flange acc. ISO 5211/1 |     |    |   |    |     |             | Wafer mass (kg) | Lugged mass (kg) |           |          |
|-----|-----|-----|-----|-------|--------|----|-----|-----|-----|----|----------|---------------------|---------------------------------|-----|----|---|----|-----|-------------|-----------------|------------------|-----------|----------|
|     |     |     |     | Wafer | Lugged |    |     |     |     |    | $G_{H9}$ | $K_{-0.05}^{\circ}$ | Type                            | E   | J  | L | P  | PCD | Hole $\phi$ |                 |                  | No. holes | $\alpha$ |
| 40  | 40  | 78  | 130 | 56    | 68     | 33 | 49  | 24  | 64  | 25 | 12       | 8                   | F-05                            | 65  | 35 | 4 | 9  | 50  | 6.6         | 4               | 45.0             | 1.5       | 2.7      |
| 50  | 50  | 94  | 135 | 61    | 73     | 43 | 66  | 27  | 80  | 25 | 12       | 8                   | F-05                            | 65  | 35 | 4 | 9  | 50  | 6.6         | 4               | 45.0             | 2.1       | 3.7      |
| 65  | 62  | 109 | 150 | 76    | 80     | 46 | 78  | 43  | 93  | 30 | 16       | 11                  | F-07                            | 90  | 55 | 4 | 12 | 70  | 9.0         | 4               | 45.0             | 3.2       | 5.0      |
| 80  | 78  | 126 | 160 | 84    | 103    | 46 | 97  | 64  | 112 | 30 | 16       | 11                  | F-07                            | 90  | 55 | 4 | 12 | 70  | 9.0         | 4               | 45.0             | 3.6       | 5.9      |
| 100 | 99  | 156 | 180 | 97    | 117    | 52 | 129 | 87  | 144 | 30 | 16       | 11                  | F-07                            | 90  | 55 | 4 | 12 | 70  | 9.0         | 4               | 45.0             | 5.2       | 8.3      |
| 125 | 124 | 189 | 195 | 120   | 133    | 56 | 160 | 113 | 175 | 30 | 20       | 14                  | F-07                            | 90  | 55 | 4 | 12 | 70  | 9.0         | 4               | 45.0             | 7.6       | 11.5     |
| 150 | 151 | 214 | 210 | 132   | 144    | 56 | 181 | 141 | 196 | 30 | 20       | 14                  | F-07                            | 90  | 55 | 4 | 12 | 70  | 9.0         | 4               | 45.0             | 8.5       | 13.0     |
| 200 | 195 | 267 | 240 | 164   | 180    | 60 | 233 | 188 | 248 | 50 | 25       | 18                  | F-12                            | 150 | 85 | 4 | 18 | 125 | 13.5        | 4               | 45.0             | 16.0      | 22.2     |
| 250 | 245 | 321 | 275 | 200   | 220    | 68 | 290 | 237 | 305 | 50 | 30       | 22                  | F-12                            | 150 | 85 | 4 | 18 | 125 | 13.5        | 4               | 45.0             | 23.5      | 33.5     |
| 300 | 292 | 375 | 310 | 227   | 245    | 78 | 340 | 283 | 355 | 50 | 30       | 22                  | F-12                            | 150 | 85 | 4 | 18 | 125 | 13.5        | 4               | 45.0             | 32.0      | 51.0     |


### NOTES

1. Flange accommodation must be specified when ordering.
2. Q is the disc chordal dimension at face of valve for disc clearance into pipe fitting or equipment.
3. Specify size, figure number, part name, material and flange accommodation when ordering spare parts.
4. Valve size shown is DN 100.
5. Mass shown is for valve with a composite disc stem about 3% up to 20% lower, depending on size and wafer or lugged type.



# KEYSTONE BREWSEAL BUTTERFLY VALVES

## WAFER AND LUGGED



DN 40 - 300  
(WAFER VERSION IS SHOWN)

### ACTUATOR SELECTION

| Actuator type | Figure   | Remark              | Suitable for |
|---------------|----------|---------------------|--------------|
| Handle        | F419     | Leverlock           | DN 40 - 150  |
|               |          | Composite leverlock |              |
| Gear          | F455     | CM or WM            | DN 40 - 300  |
| Pneumatic     | PremiAir | -                   | DN 40 - 300  |
| Electric      | EPI-2    | -                   | DN 40 - 300  |

### NOTE

For other actuators and selection, please contact your local sales outlet.

### PARTS LIST

| Part | Name          |
|------|---------------|
| 1.   | Dirtscraper   |
| 2.   | Shaft bushing |
| 3.   | Body          |
| 4.   | Shaft         |
| 5.   | Seat          |
| 6.   | Disc          |
| 7.   | Split seal    |
| 8.   | Body screws   |
| 9.   | Disc screw    |

# KEYSTONE BREWSEAL BUTTERFLY VALVES

## VALVE DATA FOR WAFER AND LUGGED VERSIONS

### K<sub>v</sub> VALUES

| Disc opening | DN   |      |      |      |      |      |      |      |      |       |
|--------------|------|------|------|------|------|------|------|------|------|-------|
|              | 40   | 50   | 65   | 80   | 100  | 125  | 150  | 200  | 250  | 300   |
| 10°          | -    | -    | -    | -    | -    | -    | -    | -    | 19.5 | 47.3  |
| 20°          | 0.6  | 0.9  | 2.4  | 5.0  | 9.2  | 14.8 | 22.4 | 53   | 151  | 314   |
| 30°          | 3.8  | 5.9  | 11.1 | 20.4 | 37.6 | 66.8 | 108  | 204  | 300  | 369   |
| 40°          | 9.2  | 14.3 | 26.2 | 47.4 | 84.8 | 143  | 221  | 392  | 572  | 718   |
| 50°          | 18.1 | 28.3 | 49.7 | 87.9 | 154  | 254  | 381  | 657  | 956  | 1212  |
| 60°          | 33.5 | 51.6 | 87.4 | 151  | 260  | 420  | 621  | 1050 | 1540 | 1993  |
| 70°          | 54.2 | 88.6 | 156  | 274  | 471  | 743  | 1062 | 1731 | 2628 | 3624  |
| 80°          | 57.6 | 111  | 232  | 442  | 789  | 1261 | 1802 | 2946 | 4616 | 6613  |
| 90°          | 58.5 | 112  | 249  | 492  | 895  | 1444 | 2099 | 3715 | 6883 | 11343 |

### NOTES

1. Rated K<sub>v</sub> = the volume of water in m<sup>3</sup>/hr that will pass through a given valve opening at a pressure drop of 1 bar.

$$2. K_v = Q \sqrt{\frac{R.D.}{\Delta p}} \text{ (liquid)}$$

Q = flow through valve (m<sup>3</sup>/hr)

R.D. = relative density of liquid (water = 1)

### DYNAMIC TORQUE FACTOR F<sub>T</sub> FOR METRIC UNITS

| Disc opening | DN  |     |     |      |      |      |       |       |       |       |
|--------------|-----|-----|-----|------|------|------|-------|-------|-------|-------|
|              | 40  | 50  | 65  | 80   | 100  | 125  | 150   | 200   | 250   | 300   |
| 10°          | -   | -   | -   | -    | -    | -    | -     | -     | -     | -     |
| 20°          | 0.1 | 0.1 | 0.2 | 0.5  | 0.9  | 1.8  | 3.0   | 7.2   | 14.1  | 24.3  |
| 30°          | 0.1 | 0.3 | 0.6 | 1.1  | 2.1  | 4.1  | 7.1   | 16.8  | 32.8  | 56.7  |
| 40°          | 0.3 | 0.5 | 1.1 | 2.1  | 4.1  | 8.0  | 13.8  | 32.8  | 64.1  | 110.7 |
| 50°          | 0.4 | 0.9 | 1.9 | 3.6  | 7.0  | 13.7 | 23.6  | 56.0  | 109.4 | 189.0 |
| 60°          | 0.8 | 1.5 | 3.3 | 6.1  | 12.0 | 23.4 | 40.5  | 96.0  | 187.5 | 324.0 |
| 70°          | 1.3 | 2.5 | 5.5 | 10.2 | 20.0 | 39.1 | 67.5  | 160.0 | 312.5 | 540.0 |
| 80°          | 2.0 | 3.9 | 8.5 | 15.9 | 31.0 | 60.5 | 104.6 | 248.0 | 484.4 | 837.0 |
| 90°          | -   | -   | -   | -    | -    | -    | -     | -     | -     | -     |

### NOTES

1. Dynamic operating torque formula:

$$T_D = F_T \times \Delta P$$

T<sub>D</sub> = Dynamic torque (Nm)

ΔP = Pressure drop across disc at desired disc-opening (bar)

F<sub>T</sub> = Dynamic torque factor (see table)

2. The above mentioned dynamic torque includes all frictional resistances.

3. The dynamic torque is tending to close the disc.

4. ΔP to be determined with K<sub>v</sub> formula.

### MAXIMUM ALLOWABLE SHAFT TORQUES IN Nm

| W. Nr.   | DN |    |     |     |     |     |     |     |      |      |
|----------|----|----|-----|-----|-----|-----|-----|-----|------|------|
|          | 40 | 50 | 65  | 80  | 100 | 125 | 150 | 200 | 250  | 300  |
| 1.4408   | 32 | 32 | 80  | 80  | 80  | 160 | 160 | 327 | 580  | 580  |
| 1.4057 * | 65 | 65 | 110 | 160 | 160 | 320 | 320 | 935 | 1660 | 1660 |

\* for Composite disc

### NOTES

1. In ISO 5211/2 a table is listed representing the maximum torques which can be transmitted through the actuator flange. These values are based upon specific criteria and can be lower than the maximum allowable shaft torques. In this case the criteria can be changed in order to reach the maximum allowable shaft torques.

# KEYSTONE BREWSEAL BUTTERFLY VALVES

## VALVE DATA FOR WAFER AND LUGGED VERSIONS

### SIZING TORQUES IN Nm

| ΔP in bar   | DN |    |    |    |     |     |     |     |     |     |
|-------------|----|----|----|----|-----|-----|-----|-----|-----|-----|
|             | 40 | 50 | 65 | 80 | 100 | 125 | 150 | 200 | 250 | 300 |
| <b>I*</b>   |    |    |    |    |     |     |     |     |     |     |
| 3.5         | 10 | 13 | 19 | 26 | 37  | 58  | 81  | 148 | 241 | 345 |
| 7           | 10 | 13 | 20 | 27 | 40  | 63  | 88  | 164 | 271 | 387 |
| 10          | 11 | 14 | 21 | 30 | 44  | 70  | 99  | 188 | 315 | 451 |
| <b>II*</b>  |    |    |    |    |     |     |     |     |     |     |
| 3.5         | 11 | 14 | 21 | 29 | 42  | 66  | 93  | 169 | 274 | 392 |
| 7           | 11 | 14 | 22 | 31 | 45  | 71  | 100 | 185 | 303 | 434 |
| 10          | 11 | 15 | 23 | 33 | 49  | 78  | 111 | 208 | 347 | 498 |
| <b>III*</b> |    |    |    |    |     |     |     |     |     |     |
| 3.5         | 12 | 15 | 23 | 32 | 48  | 74  | 105 | 190 | 306 | 439 |
| 7           | 12 | 16 | 24 | 34 | 50  | 79  | 112 | 206 | 336 | 481 |
| 10          | 12 | 16 | 26 | 36 | 54  | 86  | 122 | 229 | 380 | 545 |

\* Application I, II, III

### NOTES

- Application I** : Water.  
Temp.: 0-80 °C; Valve opens at least once a month.
    - Application II** : All other liquid applications and lubricating gasses.
    - Application III** : Non-lubricating and dry media.
  - The charted maximum sizing operating torque is the sum of all friction and resistance for opening and closing of the disc against the indicated pressure differential.
  - The effect of dynamic torque is not considered in tabulation.
  - In sizing operators it is not necessary to include safety-factors.
- \* For limited shaft material selection only.

### MATERIAL SPECIFICATION

| Part name    | Material                        | EN designation   | EN/DIN Mat. no. | Remarks                          |
|--------------|---------------------------------|------------------|-----------------|----------------------------------|
| Body         | Ductile iron                    | GJS-400-15       | EN GJS 400 15   | Pressure 10 bar                  |
|              | Stainless steel                 | GX5CrNiMo19-11-2 | 1.4408          | Comparable with CF8M             |
| Disc         | Stainless steel                 | GX5CrNiMo19-11-2 | 1.4408          | Comparable with CF8M             |
|              | Stainless steel mirror polished | GX5CrNiMo19-11-2 | 1.4408          | Comparable with CF8M             |
|              | Composite                       |                  |                 | Engineered Composite DN 40 - 300 |
| Shaft        | Stainless steel (cast)          | GX5CrNiMo19-11-2 | 1.4408          | DN 40 - 300                      |
|              | Stainless steel                 | X 17 CrNi 16-2   | 1.4057          | DN 40 - 300                      |
| Seat         | XP EPDM                         |                  |                 | FDA approved                     |
|              | PTFE/EPDM                       |                  |                 | Upon request                     |
| Body screw   | Stainless steel                 |                  |                 | A2                               |
| Bushing      | Polyacetal                      |                  |                 |                                  |
| Dirt scraper | NBR/steel                       |                  |                 |                                  |
| Split seal   | Graphite                        |                  |                 |                                  |

### NOTE

Please refer to the OptiSeal documentation for safety, installation and maintenance instructions.

