

# ATEX Hazardous Area Approvals Fisher™ FIELDVUE™ DLC3020f Digital Level Controller for FOUNDATION™ Fieldbus

## Hazardous Area Classifications and Special Instructions for “Safe Use” and Installations in Hazardous Locations

Certain nameplates may carry more than one approval, and each approval may have unique installation/wiring requirements and/or conditions of “safe use”. These special instructions for “safe use” are in addition to, and may override, the standard installation procedures. Special instructions are listed by approval.

---

### Note

This information supplements the nameplate markings affixed to the product and the DLC3020f quick start guide ([D103470X012](#)) and instruction manual ([D103434X012](#)), available from your [Emerson sales office](#) or Fisher.com.

Always refer to the nameplate itself to identify the appropriate certification.

---

### **⚠ WARNING**

**Failure to follow these conditions of “safe use” could result in personal injury or property damage from fire or explosion, or area re-classification.**

---

### Special Conditions for Safe Use

#### Intrinsically Safe

This apparatus can only be connected to an intrinsically safe certified equipment and this combination must be compatible regarding the intrinsic safety rules (see electrical parameters in table 1).

#### Flameproof, Type n

No special conditions for safe use.

Refer to table 1 for additional approval information.

Table 1. Approval Information

Certification	Certification Obtained	Entity Rating		Temperature Code
		Fieldbus	FISCO	
ATEX	Ⓢ II 1 G D Intrinsically Safe Ex ia IIC T5/T6 Ga Dust Ex ia IIIC T87°C (Tamb ≤ 80°C), T80°C (Tamb ≤ 73°C) Da IP66	Ui ≤ 24 V Ii ≤ 380 mA Pi ≤ 1.4 W Ci ≤ 5 nF Li = 0 mH	Ui = 17.5 V Ii = 380 mA Pi = 5.32 W Ci = 5 nF Li = 0 mH	T5 (Tamb ≤ 80°C) T6 (Tamb ≤ 73°C)
	Ⓢ II 2 G D Flameproof Ex d IIC T5/T6 Gb Dust Ex tb IIIC T87°C (Tamb ≤ 80°C), T80°C (Tamb ≤ 73°C) Db IP66	---	---	T5 (Tamb ≤ 80°C) T6 (Tamb ≤ 73°C)
	Ⓢ II 3 G D Type n Ex nA IIC T5/T6 Gc Dust Ex tc IIIC T87°C (Tamb ≤ 80°C), T80°C (Tamb ≤ 73°C) Dc IP66	---	---	T5 (Tamb ≤ 80°C) T6 (Tamb ≤ 73°C)

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher and FIELDVUE are marks owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Automation Solutions, Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Automation Solutions  
 Marshalltown, Iowa 50158 USA  
 Sorocaba, 18087 Brazil  
 Cernay, 68700 France  
 Dubai, United Arab Emirates  
 Singapore 128461 Singapore

www.Fisher.com

