



ANSI 150 RF	OVERALL END TO END	CENTER TO END	DIAMETER OF FLANGE	CENTER OF HOUSING TO TOP OF JUNCTION BOX	CENTER OF HOUSING TO EDGE OF TRANSDUCER CONNECTOR	APPROXIMATE WEIGHT	CLEARANCE REQUIRED FOR SHROUD REMOVAL
SIZE	A	B	C	D	E	W.T. (LBS)	G
4"	13.78	6.89	9.00	6.26	4.16	113	6.62
6"	14.00	7.00	11.00	7.42	5.03	148	9.50
8"	16.00	8.00	13.50	8.39	5.88	196	11.25
10"	19.69	9.84	16.00	9.39	6.72	271	13.00

SALES ORDER NO.: _____
 CUSTOMER: _____
 CUSTOMER P.O. NO.: _____
 CERTIFIED CORRECT - MICRO MOTION INC.: _____
 DATE: _____ BY _____

TAG EQUIPMENT NUMBER	SIZE	BORE (F")

NOTES:
 1) 2 INCH DIAMETER PIPE IS REQUIRED FOR REMOTE MOUNTING

STANDARD MFG TOLERANCE BLOCK UNLESS OTHERWISE NOTED ALL DIMENSIONS IN INCHES X.XX ±.015 X.XXX ±.005 DEC. ±0' 30" FINISH 200 RA MAX CORNER RAD. .003-.015 GEOMETRIC TOLERANCES & DIMENSIONS PER ASME Y14.5M LATEST REVISION					
TITLE 3812 LIQUID ULTRASONIC REMOTE MOUNT METER 4" - 10" 150 ANSI RF FLG				DWG NO. DMC-006426	
AA	02-15-23	PH	CA:1214444	BP	KG
A	09/17/11	CV	RELEASED	MOD	KDG
REV	DATE	DWN	DESCRIPTION	CHKD	APPD
THIS DOCUMENT IS CONFIDENTIAL, CONTAINS PROPRIETARY INFORMATION, AND SHOULD NOT BE DISTRIBUTED, COPIED OR OTHERWISE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF MICRO MOTION, INC.				SHEET 1 OF 1	