## **G3 Fieldbus - Electronics Made Easy!**

Innovative Graphic Display is used for easy commissioning, visual status & diagnostics.

#### **Commissioning Capabilities**

- Set network address (including IP & Subnet mask for Ethernet)
- · Set baud rate
- Set auto or manual I/O sizes
- Set fault/idle output states
- · Set brightness
- Set factory defaults
- · Visual diagnostics

- · Shorted and open load detection
- Shorted sensor/cable detection
- Low & missing power detection
- · Missing module detection
- · Self-test activation
- · Log of network errors
- · Distribution errors



Graphic Display for Configuration & Diagnostics



Auto Recovery Module



Highly Distributable



Easy, Robust Connections

#### **G3 Fieldbus Communications Electronics**

Why use Aventics Fieldbus communication electronics?

## Modular Reality...

#### No internal wiring simplifies assembly

- SPEEDCON® M12 connector technology allows for fast and efficient 1/2 turn I/O connector attachment
- Power connector allows output power to be removed while inputs and communication are left active
- · IP65 protection
- Up to 1200 Input/1200 Output capability with one communication node!
- Up to 128 valve solenoids per manifold, up to 17 manifolds per communication node!
- One node supports 16 I/O modules Analog I/O, Digital I/O (NPN & PNP) and Specialty
- Integrated web server with EtherCAT®, EtherNet/ IP™ DLR, Ethernet POWERLINK®, Modbus® TCP/IP, and PROFINET™
- Innovative clip design allows easy module removal/ replacement without dismantling manifold
- · Auto Recovery Module (ARM) protects configuration information during a critical failure. Allows configuration information to be saved and reloaded to replacement module automatically

## Aventics I/O with SPEEDCON® Technology

- 1/2 turn for faster I/O connections
- · Backwards compatible with standard M12 cables/connectors
- Meets the same IP/NEMA standards as M12/Micro cables/connectors
- · Same cost as standard M12/Micro cables/connectors

#### **Supported Protocols**

- CANopen®
- DeviceNet™
- EtherCAT®
- EtherNet/IP™ DLR w/ QuickConnect™
- Ethernet POWERLINK®
- Modbus® TCP/IP
- PROFIBUS™ DP
- PROFINET™








Modbus is a registered trademark of Modbus Organization, Inc.
EtherNet/IP, DeviceNet and QuickConnect are trademarks of ODVA.
EtherCAT is a registered trademark of the EtherCAT Technology Group.
CANopen is a registered Community trademark of CAN in Automation e.V.
PROFIBUS and PROFINET are trademarks of Profibus Nutzerorganisation e.V.
Ethernet POWERLINK is a registered trademark of Bernecker + Rainer Industrie – Elektronik Ges.m.b.H.

## **G3 Electronics Modularity**

#### Discrete I/O

The Series G3 product line is a completely modular system. All of the G3 electronic modules plug together, via mechanical clips, allowing easy assembly and field changes. This makes the system highly distributable. Additional flexibility is incorporated because the same modules can be used in either centralized or distributed applications.

The G3 electronics interfaces with the series 501, 502 and 503 but also with the highly modular Aventics generation Series 2000 and ISO 5599-2 Series 511, 512 and 513 valve lines to further enhance the modularity and flexibility of the entire system solution.




## **G3 Platform Distribution Options**

The G3 platform is flexible to the point that there are a virtually infinite number of I/O distribution options using the few basic G3 modules. The following basic rules should be followed in the configuration of your control architecture.

Typical Main Fieldbus Island


#### Valve Side


• Up to a total of 128 (Series 501)/80 (Series 502/503) valve solenoids can be driven in a manifold assembly integrated into the Main Fieldbus Island. This can be any number of single or double solenoid valves with a total number of solenoids not to exceed 128 (Series 501)/80 (Series 502/503).




#### I/O Side Distribution


- A total of 16 modules can be integrated into the network and controlled by the main fieldbus communication module (Node)
- Modules include analog and digital I/O modules providing addressing capacity for up to 1200 Inputs/1200 Outputs per node
- Unique distribution system allows system efficiency by allowing the same modules to be used in either centralized or distributed applications
- Distribution options include Inputs only, Outputs only, I/O only, valves with Inputs, valves with Outputs and valves with I/O
- Configuration can include up to 16 of the following modules:
  - Digital I/O modules
  - Sub-bus valve modules
  - Analog I/O modules







## **G3 Platform Distribution Options**




#### **Distribution Benefits**

- Up to 1200 Input / 1200 Output capability with one communication node!
- 16 manifolds per communication node, in line or in star
- Up to 128 valve solenoids per manifold, up to 17 manifolds per communication node!
- One node supports 16 distributed modules max. (Manifold, Analog I/O, Digital I/O (NPN & PNP)
- Unique distribution system allows system efficiency by allowing the same modules to be used in either centralized or distributed applications
- Maximum Sub-bus length not to exceed 30 meters. Maximum Sub-bus cable current not to exceed 4 amps or excessive cable voltage drops per segment. Auxiliary power connections available for currents above 4 amps. Consult factory for possible deviations.


NOTE: See page 39 for reference numbers


## **G3 Platform Distribution Options**


## **Integrated Valve systems**



## Star distributed mode







## **DeviceNet**<sup>™</sup>

DeviceNet™ is an open bus fieldbus communication system developed by Allen-Bradley based on Controller Area Network (CAN) technology. The governing body for DeviceNet™ is the Open DeviceNet™ Vendors Association (ODVA). The ODVA controls the DeviceNet™ specification and oversees product conformance testing.


Aventics' G3 nodes for DeviceNet<sup>™</sup> have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

They have been tested and approved for conformance by the ODVA.

More information about DeviceNet™ and the ODVA can be obtained from the following website: www.odva.org

Description	Replacement Part Number
DeviceNet™ Communications Module (node)	240-180





#### **Technical Data**

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 V DC +/- 10%	0.0404 A
BUS Power	11-25 V DC	0.025 A
Valves & Discrete I/O	24 V DC +/- 10%	8 A Maximum
Power Connector	Single key 4 pin 7/8" MINI type (male)	
Communication Connector	Single key 5 pin 7/8" MINI type (male)	
LEDs	Module Status and Network Status	

Operating Data		
Temperature Range (ambient)	-20°C to +50°C (Electronics only)	
Humidity	95% relative humidity, non-condensing	
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6	
Moisture Protection	IP65_IP67 (with appropriate assembly and termination)	

Configuration Data		
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, DeviceNet QuickConnect, Diagnostics and all other system settings.	
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure.	
Maximum Valve-Solenoid Outputs	32 for all series	
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data		
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, with Auto-Baud detection	
Supported Connection Type	Polled, Cyclic, Change of State (COS) and combination Message Capability	
Communication Connector	Single key 5 pin 7/8" MINI type (male)	
Diagnostics	Power, short, open load conditions and module health are monitored	
Special Features	Supports Auto-Device Replacement (ADR) and fail-safe device settings	

Weight	
DeviceNet™ Communications Module	252 g

#### **DeviceNet™** bus connection

the front panel of the communication module for DeviceNet™ is equipped with a 5 pin 7/8 - 16 UN male socket (E).


The bus can be connected in the two following ways:

- directly to the module with a T-connector;
- with a straight connector, cable (max. length: 3 m) and a DeviceNet distributor box.

The modules on either side of the system must be provided with terminating resistors (L1 or L2).

#### Wiring with T-connector

#### Connection with DeviceNet<sup>™</sup> distributor box (X)



### **Accessories for DeviceNet™**

The modules on either side of the system must be provided with terminating resistors  $\ensuremath{\mathbb{L}}$ 

N°	Accessories	Description			Part Number (Europe)	Part Number (Americas)
		M12 Backplane extension cables with	SPEEDCON co	nnecto		
G	100	5 pin straight 7/8-16 UN female network connec Field Wireable	tor,		88161930	MC05F90000000000
	×	5 pin straight 7/8-16 UN female network connec	tor,	5 m	-	MC0505MGD0000000
	1 6	Single Ended Cable - Shielded		10 m	-	MC0510MGD0000000
	X	5 Pin M12 Straight female network connector,		5 m	-	TC0505MGD0000000
	1	Single Ended Cable - Shielded		10 m	-	TC0510MGD0000000
Н	88	5 pin straight 7/8-16 UN male network connecto	r, Field Wireable	!	88161931	MA05F90000000000
F	00	T-connector 7/8-16 UN, 5 male / female / female pins, MINI 3 Way "T"		88161932	мс0500000МТ05000	
L1		Terminating resistor 7/8-16 UN female plug 1.	20 ohms		88161933	-
L2	· Ca	Terminating resistor 7/8-16 UN male plug 120 ohms		88161934	MA05TR0000000000	
	0	Terminating resistor M12 male plug		-	TA05TR0000000000	
		4 pin straight female cable connector 7/8", su	pply 24		230-1003	-
		4 pin elbow female cable connector 7/8", supp	oly 24 V		230-1001	-
J		4 pin elbow female cable connector 7/8" with 9.15 m supply 24 V DC	1 = brown 2 = v 3 = blue 4 = l		230-950	-
	X	7/8" MINI Straight 5 Pin Female Single Ended Ca	ıble,	5 m	-	MC0505MAG0000000
	11 6	Euro Color Code		10 m	-	MC0510MAG0000000
	X	7/8" MINI 90° 5 Pin Female Single Ended Cable,  Euro Color Code		5 m	-	MD0505MAG0000000
	11 0			10 m	-	MD0510MAG0000000

(K) Cable to be ordered separately.

## AVENTICS™ G3 Electronics and I/O

Series G3

MINI Cable Pin Out/Color Code

(Male View)

M12 Cable Pin Out/Color Code

(Male View)

(Male View)

(Male View)

(Male View)

Technical Data	Cable	T & TR	Field Wireable
Molded Body/Insert	PVC	PVC	Body = Glass Filled Polyamide
Coupling Nut	Nickel Plated Brass or Anodized Aluminum	Clear Anodized Aluminum	Black Anodized Aluminum
Cable Jacket Material	PVC	N/A	N/A
Cable O.D.	MINI = 8mm	N/A	5 – 13mm - One size fits all
Voltage Rating (Nominal)	150 Volts	T = 300 Volts	600 Volts
Current Rating	MINI = 4.0 Amps MR = 3.0 Amps	T = 8.0 Amps TR = NA	8.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP65 (mated)
Operating Temperature	-40 °C to 80 °C (-40 °F to 176 °F)	-40 °C to 105 °C (-40 °F to 221 °F)	-40 °C to 90 °C (-40 °F to 194 °F)
Conductor Gauge	22 AWG Power 24 AWG Signal	N/A	16 – 22 AWG
Bend Radius Minimum	Cable = 72mm	N/A	N/A
Wire Connection	NA	N/A	Screw Terminal


## Modbus® TCP/IP

Ethernet used throughout the world to network millions of PC's has now evolved into a viable industrial network. Ethernet is an open architecture high-level communication network that meets the demands of today's industrial applications requiring high-speed (10/100 Mbit/s), high-throughput and flexibility.

Additionally, Ethernet technology can integrate an on-board web server, which can make the node readily accessible for configuration, testing and even retrieval of technical documentation.

Aventics' G3 nodes for Modbus® TCP/IP have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.





Description	Replacement Part Number
Modbus® TCP/IP Communications Module (node)	240-292

#### **Technical Data**

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 V DC +/- 10%	0.0657 A
Valves & Discrete I/O	24 V DC +/- 10%	8 A maximum
Power Connector	Single key 4 pin 7/8" MINI type (male)	
Communication Connector	mmunication Connector D-coded 4 pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range (ambient)	-20°C to +50°C (Electronics only)
Humidity	95% relative humidity, non-condensing
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture Protection	IP65, IP67 (with appropriate assembly and termination)

Configuration Data		
Graphic Display	Display used for setting IP Address, Subnet mask, Fault/Idle Actions, DHCP / BootP and all other system settings.	
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure	
Maximum Valve-Solenoid Outputs	128 for Series 501, 80 for Series 502/503 and 32 for all other series	
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data			
Supported Baud Rates	10 Mbit / 100 Mbit		
Communication Connector D-coded 4 pin M12 type (female)			
Diagnostics Power, short, open load conditions and module health are monitored			
Special Features Integrated web server and fail-safe device settings, HTTP, FTP, and UNICAST (for EtherNet/IP™)			

Weight		
Modbus® TCP/IP Communications Module	255 g	

**EMERSON** 

### **Accessories for Modbus® TCP/IP**

Accessory	Description		Part Number (Europe)	Part Number (Americas)	
	M12 Straight 4 Pin Male D-Coded to Male RJ45 network		5m	QA0405MI	K0VA04000
8 4	Cable - Shielded		10m	QA0410MI	K0VA04000
	M12 Straight 4 Pin Male D-Coded Single Ende	d Cabla	5m	-	QA0405MK00000000
5	Witz Straight 4 Fill Male D-Coded Single Ender	u Cable	10m	-	QA0410MK00000000
	M12 Straight 4 Pip Male D. Coded Double Ende	d Cabla	5m	-	QA0405MK0QA04000
9 5	M12 Straight 4 Pin Male D-Coded Double Ende	d Cable	10m	-	QA0410MK0QA04000
	M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor 0.2m			-	QA04D2MK0VC04000
	M12 Straight 4 Pin Male D-Coded Field Wireable network Connector PG 9 Cable Gland – Screw Terminal			QA04F200	00000000
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland - IDC		-	QA04F2000000071N	
	RJ45 Field Wireable Connector PG 9 Cable Gland - IDC			-	VA08F2000000071N
	4 pin straight female cable connector 7/8", suply 24 V DC		230-1003	-	
6111	4 pin elbow female cable network connector 7/8" supply 24 V DC		230-1001	-	
	4 pin elbow female cable connector 7/8" with 9.15 m cable, suply 24 V DC  1 = brown 2 = white 3 = blue 4 = black		230-950	-	


## AVENTICS™ G3 Electronics and I/O

Series G3

M12 D-Coded Cable -Pin Out/Color Code

(Male View)





Technical Data	Cable	RJ45 Field Wireable	M12 Field Attachable
Molded Body/Insert	TPU, PA, PA66	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc or Brass	NA	Nickel Plated Brass
Cable Jacket Material	PUR or PVC	NA	NA
Cable O.D.	0.67 to 8.0mm	4.5 to 8.0mm	6.0 to 8.0mm
Voltage Rating (Nominal)	42 Volts	NA	60 Volts
Current Rating	1.5 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated)	IP20	IP 65 (mated)
Operating Temperature	-20 °C to 60 °C (-4 °F to 140 °F)	-20 °C to 70 °C (-4 °F to 158 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	26 & 24 AWG	26 – 22 AWG Solid/Stranded	Screw 24 – 18 AWG IDC 26 – 22 AWG
Bend Radius	40mm	NA	NA
Wire Connection	NA	IDC	IDC, Screw Terminal

### PROFIBUS™ DP

PROFIBUS™ DP is a vendor-independent, open fieldbus protocol designed for communication between automation control systems and distributed I/O at the device level.


Aventics' G3 nodes for PROFIBUS<sup>TM</sup> DP have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

The G3 PROFIBUS<sup>™</sup> DP nodes have been designed and tested to conform to the PROFIBUS<sup>™</sup> standard EN50170. Certification has been done by the PROFIBUS<sup>™</sup> Interface Center (PIC) according to the guidelines determined by the PROFIBUS<sup>™</sup> Trade Organization (PTO). The certification process ensures interoperability for all PROFIBUS<sup>™</sup> devices.

More information regarding PROFIBUS $^{\text{TM}}$  can be obtained from the following website: www.profibus.com

Description	Replacement Part Number
PROFIBUSTM DP Communications Module (node)	240-239





#### **Technical Data**

Electrical Data	Voltage	Current	
Node Power at Max. Brightness	24 V DC +/- 10%	0.0623 A	
Valves & Discrete I/O	24 V DC +/- 10%	8 A maximum	
Power Connector	Single key 5 pin 7/8" MINI type (male)		
Communication Connector	Single reverse key (B-Coded) 5 pin M12 type (1 male and 1 female)		
LEDs	Module Status and Network Status		

Operating Data			
Temperature Range (ambient)	-20°C to +50°C (Electronics only)		
Humidity	95% relative humidity, non-condensing		
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6		
Moisture Protection	IP65, IP67 (with appropriate assembly and termination)		

Configuration Data			
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, and all other system settings.		
ARM (Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total system failure			
Maximum Valve-Solenoid Outputs	128 for Series 501, 80 for Series 502/503 and 32 for all other series		
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs		

Network Data			
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, with Auto-Baud detection		
Communication Connector Single reverse key (B-Coded) 5 pin M12 type (1 male and 1 female)			
Diagnostics	Power, short, open load conditions and module health are monitored		
Special Features Supports Auto-Device Replacement (ADR) and fail-safe device settings			


Weight			
PROFIBUS <sup>™</sup> DP Communications Module	227 g		

#### PROFIBUS™ DP bus connection

The front panel of the communication module for Profibus-DP® is equipped with:

- a 5 pin male 7/8" socket for power supply
- a 5 pin male M12-B socket or 5 pin female M12-A socket for the bus cable (with a T-connector on integrated M12 COM-IN/COM-OUT connector)

#### **Fieldbus connection**



## **Accessories for PROFIBUS™ DP**

The modules on either side of the system must be provided with terminating resistors (H)


N°	Accessory	Description		Part Number (Europe)	Part Number (Americas)	
F		T-connector M12-B, 5 female / male / male pins (Profibus 12Mb max)			88100712	-
G	The second second	M12-B connector , 5 female pins (Profibus 12Mb max)	- for cable dia. 6 - 8 mm		88100713	RC05F200P0000000
		M12 Straight 5 Pin Female Rever	se Key Single Ended Cable	5m	-	RC0505MHP0000000
	3/	- Shielded		10m	-	RC0510MHP0000000
L		M12-B connector , 5 male pins - (Profibus 12Mb max)	for cable dia. 6 - 8 mm		88100714	RA05F200P0000000
	10	M12 Straight 5 Pin Female Rever	se Key Single Ended Cable	5m	-	RA0505MHP0000000
	0 1	- Shielded	, ,	10m	-	RA0510MHP0000000
		M12 Straight 5 Pin MALE TO FEMALE Reverse Key		5m	-	RC0505MHPRC05000
	0 5	EXTENSION CABLE		10m	-	RC0510MHPRC05000
Н		Terminating resistor M12-B - male plug		88100716	RA05TR0000000000	
		5 pin straight female cable conn	ector 7/8"		MC05F90000000000	-
		5 pin elbow female cable connector 7/8"		MD05F20000000000	-	
J	X	7/8" MINI Straight 5 Pin Female		5m	-	MC0505MAG0000000
	11 0	Single Ended Cable, Euro Color Code	male view	10m	-	MC0510MAG0000000
	X	7/8" MINI 90° 5 Pin Female	GNYE  S WH	5m	-	MD0505MAG0000000
	11 0	ingle Ended Cable, uro Color Code		10m	MD0510M	AG000000
		Dust cover - M12 female		88157773	-	

(K) Cable to be ordered separately.

M12 Reverse Key B-Coded Cable -Pin Out/Color Code

(Male View)





Technical Data	Cable	RJ45 Field Attachable	M12 Field Attachable
Molded Body/Insert	TPU	TR = TPU	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc or Brass	Nickel Plated Brass
Cable Jacket Material	PUR	N/A	N/A
Cable O.D.	7.4 mm	N/A	8.5 mm Max.
Voltage Rating (Nominal)	250 Volts	60 Volts	60 Volts
Current Rating	4.0 Amps	4.0 Amps	4.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP 65 (mated)
Operating Temperature	-20 °C to 80 °C (-4 °F to 176 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	24 AWG	N/A	18 AWG Maximum
Bend Radius	Cable = 78mm	N/A	N/A
Wire Connection	N/A	N/A	Screw Terminal

## **PROFINET**<sup>TM</sup>

PROFINET<sup>™</sup> is the innovative open standard for Industrial Ethernet, development by Siemens and the PROFIBUS® User Organization (PNO). PROFINET<sup>™</sup> complies to IEC 61158 and IEC 61784 standards. PROFINET<sup>™</sup> products are certified by the PNO user organization, guaranteeing worldwide compatibility.


Aventics' G3 nodes for PROFINET™ IO (PROFINET™ RT) have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

PROFINET™ is based on Ethernet and uses TCP/IP and IT standards and complements them with specific protocols and mechanisms to achieve a good Real Time performance.

More information regarding PROFINET™ can be obtained from the following website: www.profinet.com

Description	Replacement Part Number
PROFINET® Communications Module (node)	240-240





#### **Technical Data**

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 V DC +/- 10%	0.0903 A
Valves & Discrete I/O	24 V DC +/- 10%	8 A maximum
Power Connector	Single key 5 pin 7/8" MINI type (male)	
Communication Connector	Two D-coded 4 pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

	Operating Data	
Temperature Range (ambient)	Temperature Range (ambient) -20°C to +50°C (Electronics only)	
Humidity	95% relative humidity, non-condensing	
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6	
Moisture Protection	IP65, IP67 (with appropriate assembly and termination)	

Configuration Data	
Graphic Display	Display used for setting IP Address, Subnet Mask, Fault/Idle Actions, and all other system settings.
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure.
Maximum Valve-Solenoid Outputs	128 for Series 501, 80 for Series 502/503 and 32 for all other series
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data		
Supported Baud Rates	Supported Baud Rates 10 Mbit / 100 Mbit	
Communication Connector	Two D-coded 4 pin M12 type (2-Female)	
Diagnostics	Power, short, open load conditions and module health and configuration are monitored	
Special Features	Integrated web server, Integrated 2 port switch and fail-safe device settings, and FSU	


	Weight
PROFINET™ Communications Module	227 g

**EMERSON** 

### **Accessories for PROFINET™**

Accessory	Description			Part Number (Europe)	Part Number (Americas)
	MA2 Secretaria A Bir Mala D. Godard	M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable - Shielded		QA0405MK0VA04000	QA0405MR0VA04000
00	M12 Straight 4 Pin Maie D-Coded	to Male RJ45 Cable - Shleided	10m	QA0410MK0VA04000	QA0410MR0VA04000
	M42 Chroimht 4 Din Mala D. Cadad	Cincula Fundad Cabla	5m	-	QA0405MR00000000
S A	M12 Straight 4 Pin Male D-Coded	Single Ended Cable	10m	-	QA0410MR00000000
1)	MA2 Straight A Big Mala D Godad	Double Forded Cobbs	5m	-	QA0405MR0QA04000
55	M12 Straight 4 Pin Male D-Coded	Double Ended Cable	10m	-	QA0410MR0QA04000
83	M12 Straight 4 Pin Male D-Coded Convertor	to RJ45 Female Socket	0.2m	-	QA04D2MK0VC04000
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland – Screw Terminal		QA04F200	00000000	
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland - IDC		-	QA04F200R000071N	
	5 pin straight female Field Wireab	5 pin straight female Field Wireable cable connector 7/8"		MC05F90000000000	-
	5 pin elbow female Field Wireable	5 pin elbow female Field Wireable cable connector 7/8"		MD05F20000000000	-
	RJ45 Field Wireable Connector PG 9 Cable Gland		-	VA08F200R000071N	
X	7/8" MINI Straight 5 Pin Female S	ingle Ended Cable,	5m	-	MC0505MAG0000000
11 0	Euro Color Code		10m	-	MC0510MAG0000000
X	7/8" MINI 90° 5 Pin Female Single	male view	5m	-	MD0505MAG0000000
11 0	Ended Cable, Euro Color Code	5 SNTE	10m	MD0510M	AG000000


### Server web page



M12 D-Coded Cable -Pin Out/Color Code

(Male View)





Technical Data	Cable	RJ45 Field Attachable	M12 Field Attachable
Molded Body/Insert	TPU	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc	N/A	Nickel Plated Brass
Cable Jacket Material	PVC	N/A	N/A
Cable O.D.	6.5 to 7.4mm	Accepts 4.5 to 8.0mm	Accepts 6.0 to 8mm
Voltage Rating (Nominal)	250 Volts	N/A	60 Volts
Current Rating	4.0 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated), RJ45 – IP20	IP20	IP 65 (mated)
Operating Temperature	-25 °C to 60 °C (-13 °F to 140 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	22 & 24 AWG	22 AWG Solid/Stranded	Screw 24-18 AWG IDC 26-22 AWG
Bend Radius Minimum	19.5mm (fixed) 45.5mm (Flexible)	N/A	N/A
Wire Connection	N/A	IDC	Screw Terminal, IDC

#### **Ethernet POWERLINK®**

Ethernet POWERLINK® is a open fieldbus protocol designed by B&R for communication between automation control systems and distributed I/O at the device level.


Aventics' G3 Ethernet POWERLINK® nodes have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

The G3 Ethernet POWERLINK® nodes have been designed and tested to conform to the Ethernet POWERLINK® specifications available at EPSG group (Ethernet Powerlink® Standardization Group). The certification process ensures interoperability for all Ethernet POWERLINK® devices and compatibility with B&R systems.

More information regarding Ethernet POWERLINK® can be obtained from the following website: www.ethernet-powerlink.org

Description	Replacement Part Number
Ethernet POWERLINK® Communications Module (node)	240-309





# Pin 1 = 0 V DC (valves & outputs) Pin 2 = 0 V DC (node & inputs) Pin 3 = Earth Ground Pin 4 = +24 V DC (node & inputs)

#### Pin 4 = +24 V DC (node & inputs) Pin 5 = +24V DC (valves & outputs)

#### **Technical Data**

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 V DC +/- 10%	0.0955 A
Valves & Discrete I/O	24 V DC +/- 10%	8 A maximum
Power Connector	Single key 5 pin 7/8" MINI type (male)	
Communication Connector	Two D-coded 4 pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range (ambient) -20°C to +50°C (Electronics only)	
Humidity	95% relative humidity, non-condensing
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture Protection	IP65_IP67 (with appropriate assembly and termination)

Configuration Data		
Graphic Display Display used for setting Node Address, Baud Rate, Fault/Idle Actions, and all other system settings.		
ARM (Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure		
Maximum Valve-Solenoid Outputs 128 for Series 501, 80 for Series 502/503 and 32 for all other series		
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data				
Supported Baud Rates 10 Mbit/100 Mbit				
Communication Connector Two D-coded 4 pin M12 type (female)				
Diagnostics Power, short, open load conditions and module health are monitored				
Special Features Integrated web server, Integrated 2 port switch and fail-safe device settings				

Weight			
Ethernet POWERLINK® Communications Module	227 g		

**EMERSON** 

### **Accessories for Ethernet POWERLINK®**

Accessory	Description			Part Number (Europe)	Part Number (Americas)
	M12 Straight 4 Din Mala D Coded to	Mala BIAE Cabla Shioldad	5m	QA0405MK0VA04000	QA0405MS0VA04000
<b>S</b>	M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable - Shielded  10m			QA0410MK0VA04000	QA0410MS0VA04000
1)	M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable - Shielded			-	QA0405MS0QA04000
55	Witz Straight 41 in Male D Coded to	ividic 1945 Cable - Siliciaca	10m	-	QA0410MS0QA04000
8	M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor 0.2m			-	QA04D2MK0VC04000
M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland – Screw Terminal				QA04F200	00000000
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland - IDC			-	QA04F200R000071N
	5 pin straight female Field Wireable cable connector 7/8"			MC05F90000000000	-
	5 pin elbow female Field Wireable cable connector 7/8"			MD05F20000000000	-
	RJ45 Field Wireable Connector			-	VA08F200R000071N
X	7/8" MINI Straight 5 Pin Female	raignt 5 Pin Female d a Cable, male view —	5m	-	MC0505MAG0000000
11 6	Single Ended Cable, Euro Color Code		10m	-	MC0510MAG0000000
×	7/8" MINI 90° 5 Pin Female Single	4	5m	-	MD0505MAG0000000
11 0	Ended Cable, Euro Color Code			MD0510M	AG000000

## Server web page


Module	Part No.	Description		Details					Activ	vity 🔍
Node	240-181	EtherNet Communications Module		Sho	w Details			Close all D	etails	✓
Valve Driver	219-828	Valve Driver Output Module		Sho	w Details			Close all D	etails	1
ARM	240-182	Auto Recovery Module		Sho	w Details			Close all Details		✓
No. 1	240-207	16 Outputs PNP Digital M12 x 8		Show Details			Close all Details		✓	
No. 2	240-211	8 Inputs / 8 Outputs PNP Digital M12 x 8		Show Details				Close all Details		
No. 3	240-241	Sub-Bus Valve Driver		Show Details				Close all Details		
No. 4	240-205	16 Inputs PNP Digital M12 x 8		✓ Sho	w Detail	ls ld		Close all D	etails	- !
Firmware Re	vision:	2.021		_		_				
i	9	PNP Inputs:	0 0	0 1	2	3	<b>4</b>	8 5	6	0 7
	0!	I/O Mapping Input (Starting) Byte: 15	8	9	0 10	o 11	O 12	<u>13</u>	O 14	15
1 0	0	Short Circuit on Connector: I/O Mapping Diagnostics (Starting) Byte: 17	- A	В	• c	o D	○ E	0 F	G	Он


#### M12 D-Coded Cable & RJ45 Pin Out/Color Code

(Male View)










Technical Data	Cable	RJ45 Field Attachable	M12 Field Attachable
Molded Body/Insert	N/A	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc or Brass	N/A	Nickel Plated Brass
Cable Jacket Material	PUR	N/A	N/A
Cable O.D.	6.5mm	Accepts 4.5 to 8.0mm	Accepts 6.0 to 8mm
Voltage Rating (Nominal)	N/A	N/A	60 Volts
Current Rating	N/A	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated), RJ45 – IP20	IP20	IP 65 (mated)
Operating Temperature	-25 °C to 60 °C (-13 °F to 140 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	22 AWG	22 AWG Solid/Stranded	Screw 24 – 18 AWG IDC 26-22 AWG
Bend Radius Minimum	45.5mm	N/A	N/A
Wire Connection	N/A	IDC	Screw Terminal, IDC


## **CANopen®**

CANopen® is an open protocol based on Controller Area Network (CAN). It was designed for motion oriented machine control networks but has migrated to various industrial applications. CAN in Automation (CIA) is the international users' and manufacturers' organization that develops and supports CAN-based protocols. Aventics' G3 CANopen® nodes have an integrated graphic display and are capable of addressing combinations of up to 256 outputs and 256 inputs.

More information regarding this organization can be found at: www.can-cia.org







#### **Technical Data**

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 V DC +/- 10%	0.0404 A
BUS Power	11-25 V DC	0.025 A
Valves & Discrete I/O	24 V DC +/- 10%	8 A maximum
Power Connector	Single key 4 pin 7/8" MINI type (male)	
Communication Connector	unication Connector Single key 5 pin 7/8" MINI type (male)	
LEDs	Module Status and Network Status	

Operating Data				
Temperature Range (ambient) -20°C to +50°C (Electronics only)				
Humidity	95% relative humidity, non-condensing			
Vibration / Shock IEC 60068-2-27, IEC 60068-2-6				
Moisture Protection IP65, IP67 (with appropriate assembly and termination)				

Configuration Data					
Graphic Display					
ARM (Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total of system failure.					
Maximum Valve-Solenoid Outputs	32 for all series				
Maximum Addressable I/O Points	Various combinations of 256 outputs and 256 inputs				

Network Data					
Supported Baud Rates 125K Baud, 250K Baud, 500K Baud, 1M Baud					
Communication Connector Single key 5 pin 7/8" MINI type (male)					
Diagnostics Power, short, open load conditions and module health are monitored and fail-safe device settings					

	Weight
CANopen® Communications Module	252 g

### **CANopen®** bus connection

The front panel of the communication module for CANopen® is equipped with:

- a 4 pin male 7/8" socket for power supply a 5 pin male 7/8" socket for the bus cable (E)


The bus can be connected in the two following ways:

- directly to the module with a T-connector,
- with a straight connector, cable (max. length: 3 m) and a DeviceNet distributor box.

The modules on either side of the system must be provided with terminating resistors (L1 or L2).

#### Wiring with T-connector

#### **Connection with distributor box**



## **Accessories for CANopen®**


The modules on either side of the system must be provided with terminating resistors (H)

	Accessory	Description		Part Number (Europe)	Part Number (Americas)
G	100	5 pin straight 7/8-16 UN female network connector, Field Wireable	aight 7/8-16 UN female network connector, reable		MC05F90000000000
	×	5 pin straight 7/8-16 UN female network connector,		-	MC0505MGD0000000
	1 6	Single Ended Cable - Shielded	10m	-	MC0510MGD0000000
	×	5 Pin M12 Straight female network connector, Single Ended	5m	-	TC0505MGD0000000
	1	Cable - Shielded	10m	-	TC0510MGD0000000
н		5 pin straight 7/8-16 UN male network connector, Field Wire	able	88161931	MA05F90000000000
F		T-connector 7/8-16 UN, 5 male / female / female pins, MINI 3 Way "T"	88161932	MC0500000MT05000	
L1		Terminating resistor 7/8-16 UN female plug 120 ohms	88161933	-	
L2	6	Terminating resistor 7/8-16 UN male plug 120 ohms	88161934	MA05TR0000000000	
	1	Terminating resistor M12 male plug		-	TA05TR0000000000
		4 pin straight female cable connector 7/8", supply 24		230-1003	-
	611	4 pin elbow female cable connector 7/8", supply 24 V		230-1001	-
J		4 pin elbow female cable connector 7/8" with 9.15 m supply 24 V DC		230-950	-

(K) Cable to be ordered separately.

## AVENTICS™ G3 Electronics and I/O

**Series** G3



Technical Data	Cable	T & TR	Field Wireable
Molded Body/Insert	PVC	PVC	Body = Glass Filled Polyamide
Coupling Nut	Nickel Plated Brass or Anodized Aluminum	Clear Anodized Aluminum	Black Anodized Aluminum
Cable Jacket Material	PVC	N/A	N/A
Cable O.D.	MINI = 8mm	N/A	5 – 13mm - One size fits all
Voltage Rating (Nominal)	150 Volts	T = 300 Volts	600 Volts
Current Rating	MINI = 4.0 Amps MR = 3.0 Amps	T = 8.0 Amps TR = NA	8.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP65 (mated)
Operating Temperature	-40 °C to 80 °C (-40 °F to 176 °F)	-40 °C to 105 °C (-40 °F to 221 °F)	-40 °C to 90 °C (-40 °F to 194 °F)
Conductor Gauge	22 AWG Power 24 AWG Signal	N/A	16 – 22 AWG
Bend Radius Minimum	Cable = 72mm	N/A	N/A
Wire Connection	NA	N/A	Screw Terminal

## **EtherNet/IP™ DLR**

EtherNet/IP™ is an open architecture high-level communication network that meets the demands of today's industrial applications requiring high-speed (10/100 Mbit/s), high-throughput and flexibility.


Capable of addressing up to 1200 outputs and 1200 inputs, Aventics' G3 EtherNet/IP™ DLR (Device Level Ring) node with integrated display has an embedded switch which allows the unit to be used in simplified networks with linear topology configurations (daisy chain). This technology alleviates the need for an external Ethernet switch device in a single subnet configuration. Additionally, the DLR compatibility allows the node to be used in a fault tolerant "ring" network, when using appropriate EtherNet/IP™ DLR scanners. DLR configuration allows communication recovery from a single point failure on the network ring (e.g. failed network connection or cable).

The G3 EtherNet/IP™ nodes have been tested and approved for conformance by the ODVA.

More information about Ethernet/IP™ and the ODVA can be obtained from the following website: www.odva.org.

Description	Replacement Part Number
EtherNet/IP™ DLR Communications Module (node)	240-325





#### **Technical Data**

Electrical Data	Voltage	Current	
Node Power at Max. Brightness	24 V DC +/- 10%	0.0953 A	
Valves and Discrete I/O	24 V DC +/- 10%	8 A Maximum	
Power Connector	Single key 4 pin 7/8" MINI type (male)		
Communication Connector	Two D-coded 4 pin M12 type (female)		
LEDs	Module Status, Network Status and Activity / Link		
	Operating Data		
Temperature Range	-20°C to +50°C (Electronics only)		
Humidity	95% relative humidity, non-condensing		
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6		
Moisture	loisture IP65, IP67 (with appropriate assembly and termination)		
	Configuration Data		
Graphic Display Display used for setting IP address, Subnet Mask, Fault/Idle Actions, and all other system settings			
ARM (Auto Recovery Module) Optional module that contains automatic recovery of system settings in the event of total or partial system failure			
laximum Valve Solenoid Outputs 128 for Series 501, 80 for Series 502/503 and 32 for all other series			
Maximum Sub-Bus I/O Points	aximum Sub-Bus I/O Points Various combinations of 1200 outputs and 1200 inputs		
	Network Data		
Supported Baud Rates	10 Mbit / 100 Mbit		
Communication Connector	Two D-coded 4 pin M12 type (female)		
Diagnostics	Power, short, open load conditions and module health and	d configuration are monitored	
Special Features	Embedded two port switch, Device Level Ring (DLR) compatibility, Linear network topology, QuickConnect™ capability, fail-safe device settings, integrated web server, HTTP, TFTP, UNICAST		
Weight			

EtherNet/IP™ DLR Communications module

227 g


### **Accessories for EtherNet/IP™ DLR**

Accessory	Description		Part Number (Europe)	Part Number (Americas)
1)	M12 Straight 4 Pin Male D-Coded to Male RJ45 network Cable		QA0405MI	K0VA04000
5 6	- Shielded	10m	QA0410MI	K0VA04000
	M12 Straight 4 Pin Male D-Coded Single Ended Cable	5m	-	QA0405MK00000000
O A		10m	-	QA0410MK00000000
	M12 Straight 4 Pin Male D-Coded Double Ended Cable	5m	-	QA0405MK0QA04000
<b>9</b>		10m	-	QA0410MK0QA04000
1	M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor	0.2m	-	QA04D2MK0VC04000
	M12 Straight 4 Pin Male D-Coded Field Wireable network Connector		QA04F200	00000000
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland - IDC	-	QA04F2000000071N	
	RJ45 Field Wireable Connector PG 9 Cable Gland - IDC	-	VA08F2000000071N	
100	4 pin straight female cable connector 7/8", suply 24 V DC		230-1003	-
	4 pin elbow female cable connector 7/8", suply 24 V DC		230-1001	-
10	4 pin elbow female cable connector 7/8" with 9.15 m cable, suply 24 V DC  1		230-950	-

M12 D-Coded Cable -Pin Out/Color Code

(Male View)





Technical Data	Cable	RJ45 Field Wireable	M12 Field Attachable
Molded Body/Insert	TPU, PA, PA66	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc or Brass	NA	Nickel Plated Brass
Cable Jacket Material	PUR or PVC	NA	NA
Cable O.D.	0.67 to 8.0mm	4.5 to 8.0mm	6.0 to 8.0mm
Voltage Rating (Nominal)	42 Volts	NA	60 Volts
Current Rating	1.5 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated)	IP20	IP 65 (mated)
Operating Temperature	-20 °C to 60 °C (-4 °F to 140 °F)	-20 °C to 70 °C (-4 °F to 158 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	26 & 24 AWG	26 – 22 AWG Solid/Stranded	Screw 24 – 18 AWG IDC 26 – 22 AWG
Bend Radius	40mm	NA	NA
Wire Connection	NA	IDC	IDC, Screw Terminal

### **EtherCAT®**

EtherCAT® is an open ethernet based fieldbus protocol developed by Beckhoff. EtherCAT® sets new standards for real-time performance and topology flexibility with short data update/cycle times and low communication jitter.


Aventics' G3 EtherCAT® node has an integrated graphic display for simplified commissioning and diagnostics. It is capable of addressing combinations of up to 1200 outputs and 1200 inputs.

The G3 nodes for EtherCAT® have been designed and tested to conform with EtherCAT® specifications set forth by the ETG.

More information regarding EtherCAT® can be obtained from the following website: www.ethercat.org.

Description	Replacement Part Number
EtherCAT® Communications Module (node)	240-310





#### **Technical Data**

Electrical Data	Voltage	Current	
Node Power at Max. Brightness	24 V DC +/- 10%	0.073 A	
Valves and Discrete I/O	24 V DC +/- 10% 8 A Maximum		
Power Connector	Single key 5 pin 7/8" MINI type (male)		
Communication Connector	Two D-coded 4 pin M12 type (female)		
LEDs	Module Status, Network Status and Activity /Link		
Outputing Date			

Operating Data		
Temperature Range	-20°C to +50°C (Electronics only)	
Humidity 95% relative humidity, non-condensing		
Vibration / Shock IEC 60068-2-27, IEC 60068-2-6		
Moisture IP65, IP67 (with appropriate assembly and termination)		

Configuration Data		
Graphic Display	Display used for setting IP address, Subnet Mask, Fault/Idle Actions, and all other system settings	
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system settings in the event of total or partial system failure	
Maximum Valve Solenoid Outputs	128 for Series 501, 80 for Series 502/503 and 32 for all other series	
Maximum Sub-Bus I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data		
Supported Baud Rates	10 Mbit / 100 Mbit	
Communication Connector	Two D-coded 4 pin M12 type (female)	
Diagnostics	Power, short, open load conditions and module health and configuration are monitored.	
Special Features Integrated web server, fail-safe device settings		

	Weight
EtherCAT® Communications module	227 g

### **Accessories for EtherCAT®**

Accessory	Description		Part Number (Europe)	Part Number (Americas)
	M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable -		QA0405MK0VA04000	QA0405MT0VA04000
00	Shielded supply 24 V DC	10m	QA0410MK0VA04000	QA0410MT0VA04000
1)	M12 Straight 4 Pin Male D-Coded Single Ended Cable	5m	-	QA0405MT00000000
O A	1112 Straight 41 III Male D Coaca Single Enaca casic	10m	-	QA0410MT00000000
	M12 Straight 4 Pin Male D-Coded Double Ended Cable	5m	-	QA0405MT0QA04000
<b>S</b>		10m	-	QA0410MT0QA04000
03	M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor	0.2m	-	QA04D2MK0VC04000
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland – Screw Terminal	QA04F200	00000000	
	M12 Straight 4 Pin Male D-Coded Field Wireable Connector PG 9 Cable Gland - IDC		-	QA04F200R000071N
	RJ45 Field Wireable Connector PG 9 Cable Gland - IDC		-	VA08F200R000071N
100	5 pin straight female cable connector 7/8", supply 24 V DC	MC05F90000000000	-	
	5 pin elbow female cable connector 7/8", supply 24 V DC		MD05F20000000000	-
X	7/8" MINI Straight 5 Pin Female Single Ended Cable,	5m	-	MC0505MAG0000000
11 6	Euro Color Code male view 1 BK	10m	-	MC0510MAG0000000
X	7/8" MINI 90° 5 Pin Female Single		-	MD0505MAG0000000
11 0	Ended Cable, Euro Color Code	10m	MD0510M	AG000000


## AVENTICS™ G3 Electronics and I/O

**Series** G3

M12 D-Coded Cable -Pin Out/Color Code

(Male View)





Technical Data	Cable	RJ45 Field Wireable	M12 Field Attachable
Molded Body/Insert	TPU/PE	Housing = PA Carrier = PC	Nickel Plated Zinc/PA 66
Coupling Nut	Nickel Plated Zinc	NA	Nickel Plated Brass
Cable Jacket Material	PVC	NA	NA
Cable O.D.	6.5mm	Accepts 4.5 to 8.0mm	Accepts 4.0 to 8mm
Voltage Rating (Nominal)	250 Volts	NA	60 Volts
Current Rating	4.0 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated), RJ45 – IP20	IP20	IP 65 (mated)
Operating Temperature	-40 °C to 70 °C (-40 °F to 158 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	22 & 24 AWG	22 AWG Solid/Stranded	Screw 24 – 18 AWG IDC 26 – 22 AWG
Bend Radius Minimum	19.5mm (fixed) 45.5mm (Flexible)	NA	NA
Wire Connection	NA	IDC	Screw Terminal, IDC

#### I/O Modules M12

with short circuit protection integrated Digital I/O 5-pin M12 Modules

	Description	Pa	art Numb	er
	Signal Type	PNP	NPN	NAMUR
	16 Inputs	240-205	240-209	-
Inputs	16 Inputs 19 Pin M23 ( <b>Fig. B Only</b> )	240-323	-	-
	8 Inputs ( <b>Ex ia</b> )	-	-	240-320
	16 Outputs PNP	240-207	-	-
Outputs	8 Outputs PNP high current (1A) ( <b>Fig. A Only</b> )	240-300	-	-
Inputs & Outputs	8 Inputs & 8 Outputs	240-211	-	-



ia (Namur) input module

# **Analog I/O (16 bit resolution)** 5-pin M12 Modules

	Description	Part Number	
	Signal Type	0-10 V DC	4-20 mA
A 1 1/0	4 Inputs	240-212	240-214
Analog I/O	2 Inputs & 2 Outputs	240-213	240-215
Analog I/O for proportional valves (Sentronic <sup>PLUS</sup> )	2 Inputs & 2 Outputs 4 Inputs & 4 Outputs	240-307 -	- 240-363



# **Digital Inputs -Terminal Strip Modules** with short circuit protection integrated

Digital Inputs -Terminal Strip Modules

	Description Part Number		umber
	Signal Type	PNP	NAMUR
	16 Inputs	240-203	-
Inputs	8 Inputs ( <b>Ex ia</b> )	-	240-322
Outputs	16 Outputs	240-330	-





ia (Namur) input module

#### **Technical Data**

Operating Data	5-pin M12 Modules	Terminal Strip Modules
Temperature Range (ambient)	-20°C to +50°C (Electronics only)	
Humidity	95% relative humidity, non-condensing	
Vibration / Shock	IEC 60068-2-27, IEC 60068-2-6	
Wire Range	-	12 to 24 AWG
Strip Length	-	7 mm
Tightening Torque	-	0.5 Nm
Ingress Protection	IP65, IP67 (with appropriate assembly and termination)	IP20


Weight		
M12 Module - Analog	244 g	
M12 Module - Digital	274 g	
M12 Module - High Current Outputs	264 g	
M23 Module	343 g	
Terminal Strip Module	292 g	

Electrical data	Namur Ex ia Module
Voltage	24 VDC Module Supply Sensor Supply = 8.2 VDC Nominal
Input Type  NC (Normally Closed)	NAMUR Signal Current (0) $\geq$ 2.1 mA Signal Current (1) $\leq$ 1.2 mA Short Circuit Monitoring $<$ 100 $\Omega$ Open/Broken Wire Detection $<$ 0.05 mA
Safety Parameter Output Maximums	$Uo \le 9.6 \text{ V}$ $Io \le 13 \text{ mA}$ $Po \le 31 \text{ mW}$
Diagnostics	Open (broken wire) and Short Circuit
Certification	
Module Marking (ATEX)	
I/O Connector	M12 4 Pin Female (Compatible with 5 Pin)
	Terminal Strip
Weight	284 g
Operating Data	
Temperature Range	-20°C to +50°C (Electronics only)
Humidity	95% relative humidity; non-condensing
Ingress Protection	IP65 (with appropriate assembly and terminations)

### I/O Modules

## Digital I/O 3 Pin M8 Sub-bus Module

Description	Part Number	
Inputs		
8 PNP Inputs	240-379	




#### **Technical Data**

Operating Data		
Temperature Range (ambient)	-23°C to 50°C	
Humidity	95% relative humidity, non-condensing	
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6	
Ingress Protection	IP67 (with appropriate assembly and termination)	
Connector	M8 3 Pin Female	
Special Features	Linear topology and internally powered through Sub-bus connection	
M12 Terminating Resistor (required on last M8 Module)	TA05TR0000000000	



Weight		
Sub-bus Module		204 g



#### I/O Modules M12


RTD temperature sensor input module Analog I/O (16 bit resolution) 5-pin M12 Modules

	Description	Part Number
Analog I/O	4 Inputs	240-311

Operating Data	RTD temperature sensor input module	
Temperature range (ambient)	-20° to +50° C	
Humidity	95% relative humid	ity, non-condensing
Vibration / Shock	IEC 60068-2-27	, IEC 60068-2-6
Sensor type of input	Pt100 - Pt200 - Pt500 - Pt1000	Ni100 - Ni120 - Ni500 - Ni1000
Sensor connection technology		with compensation tion cable)
Temperature range of input signal	-200°C to +850°C	
Minimum temperature scale	25℃	
Moisture protection	IP65, IP67 with appropriate assembly and termination	
Absolute accuracy at +25°C	0.03% (linearity / repeatability / hysteresis / stability)	
Temperature error relatives to input range	+/- 0.05%	
ATEX certification	compatible to zone 2-22 and sensor installed in zone 2-22	
Standard	DIN/IEC 60751, IEC 751, DIN 43710	
Module weight	247 g	



#### Wiring diagrams



- 4 Wire Sensor Type 4 Wire Cable (Fig.4)
- . For maximum accuracy on a 3 wire sensor type make identified jumper connections at the sensor end (see Fig.3). Cable resistance, resulting from cable length, affects mesuring error; therefore use cables that are as short as possible.
  - . For long cable runs and high accuracy use 4 wire sensor types.

#### **IO-Link Master**

Multiple masters can be incorporated into one valve system, can be distributed via Sub-bus up to 30 meters, and can support standard IO-Link smart sensors.

Description	Replacement Part Number
8 Port Class A IO-Link Master	240-381

Supports 580 IO-Link for Series 500 valve systems, Series AV and ES05 valve systems with IO-Link, Sentronic proportional valves with IO-Link, AF2 Flow Sensors with IO-Link, and other IO-Link smart sensors



#### **Wiring Diagram**



Pin 1= +24VDC (UNSW) Pin 2= Digital Input / Digital Output
Pin 3= 0VDC (UNSW)
Pin 4= IO-Link / Digital Input /
Digital Output

#### **Technical Data**

Operating Data						
Supported Protocols	Ethernet/IP DLR and PROFINET					
Input Type	Class A					
Supported Sensor Type IO-Link and Digital						
Temperature Range (ambient) -23 °C to 50 °C (-10 °F to 122 °F)						
Humidity	95% relative humidity, non-condensing					
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6					
Ingress Protection	IP65 (with appropriate assembly and termination)					
Connector	M12 5 Pin Female, SPEEDCON®					
Data Format	Mapped & Event Diagnostics					
Consist Factories	Up to 16 IO-Link Class A master modules per communication module					
Special Features	Supports IO-Link Class B solutions with optional T-adapter R412028657					

Weight					
Class A IO-Link Master	278g / 9.8 oz				

NOTE: For IO-Link communication cables see the 580 Series IO-Link Communication Class A & B Cables and Connectors section and for power cables see the 580 Series Power Cables and Connectors section.

## **I/O Module Accessories**


Accessory	Description	Part Number (Europe)	Part Number (Americas)			
5	M12 Straight 4 Pin Male Field Wireable Connector, IDC Connection - PG 9 Cable Gland w/ SPEEDCON® connector technology	-	TA04F2000000081E			
	5 pin straight male M12 connector		88100330	-		
60	M12 Straight 4 Pin Male Field Wireable Connector, Screw Terminal - PG 7 C	-	TA04F10000000000			
600	M12 Straight 4 Pin Male Field Wireable Connector, Screw Terminal - PG 9 C	-	TA04F20000000000			
	5 pin elbow male M12 connector		88161927	-		
	M12 Straight 4 Pin Male Field Wireable Connector, Screw Terminal - PG 7 Cable Gland		-	TB04F10000000000		
	M12 Straight 4 Pin Male Field Wireable Connector, Screw Terminal - PG 9 Cable Gland		-	TB04F20000000000		
	Dust Cover - M12 Male		230	-647		
	5 pin male DUO M12 connector for 2 inputs (2 cables, Ø3-5 mm)		88100253	-		
	M12 to M12 "Y" Splitter, 21mm Spacing	-	TA0500000JC05000			
	M12 to M8 "Y" Splitter		- ТАО400000КСОЗ			
	4 3	1.5 m	TA04E5MIE000071P			
4/	M12 SPEEDCON connector Straight 4 Pin Male Single Ended Cable, Euro Color Code	3 m	TA0403MIE000071P			
1	1 <b>B</b> N	5 m	TA0405M1	E000071P		
1	M12 SPEEDCON connector 90° 4 Pin Male Single	1.5 m		E000071P		
y /	Ended Cable, Euro Color Code	3 m	TB0403MIE000071P			
		5 m	TB0405M			
	M12 Straight 4 Pin Male to Female Cable Extension	1.5 m	TC04E5MIETA0471P			
0 4		3 m	TC0403M1	ETA0471P		
1		1.5 m	TC03E5M1	EPA0371P		
	M12 Straight 3 Pin Male to M8 3 Pin Straight Female Extension	3 m	TC0303M1	EPA0371P		
1	MO 2 Din Straight Mala to MO 2 Din Straight Formula Futurais	1.5 m	PC03E5M1	EPA0371P		
0	M8 3 Pin Straight Male to M8 3 Pin Straight Female Extension	3 m	PC0303M1	EPA0371P		
	Paralle and the Tamping Labels	I/O 0-7	140-	1073		
ALC:	Replacement Terminal strip	I/O 8-15	140-	1074		
-	Keying Element for terminal strip		140-	1076		
-	Keying Element for Module		140-	1077		
00	IO-Link Class A to Class B T-connector		R4120	28657		

## **Backplane extension modules and Accessories**

N°*	Accessories		Descr	iption		Weight	Part Number		
			Backplane Ext	ension Modules					
	N. S.		•						
					with I/O	235 g	240-241		
1	120	Distributed Valve Module	Distributed module f display	or valves with	w/o I/O, w/o clips (500 Series only)	320 g	P580AEDS4010A00		
	S OF THE ST		w/o I/O, with DIN Rail Clips (500 Series only)	332 g	P580AEDS4010DRM				
	-	G3 Backplane	G3 Left End Module for backplane		with DIN Rail Clips	141 g	240-244		
2	1. 9	extension Left End Module	distribution and 24VDC to		W/o clips	130 g	240-183		
			I/O modules	for Ex ia Namur	W/o clips	-	240-318		
	- 10 m	G3 Backplane	G3 Right Module allowing the		with DIN Rail Clips	141 g	240-246		
3		extension	connection of		W/o clips	130 g	240-185		
		Right Module	distributed I/O modules	for Ex ia Namur	W/o clips	-	240-319		
			Miscellane	ous Modules					
4		Auto Recovery	Protects configuration information during a critical failure. Allows		ARM Module	131 g/	240-383		
4		Module (ARM)	configuration inform saved and reloaded t module automatically	o replacement	Wireless ARM Module	4.6 oz	240-382		
6		G3 Left Terminator	Must be installed after the last I/O module or after the		with DIN Rail Clips	102 g	240-245		
	60 to	Module communication module no I/O modules installed			W/o clips	91 g	240-184		
			Provides nelectrical		-	45 g	240-179		
7	3	Jumper Clip	connections between modules	jumper clip for Namur input	-	-	240-317		
							serie 500		
					with DIN Rail Clips	227 g	P599AE508827002		
_	100	Valve Driver	G3 electrical interface	a to pneumatics	W/o clips	216 g	P599AE508827001		
8		Module	ends and valves	e to priedifiatics			serie 2000		
					with DIN Rail Clips	147 g	219-858		
	•				W/o clips	136 g	219-828		
		Right Hand			with DIN Rail Clips	- 130 g	240-289		
-	-32	Mounting Cover	Used when a commu is used without local		W/o clips	-	240-255		
-		Hub	4 Branches		-	-	340-326		
Accessories									
	(o manninam)								
		Labels	For use with Murrpla	stik <sup>©</sup> Type 20 Soft	ware	-	122-1251		
		M12	Protects the connect	or against dust	Male	-	230-647		
		Dust Cover	Trotects the connecti	or ayanısı düst	Female	-	88157773		

<sup>\*</sup> See page 4 for reference numbers

# Example Backplane extension Layout and Cabling (DeviceNet™ / CANopen® Network)



NOTE: See page 41 for reference numbers

TA0405MIE000071P

I/O Connector with Molded Cable

N° *	Accessory	Description		Part Number (Europe)	Part Number (Americas)			
		M12 Backplane extension cables with SPEEDCON o	onnect	or technology				
	F 3		TA0501M	GDTC0571P				
А	11	M12 Straight 5 Pin Male to Female Backplane extension Cable - Shielded (backplane extension)  TA0505MGDTC0571						
	<b>9</b>		10 m	TA0510MGDTC0571P				
		M12 Backplane field wireable connector	s and ca	able				
		M12 Straight 5 Pin Female Field Wireable Connector, Spring Ca PG9 Cable Gland	-	TC05F2000000071V				
		M12 Straight 5 Pin Male Field Wireable Connector, Spring Cage PG9 Cable Gland		-	TA05F2000000071V			
A		M12 90° 5 Pin Female Field Wireable Connector, Spring Cage PG9 Cable Gland		-	TD05F2000000071V			
		M12 90° 5 Pin Male Field Wireable Connector, Spring Cage PG9 Cable Gland		-	TB05F2000000071V			
	11		50 m	-	000550MGD0005000			
	0	Bulk Sub-bus Cable*	100 m	-	0005A0MGD0005000			
	1.59-5	7/8" MINI 4 Pin cables & connectors for backplane exte	nsion va	alve module power				
	X	7/8" MINI Straight 4 Pin Female Single Ended Cable Furo Color Male View	5 m	МС0405М	AC0000000			
	10	Single Ended Cable, Euro Color Code  Male View  Male View	10 m	MC0410M	AC0000000			
	X	7/8" MINI 90° 4 Pin Female Single	5 m	MD0405M	AC0000000			
В		Ended Cable, Euro Color Code	10 m	MD0410M	AC0000000			
	10	7/8" MINI Straight 4 Pin Female Field Wireable Connector –Cabl Gland – One size fits all	e	230-1003	MC04F90000000000			
		7/8" MINI 90° 4 Pin Female Field Wireable Connector – PG 9 Ca Gland	230-1001	MD04F20000000000				

<sup>\*</sup> See page 40 for reference numbers

N°*	Accessory	Description		Part Number (Europe)	Part Number (Americas)	
		M12 4 Pin cables for backplane extension In/Out modul	e powe	r		
	*	M42 to 7/9" MINI Cable for Packelane outaging Power	1 m	TA0401MA	.0MC0471T	
С		M12 to 7/8" MINI Cable for Backplane extension Power M12 Straight 4 Pin Male to 7/8" MINI 4 Pin Female Extension	5 m	TA0405MA	.0MC0471T	
	<b>9</b> 6	(distribution of the power 24V to valve systems)	10 m	TA0410MA	.0MC0471T	
	×		1 m	TC0401M	AETA04000	
	1	M12 Straight 4 Pin Male to Female Cable Extension	5 m	TC0405M	AETA04000	
			10 m	TC0410MAETA04000		
	X	M12 Straight 4 Pin Male to Female Cable  Male View  Male View	1 m	TC0405M	VE0000000	
		Extension	5 m	TC0410M	VE0000000	
D	X	M12 Straight 4 Pin Male to Female Cable	1 m	TD0405MAE0000000		
		Extension	5 m	TD0410MAE0000000		
	0	M12 Straight 4 Pin Female Field Wireable Connector - PG 7 Cable Gland	TC04F100	00000000		
	0	M12 Straight 4 Pin Female Field Wireable Connector - PG 9 Cable Gland		TC04F200	00000000	
		M12 90° 4 Pin Female Field Wireable Connector - PG 7 Cable Gland		TD04F100	00000000	
		M12 90° 4 Pin Female Field Wireable Connector - PG 9 Cable Gland		TD04F200	00000000	

\*NOTE: Length of field wired cables should not exceed the maximum length of 30 meters for total Sub-bus communications link. See appropriate technical manual for Sub-bus length requirements. The cable assemblies and Bulk cable are the only approved cables for the G3 Sub-bus link. See technical document TDG3SBWD1-0EN for proper installation and wiring of field wireable connectors.


<sup>\*</sup> See page 40 for reference numbers

## **Pin Out and Technical Data**

## M12 Cable - Pin Out/Euro Color Code

#### (Male View)







#### 7/8" MINI Cable - Pin Out/Euro Color Code

## (Male View)









Technical Data	M12	7/8" MINI
Molded Body/Insert	Cable = PVC Field Wireable = Polyamide	Cable = PVC Field Wireable = Polyamide or PBT
Coupling Nut	Nickel Copper Alloy	Black Anodized Aluminum/Die Cast Zinc
Cable Jacket Material	PVC	PVC
Cable O.D.	7.4mm	7.4mm (4 Pin & 5 Pin)
Voltage Rating (Nominal)	250 V Max. @ 105 °C (221 °F)	250 V Max. @ 105 °C (221 °F)
Current Rating	Cables = 4.0 Amps Field Wireable = 4.0 Amps	Cables = 5.5 Amps Field Wireable = 8.0 Amps
Degree of Protection	IP67 (mated)	IP67 (mated)
Operating Temperature	-25 °C to 85 °C (-13 °F to 185 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	Cable = 18 AWG	Cable = 18 AWG
Bend Radius	Cable = 74mm	Cable = 74mm (4 Pin & 5 Pin)
Maximum Wire AWG	Field Wireable = 18 AWG	Field Wireable = 16 AWG
Wire Connection	Field Wireable = Screw Terminal	Field Wireable = Screw Terminal
PG 7 Range	4 – 6mm	N/A
PG 9 Range	6 – 8mm	5 – 13mm -One size fits all
PG 13.5 Range	N/A	5 – 13mm - One size fits all



## M12 Cable Splitter, 2 Straight M12 Female Connectors

TA04D3MIEJC04000 - 0.3 Meter

TA04E5MIEJC04000 - 1.5 Meter

TA0403MIEJC04000 - 3.0 Meter



#### M12 Cable Splitter, 2 Straight M8 Female Connectors

TA04D3MIEKC03000 - 0.3 Meter

TA04E5MIEKC03000 - 1.5 Meter

TA0403MIEKC03000 - 3.0 Meter



#### **Wire Stripper Tool**

140-1097

## I/O Cable Connector Pin Out Diagrams

#### M12 Cable - Pin Out/Color Code

TA04XXMIE0000000, TB04XXMIE0000000

(Male View)



#### M12 Cable - Pin Out/Color Code

TC03XXMIEPA0371P

(Male to Female View)



#### M12 Cable - Pin Out/Color Code

TC03XXMIEPA0371P

(Male to Female View)






#### M12 to M12 "Y" Splitter - Pin Out

TA0500000|C05000


(Male to Female View)



#### M12 to M8 "Y" Splitter - Pin Out

TA0400000KC03000


(Male to Female View)



#### M12 Field Wireable (IDC) - Pin Out

TA04F2000000081E (SPEEDCON®)


(Male View)



#### M12 to M12 Cable Splitter - Pin Out

TA04XXMIEIC04000


(Male to Female View)



#### M12 to M8 Cable Splitter - Pin Out

TA04XXMIEKC03000


(Male to Female View)



#### M8 Cable - Pin Out/Color Code

PC03XXMIEPA0371P

(Male to Female View)



XX denotes allowable length. See pages 101 & 102.

## **Cable and Connector Technical Data**


Technical Data	M12 Cables	M12/M8 Cables	M12 Connectors
Molded Body/Insert	TPU	TPU	Polyamide (or) PA 66
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc	Nickel Plated Zinc
Cable Jacket Material	PUR	PUR	NA
Cable O.D.	4.70mm	4.70mm	PG7 4.0 to 6.0mm PG9 4.0 to 8.0mm
Voltage Rating	250 Volts	60 Volts	50 Volts
Current Rating (Cond.)	4.0 Amps	3.0 Amps	4.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP67 (mated)
Operating Temperature	-25 °C to 80 °C (-13 °F to 176 °F) (fixed instl.)	-25 °C to 80 °C (-13 °F to 176 °F) (fixed instl.)	-25 °C to 80 °C (-13 °F to 176 °F)
Conductor Gauge	22 AWG	22 AWG	22 AWG Min. 18 AWG Max.
Bend Radius	47mm	47mm	NA


Technical Data	I/O "Y" Splitter	I/O Cable Splitter	M8 Cables		
Molded Body/Insert	TPU	TPU	TPU		
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc	Nickel Plated Zinc		
Cable Jacket Material	NA	PUR	PUR		
Cable O.D.	NA	4.40mm	1.17mm		
Voltage Rating	60 Volts	60 Volts	60 Volts		
Current Rating (Cond.)	3.0 Amps	3.0 Amps	4.0 Amps		
Degree of Protection	IP67 (mated)	IP67 (mated)	IP67 (mated)		
Operating Temperature	-25 °C to 90 °C (-13 °F to 194 °F)	-25 °C to 80 °C (-13 °F to 176 °F)	-25°C to 90°C (-13 °F to 194°F)		
Conductor Gauge	NA	22 AWG or 24 AWG	24 AWG		
Bend Radius	NA	44mm	44mm		

Technical Data	Wire Stripper
Use with	PVC Insulation
Stripping Range	28 AWG to 10 AWG
Cutting Range (Flexible)	10 AWG
Cutting Range (Rigid)	12 AWG


#### **Dimensions (mm) - G3 Fieldbus Manifold Assembly**


Series 501 valve system assembly with G3 Electronics w/ Backplane extension Output






Series 501 valve system assembly with G3 Electronics w/o backplane extension output (with left terminator module)







### **Dimensions (mm) - G3 Fieldbus Manifold Assembly**


Series 502 valve system assembly with G3 Electronics w/ Backplane extension Output






Series 502 valve system assembly with G3 Electronics w/o backplane extension output






## Dimensions (mm) - G3 Fieldbus Manifold Assembly

Series 503 valve system assembly with G3 Electronics w/ Backplane extension Output





Series 503 valve system assembly with G3 Electronics w/o backplane extension output (with left terminator module)




## Dimensions (mm) - G3 Fieldbus I/O Assembly


## I/O Assembly with G3 Electronics w/o Backplane extension output









## I/O Assembly with G3 Electronics w/ Backplane extension output








RAIL HARDWARE AND 35mm DIN RAIL

Α	A1	В	C	D	Е	F	G	Н	J	J1	K	K1	Г	М	N	Р	R	S	Т	U
46.4	57.6	67.5	57.6	7.0	105.5	38.0	33.7	6.25	185.3	196.5	13.5	24.5	67.5	37	54.0	12.5	62.5	5.1	59.0	118.0


## Dimensions (mm) - G3 Sub-bus I/O Assembly

3 Pin M8 Sub-bus Module



Α	В
33	171.75


#### **How to Order - G3 Electronics**



#### **G3** Electronics

Ordering Valve System Assemblies with G3 Electronics & Discrete I/O

For valve series 501, 502, 503, 2035, ISO15407-2 & ISO 5599/2



Shaded components are described by the assembly kit (AK) model number. The communication module and number of I/O modules are described by the Electronic Interface (G3) model number designation.

Each valve station is listed in sequential order from left to right when facing the port side of the manifold as shown.

Each discrete I/O module is listed in sequential order from RIGHT to LEFT starting from the communication module as shown.

#### NOTE:

A total of 128 (501) / 80 (502/503) solenoid outputs are available. Either single solenoid valves or double solenoid valves or any combination of singles.

## Example Order - 502 Shown


Assembly Kit	G502AV3H100VA00
Valve Station #1	R502A1B40MA00F1
Valve Station #2	R502A1B40MA00F1
Valve Station #3	R502A1B40MA00F1
Valve Station #4	R502A1B40MA00F1
Mounting # 1	G502AMM22MA0010
Valve Station #1	R502A1B40MA00F1
Valve Station #2	R502A1B40MA00F1
Valve Station #3	R502A1B40MA00F1
Valve Station #4	R502A1B40MA00F1
Mounting # 2	G502AMM22MA0010
Valve Station #1	R502A1B40MA00F1
Valve Station #2	R502A1B40MA00F1
Valve Station #3	R502A1B40MA00F1
Valve Station #4	R502A1B40MA00F1
Mounting # 3	8G502AMM22MA0010
Valve Station #1	R502A1B40MA00F1
Valve Station #2	R502A1B40MA00F1
Valve Station #3	R502A1B40MA00F1
Valve Station #4	R502A1B40MA00F1
Mounting # 4	G502AMM22MA0010
Electronics	G3DN116R0E40
Station 1 240-205	
Station 2 240-205	
;	
Station 15 240-2	205

Station 15 240-205<sup>4</sup> 240-205 Station 16

Availability, design and specifications are subject to change without notice. © 2023 Emerson Electric Co. All rights reserved.

#### **G3** Electronics

Ordering G3 Electronics Assemblies with I/O Only



- 1. Refer to the selection table to specify the control electronics and I/O configuration.
- 2. Each discrete I/O module is listed in sequential order from RIGHT to LEFT as shown.
- 3. A maximum of 16 I/O modules are supported by a single communication node. Analog I/O & digital I/O (NPN & PNP)

Example Order - I/O assembly with Backplane extensions in and backplane extension out modules

Electronics G3DS316D0STD

Station 1 240-205 Station 2 240-205

Station 15 240-205 Station 16 240-205