Rosemount[™] 8600 Series Utility[™] Vortex Flowmeter



The Rosemount 8600 Vortex delivers superior reliability for general purpose applications.

- Rosemount reliability—the Rosemount 8600 Vortex improves reliability over traditional flow metering technology.
- Vibration immunity—mass balancing of the sensor system, and Adaptive Digital Signal Processing (ADSP) provide vibration immunity.
- Simplified Troubleshooting Device Diagnostics enable field verification of Meter Electronics and meter verification.



Rosemount[™] 8600 MultiVariable[™] Vortex reduces installation costs, simplifies installation, and improves performance in saturated steam

Multivariable vortex design

Incorporates temperature sensor into the vortex meter using the shedder bar as a thermowell, which keeps the temperature sensor isolated from process for easy verification and replacement.

Temperature compensated capability for saturated steam

Calculates density from measured process temperature and uses the calculated density to provide a temperature compensated mass flow.

Increased performance in saturated steam

Performance in saturated steam is improved due to the fact that the electronics will be compensating for changes in the process temperature.

Reduces installed costs

MultiVariable vortex eliminates the need for an external thermowell and temperature sensor.

Output options

Can map independent variables to analog output, pulse output, or HART® burst variables.

Available with flow computer for additional functionality

Integrate the Multivariable vortex with a pressure transmitter for full pressure and temperature compensation of superheated steam and various gases.

Remote mount electronics

Also available with remote mounted electronics up to 75 ft. (23 m).

When you integrate the Multivariable vortex with a Rosemount Flow Computer, you get:

- Remote communications
- Heat calculations
- Remote totalization
- Peak demand calculation
- Datalogging capabilities

For more information on the Rosemount Flow Computer, see the Rosemount Flow Computer Product Data Sheet.



Contents

Specifications page 3	Dimensional drawingspage 15
Typical flow rangespage 7	Ordering information page 19
Product Certificationspage 14	

Specifications

The following specifications are for the Rosemount 8600 except where noted.

Functional specifications

Process fluids

Liquid, gas, and steam applications. Fluids must be homogeneous and single-phase.

Line sizes

Flanged style

1, 1¹/₂, 2, 3, 4, 6, and 8 inches (DN 25, 40, 50, 80, 100, 150, and 200)

Pipe schedules

Process piping Schedules 10, 40, 80, and 160.

Note

The appropriate bore diameter of the process piping must be entered using the Field Communicator or AMS™ Device Manager. Meters will be shipped from the factory at the Schedule 40 default value unless otherwise specified.

Measurable flow rates

Capable of processing signals from flow applications which meet the sizing requirements below.

To determine the appropriate flowmeter size for an application, process conditions must be within the Reynolds number and velocity limitations for the desired line size provided in Table 1, Table 2, and Table 3.

Note

Consult your local sales representative to obtain a computer sizing program that describes in greater detail how to specify the correct flowmeter size for an application.

The Reynolds number equation shown below combines the effects of density (r), viscosity (m_{cp}), pipe inside diameter (D), and flow velocity (V).

$$R_D = \frac{VD\rho}{\mu_{CD}}$$

Table 1. Minimum Measurable Meter Reynolds Numbers

Meter sizes (Inches/DN)	Reynolds number limitations
1 through 4/25 through 100	5000 minimum
6 through 8/150 through 200	3000 11111111111111

Table 2. Minimum Measurable Meter Velocities(1)

	Feet per second	Meters per second
Liquids	- <u>β6/ρ</u>	√54/p
Gases	√36/p	√54/ρ

The ρ is the process fluid density at flowing conditions in lb/ft³ for ft/s and kg/m³ for m/s

1. Velocities are referenced to schedule 40 pipe.

Table 3. Maximum Measurable Meter Velocities⁽¹⁾
(Use the smaller of the two values)

	Feet per second	Meters per second
Liquids	√90,000/p or 25	√134,000/ρ or 7.6
Gases	√ <u>90,000/ρ</u> or 250	√134,000/p or 76

The ρ is the process fluid density at flowing conditions in lb/ft³ for ft/s and kg/m³ for m/s

1. Velocities are referenced to schedule 40 pipe.

Process temperature limits

Standard

-58 to 482 °F (-50 to 250 °C)

Output signals

4-20 mA HART digital signal

Superimposed on 4-20 mA signal

Optional scalable pulse output

0 to 10000 Hz; transistor switch closure with adjustable scaling via HART communications; capable of switching up to 30 Vdc, 120 mA maximum.

Analog output adjustment

Engineering units and lower and upper range values are user-selected. Output is automatically scaled to provide 4 mA at the selected lower range value, 20 mA at the selected upper range value. No frequency input is required to adjust the range values.

Scalable frequency adjustment

The scalable pulse output can be set to a specific velocity, volume, or mass (i.e. 1 pulse = 1 lb). The scalable pulse output can also be scaled to a specific rate of volume, mass, or velocity (i.e. 100 Hz = 500 lb/hr).

Ambient temperature limits

Operating

- -58 to 185 °F (-50 to 85 °C)
- -4 to 185 °F (-20 to 85 °C) for flowmeters with local indicator

Storage

- -58 to 250 °F (-50 to 121 °C)
- -50 to 185 °F (-46 to 85 °C) for flowmeters with local indicator

Pressure limits

Flange style meter

Rated for ASME B16.5 (ANSI) Class 150, 300, EN 1092-1 PN 16 and 40.

Power supply

HART analog


External power supply required. Flowmeter operates on 10.8 to 42 Vdc terminal voltage (with 250-ohm minimum load required for HART communications, 16.8 Vdc power supply is required).

Power consumption

One watt maximum

Load limitations (HART analog)

Maximum loop resistance is determined by the voltage level of the external power supply, as described by:



 $R_{\text{max}} = 41.7(V_{\text{ps}} - 10.8)$

V_{ps} = Power Supply Voltage (Volts)

R_{max} = Maximum Loop Resistance (Ohms)

Note

HART communication requires a minimum loop resistance of 250 ohms.

Optional LCD display

The optional LCD display is capable of displaying:

- Primary Variable
- Velocity Flow
- Volumetric Flow
- Mass Flow
- Percent of Range
- Analog Output
- Totalizer
- Shedding Frequency
- Pulse Output Frequency (if applicable)
- Electronics Temperature
- Process Temperature (MTA Option Only)
- Calculated Process Density (MTA Option Only)

If more than one item is selected, the display will scroll through all items selected.

Enclosure rating

FM Type 4X; IP66

Permanent pressure loss

The approximate permanent pressure loss (PPL) from the Rosemount 8600 Flowmeter is calculated for each application in the Vortex sizing software available from your local Rosemount representative. The PPL is determined using the equation:

$$PPL = \frac{A \times \rho_f \times Q^2}{D^4}$$

where:

PPL = Permanent Pressure loss (psi or kPa)

Where:

 r_f = Density at operating conditions (lb/ft³ or kg/m³)

Q = Actual volumetric flow rate (Gas = ft³/min or m³/hr; Liquid = gal/min or l/min)

D = Flowmeter bore diameter (in. or mm)

A = Constant depending on meter style, fluid type, and flow units. Determined per the following table:

Table 4. Determining the PPL

Meter	Englis	h units	SI units		
style	A _{Liquid} A _{Gas}		A _{Liquid}	A _{Gas}	
8600 F	3.4 3 10-5	1.9 3 10-3	0.425	118	

Minimum upstream pressure (liquids)

Flow metering conditions that would allow cavitation, the release of vapor from a liquid, should be avoided. This flow condition can be avoided by remaining within the proper flow range of the meter and by following appropriate system design.

For some liquid applications, incorporation of a back pressure valve should be considered. To prevent cavitation, the minimum upstream pressure should be:

- $P = 2.9*\Delta P + 1.3*p_v \text{ or } P = 2.9*\Delta P + p_v + 0.5 \text{ psia (3.45 kPa) (use the smaller of the two results)}$
- P = Line pressure five pipe diameters downstream of the meter (psia or kPa abs)
- ΔP = Pressure loss across the meter (psi or kPa)
- p_v = Liquid vapor pressure at operating conditions (psia or kPa abs)

Failure mode alarm

HART analog

If self-diagnostics detect a gross flowmeter failure, the analog signal will be driven to the following values:

Signal	Value	
Low	3.75	
High	21.75	
NAMUR Low	3.60	
NAMUR High	22.6	

High or low alarm signal is user-selectable through the fail mode alarm jumper on the electronics. NAMUR-compliant alarm limits are available through the C4 or CN Option. Alarm type is field configurable also.

Saturation output values

When the operating flow is outside the range points, the analog output continues to track the operating flow until reaching the saturation value listed below; the output does not exceed the listed saturation value regardless of the operating flow.

The NAMUR-Compliant Saturation Values are available through the C4 or CN option. Saturation type is field configurable.

Saturation	Value
Low	3.9
High	20.8
NAMUR Low	3.8
NAMUR High	20.5

Damping

Flow Damping adjustable between 0.2 and 255 seconds.

Process Temperature Damping adjustable between 0.4 and 32.0 seconds (MTA Option Only).

Response time

Three vortex shedding cycles or 300 ms, whichever is greater, maximum required to reach 63.2% of actual input with the minimum damping (0.2 seconds).

Turn-on time

HART analog

Less than four (4) seconds plus the response time to rated accuracy from power up (less than 7 seconds with the MTA Option).

Transient protection

The optional transient terminal block prevents damage to the flowmeter from transients induced by lightning, welding, heavy electrical equipment, or switch gears. The transient protection electronics are located in the terminal block.

The transient terminal block meets the following specifications:

IEEE C62.41 - 2002 Category B

3 kA crest (8 3 20 μs)

6 kV crest (1.2 3 50 μs)

 $6 \text{ kV}/0.5 \text{ kA} (0.5 \,\mu\text{s}, 100 \,\text{kHz}, \text{ring wave})$

Security lockout

When the security lockout jumper is enabled, the electronics will not allow you to modify parameters that affect flowmeter output.

Output testing

Current source

Flowmeter may be commanded to set the current to a specified value between 4 and 20 mA.

Frequency source

Flowmeter may be commanded to set the frequency to a specified value between 0 and 10000 Hz.

Low flow cutoff

Adjustable over entire flow range. Below selected value, output is driven to 4 mA and zero pulse output frequency.

Humidity limits

Operates in 0–95% relative humidity under noncondensing conditions (tested to IEC 60770, Section 6.2.11).

Overrange capability

HART analog

Analog signal output continues to 105 percent of span, then remains constant with increasing flow. The digital and pulse outputs will continue to indicate flow up to the upper sensor limit of the flowmeter and a maximum pulse output frequency of 10400 Hz.

Flow calibration

Meter bodies are flow-calibrated and assigned a unique calibration factor (K-factor) at the factory. The calibration factor is entered into the electronics, enabling interchangeability of electronics and/or sensors without calculations or compromise in accuracy of the calibrated meter body.

Typical flow ranges

Tables 5 through 9 show typical flow ranges for some common process fluids with default filter settings. Consult your local sales representative to obtain a computer sizing program that describes in greater detail the flow range for an application.

Table 5. Typical pipe velocity ranges for 8600⁽¹⁾

Process line size		Liquid velo	ocity ranges	Gas velocity ranges		
(Inches/ DN)	Vortex meter	(ft/s) (m/s)		(ft/s)	(m/s)	
1/ 25	8600F010	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	
11/2 / 40	8600F015	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	
2/ 50	8600F020	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	
3/ 80	8600F030	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	
4/ 100	8600F040	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	
6/ 150	8600F060	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	
8/ 200	8600F080	0.70 to 25.0	0.21 to 7.6	6.50 to 250.0	1.98 to 76.2	

^{1.} Table 5 is a reference of pipe velocities that can be measured for the standard Rosemount 8600. It does not consider density limitations, as described in Table 2 and 3. Velocities are referenced in schedule 40 pipe.

Table 6. Water Flow Rate Limits for the Rosemount 8600⁽¹⁾

Process line size		Minimum and maximum measurable water flow				
(Inches/ DN)	ches/ DN) Vortex meter Gal		Cubic Meters/Hour			
1/ 25	8600F010	2.96 to 67.3	0.67 to 15.3			
11/2 / 40	8600F015	4.83 to 158	1.10 to 35.9			
2/50	8600F020	7.96 to 261	1.81 to 59.4			
3/80	8600F030	17.5 to 576	4.00 to 130			
4/ 100	8600F040	30.2 to 992	6.86 to 225			
6/ 150	8600F060	68.5 to 2251	15.6 to 511			
8/ 200	8600F080	119 to 3898	27.0 to 885			

^{1.} Table 6 is a reference of flow rates that can be measured for the standard Rosemount 8600. It does not consider density limitations, as described in Table 2 and 3.

Table 7. Air Flow Rate Limits at 59 °F (15 °C)

		Minimum and maximum air flow rates for line sizes 1-in./DN 25 through 2-in./DN 50						
Process pressure	Flow rate limits	1-in./DN 25		1¹/2-in	1 ¹ /2-in./DN 40		2-in./DN 50	
·		Rosemo	Rosemount 8600		Rosemount 8600		Rosemount 8600	
		ACFM	ACMH	ACFM	ACMH	ACFM	АСМН	
0 psig (0 bar G)	max	79.2	134	212	360	349	593	
	min	9.71	16.5	18.4	31.2	30.3	51.5	
50 psig (3.45 bar G)	max	79.2	134	212	360	349	593	
	min	3.72	6.32	8.76	14.9	14.5	24.6	
100 psig (6.89 bar G)	max	79.2	134	212	360	349	593	
	min	2.80	4.75	6.58	11.2	10.8	18.3	
150 psig (10.3 bar G)	max	79.2	134	212	360	349	593	
	min	2.34	3.98	5.51	9.36	9.09	15.4	
200 psig (13.8 bar G)	max	79.2	134	212	360	349	593	
	min	2.34	3.98	5.51	9.36	9.09	15.4	
300 psig (20.7 bar G)	max	79.2	134	198	337	326	554	
	min	2.34	3.98	5.51	9.36	9.09	15.4	
400 psig (27.6 bar G)	max	73.0	124	172	293	284	483	
	min	2.34	3.98	5.51	9.36	9.09	15.4	
500 psig (34.5 bar G)	max	66.0	112	154	262	254	432	
	min	2.34	3.98	5.51	9.36	9.09	15.4	

Table 8. Air Flow Rate Limits at 59 °F (15 °C)

		Minimum and maximum air flow rates for line sizes 3-in./DN 80 through 4-in./DN 100				
Process pressure	Flow rate limits	3-in./	DN 80	4-in./DN 100		
·		Rosemo	unt 8600	Rosemount 8600		
		ACFM	ACMH	ACFM	ACMH	
0 psig (0 bar G)	max	770	1308	1326	2253	
	min	66.8	114	115	195	
50 psig (3.45 bar G)	max	770	1308	1326	2253	
	min	31.8	54.1	54.8	93.2	
100 psig (6.89 bar G)	max	770	1308	1326	2253	
	min	23.9	40.6	41.1	69.8	
150 psig (10.3 bar G)	max	770	1308	1326	2253	
	min	20.0	34.0	34.5	58.6	
200 psig (13.8 bar G)	max	770	1308	1326	2253	
	min	20.0	34.0	34.5	58.6	
300 psig (20.7 bar G)	max	718	1220	1237	2102	
	min	20.0	34.0	34.5	58.6	
400 psig (27.6 bar G)	max	625	1062	1076	1828	
	min	20.0	34.0	34.5	58.6	
500 psig (34.5 bar G)	max	560	951	964	1638	
	min	20.0	34.0	34.5	58.6	

Table 9. Air Flow Rate Limits at 59 °F (15 °C)

		Minimum and maximum air flow rates for line sizes 6-in./DN 150 through 8-in./DN 200				
Process pressure	Flow rate limits	6-in./l	DN 150	8-in./DN 200		
·		Rosemo	unt 8600	Rosemo	unt 8600	
		ACFM	АСМН	ACFM	АСМН	
0 psig (0 bar G)	max	3009	5112	5211	8853	
	min	261	443	452	768	
50 psig (3.45 bar G)	max	3009	5112	5211	8853	
	min	124	211	215	365	
100 psig (6.89 bar G)	max	3009	5112	5211	8853	
	min	93.3	159	162	276	
150 psig (10.3 bar G)	max	3009	5112	5211	8853	
	min	78.2	133	135	229	
200 psig (13.8 bar G)	max	3009	5112	5211	8853	
	min	78.2	133	135	229	
300 psig (20.7 bar G)	max	2807	4769	4862	8260	
	min	78.2	133	135	229	
400 psig (27.6 bar G)	max	2442	4149	4228	7183	
	min	78.2	133	136	229	
500 psig (34.5 bar G)	max	2188	3717	3789	6437	
	min	78.2	133	136	229	

Notes

The Rosemount 8600 measures the volumetric flow under operating conditions (i.e. the actual volume at the operating pressure and temperature—acfm or acmh), as shown above. However, gas volumes are strongly dependent on pressure and temperature. Therefore, gas quantities are typically stated in standard or normal conditions (for example: SCFM or NCMH). (Standard conditions are typically 59 °F and 14.7 psia. Normal conditions are typically 0 °C and 1 bar abs.)

The flow rate limits in standard conditions are found using the equations below:

Standard Flow Rate = Actual Flow Rate X Density Ratio

Density Ratio = Density at Actual (Operating) Conditions/Density at Standard Conditions

Table 10. Saturated Steam Flow Rate Limits (Assumes Steam Quality is 100%)

		Minimum and maximum saturated steam flow rates for line sizes 1-in./DN 25 through 2-in./DN 50						
Process pressure	Flow rate limits	1-in./	DN 25	11/2-in	./DN 40	2-in./DN 50		
		Rosemo	unt 8600	Rosemo	Rosemount 8600 Rosemoun		unt 8600	
		lb/hr	kg/hr	lb/hr	kg/hr	lb/hr	kg/hr	
15 psig (1.03 bar G)	max	342	155	917	416	1511	685	
	min	34.8	15.8	82.0	37.2	135	61.2	
25 psig (1.72 bar G)	max	449	203	1204	546	1983	899	
	min	39.9	18.1	93.9	42.6	155	70.2	
50 psig (3.45 bar G)	max	711	322	1904	864	3138	1423	
	min	50.1	22.7	118	53.4	195	88.3	
100 psig (6.89 bar G)	max	1221	554	3270	1483	5389	2444	
	min	65.7	29.8	155	70.1	255	116	

Table 10. Saturated Steam Flow Rate Limits (Assumes Steam Quality is 100%)

		Minimum and maximum saturated steam flow rates for line sizes 1-in./DN 25 through 2-in./DN 50						
Process pressure	Flow rate limits	1-in./	DN 25	1 ¹ /2-in	./DN 40	2-in./DN 50		
		Rosemo	unt 8600	Rosemount 8600 Rosemour			unt 8600	
		lb/hr	kg/hr	lb/hr	kg/hr	lb/hr kg/hr 7609 3451		
150 psig (10.3 bar G)	max	1724	782	4616	2094	7609	3451	
	min	78.1	35.4	184	83.2	303	137	
200 psig (13.8 bar G)	max	2225	1009	5956	2702	9818	4453	
	min	88.7	40.2	209	94.5	344	156	
300 psig (20.7 bar G)	max	3229	1464	8644	3921	14248	6463	
	min	107	48.5	252	114	415	189	
400 psig (27.6 bar G)	max	4244	1925	11362	5154	18727	8494	
	min	125	56.7	295	134	487	221	
500 psig (34.5 bar G)	max	5277	2393	14126	6407	23284	10561	
	min	156	70.7	367	167	605	274	

Table 11. Saturated Steam Flow Rate Limits (Assumes Steam Quality is 100%)

			um and maximum : line sizes 3-in./DN 8			
Process pressure	Flow rate limits	3-in./	DN 80	4-in./DN 100		
·		Rosemo	ount 8600	Rosemo	unt 8600	
		lb/hr	kg/hr	lb/hr	kg/hr	
15 psig (1.03 bar G)	max	3330	1510	5734	2601	
	min	298	135	513	233	
25 psig (1.72 bar G)	max	4370	1982	7526	3414	
	min	341	155	587	267	
50 psig (3.45 bar G)	max	6914	3136	11905	5400	
	min	429	195	739	335	
100 psig (6.89 bar G)	max	11874	5386	20448	9275	
	min	562	255	968	439	
150 psig (10.3 bar G)	max	16763	7603	28866	13093	
	min	668	303	1150	522	
200 psig (13.8 bar G)	max	21630	9811	37247	16895	
	min	759	344	1307	593	
300 psig (20.7 bar G)	max	31389	14237	54052	24517	
	min	914	415	1574	714	
400 psig (27.6 bar G)	max	41258	18714	71047	32226	
	min	1073	487	1847	838	
500 psig (34.5 bar G)	max	51297	23267	88334	40068	
	min	1334	605	2297	1042	

Table 12. Saturated Steam Flow Rate Limits (Assumes Steam Quality is 100%)

		Minimum and maximum saturated steam flow rates for line sizes 6-in./DN 150 through 8-in./DN 200					
Process	Flow rate	6-in./l	DN 150	8-in./l	DN 200		
Pressure	limits	Rosemo	unt 8600	Rosemo	ount 8600		
	-	lb/hr	kg/hr	lb/hr	kg/hr		
15 psig	max	13013	5903	22534	10221		
(1.03 bar G)	min	1163	528	2015	914		
25 psig	max	17080	7747	29575	13415		
(1.72 bar G)	min	1333	605	2308	1047		
50 psig	max	27019	12255	46787	21222		
(3.45 bar G)	min	1676	760	2903	1317		
100 psig	max	46405	21049	80356	36449		
(6.89 bar G)	min	2197	996	3804	1725		
150 psig	max	65611	29761	113440	51455		
(10.3 bar G)	min	2610	1184	4520	2050		
200 psig	max	84530	38342	146375	66395		
(13.8 bar G)	min	2965	1345	5134	2329		
300 psig	max	122666	55640	212411	96348		
(20.7 bar G)	min	3572	1620	6185	2805		
400 psig	max	161236	73135	279200	126643		
(27.6 bar G)	min	4192	1901	7259	3293		
500 psig	max	200468	90931	347134	157457		
(34.5 bar G)	min	5212	2364	9025	4094		

Performance specifications

The following performance specifications are for all Rosemount models except where noted. Digital performance specifications applicable to Digital HART output.

Flow accuracy

Includes linearity, hysteresis, and repeatability.

Liquids - for Reynolds numbers over 20,000

Digital and pulse output

 $\pm 0.75\%$ of rate

Analog output

Same as pulse output plus an additional 0.025% of span

Gas and steam—for Reynolds numbers over 15,000

Digital and pulse output

±1% of rate

Analog output

Same as pulse output plus an additional 0.025% of span.

Note

As the meter maximum velocity exceeds 125ft/sec (38m/sec) the accuracy error band will increase linearly to $\pm 1.5\%$ up to 250ft/sec (76m/sec).

Note

As the meter Reynolds numbers decrease below the stated limit to 10,000, the accuracy error band will increase linearly to $\pm 3.0\%$. For Reynolds numbers down to 5,000, the accuracy error band will increase linearly from $\pm 3.0\%$ to $\pm 10.0\%$.

Process Temperature Accuracy

2.2 °F (1.2 °C)

Note

For remote mount installations, add ± 0.018 °F/ft. (± 0.03 °C/m) of uncertainty to the temperature measurement.

Mass flow accuracy for temperature compensated mass flow

Digital and Pulse Output

±2.0% of rate (Nominal)

Nominal conditions include temperature variation in saturation and superheat at 150 psig (10 bar-g) and above.

For pressure below 150 psig (10 bar-g), add 0.08% of uncertainty for every 15 psi (1 bar) below 150 psig (10 bar-g).

Analog output

Same as pulse output plus an additional 0.025% of span

Repeatability

± 0.2% of actual flow rate

Stability

± 0.2% of rate over one year

Process temperature effect

Automatic K-factor correction with user-entered process temperature.

Table 13 indicates the percent change in K-factor per 100 °F

(55.5 °C) in process temperature from reference temperature of 77 °F (25 °C).

Table 13. Process Temperature Effect

Percent change in K-Factor per 100°F (55.5°C)		
<77 °F (25 °C)	+ 0.23	
>77 °F (25 °C)	- 0.27	

Ambient temperature effect

Digital and pulse outputs

No effect

Analog output

±0.1% of span from -58 to 185 °F (-50 to 85 °C)

Vibration effect

An output with no process flow may be detected if sufficiently high vibration is present.

The meter design will minimize this effect and the factory settings for signal processing are selected to eliminate these errors for most applications.

If an output error at zero flow is still detected, it can be eliminated by adjusting the low flow cutoff, trigger level, or low-pass filter.

As the process begins to flow through the meter, most vibration effects are quickly overcome by the flow signal.

Vibration specifications

Integral aluminum housings and remote aluminum housings

At or near the minimum liquid flow rate in a normal pipe mounted installation, the maximum vibration should be 0.087-in. (2.21 mm) double amplitude displacement or 1 g acceleration, whichever is smaller. At or near the minimum gas flow rate in a normal pipe mounted installation, the maximum vibration should be 0.043-in. (1.09 mm) double amplitude displacement or 1/2 g acceleration, whichever is smaller.

Mounting position effect

Meter will meet accuracy specifications when mounted in horizontal, vertical, or inclined pipelines. Best practice for mounting in a horizontal pipe is to orient the shedder bar in the horizontal plane. This will prevent solids in liquid applications and liquid in gas/steam applications from disrupting the shedding frequency.

EMI/RFI effect

Meets EMC requirements to EU Directive 2004/108/EC.

HART analog

Output error less than $\pm 0.025\%$ of span with twisted pair from 80-1000 MHz for radiated field strength of 10 V/m; 1.4 - 2.0 GHz for radiated field strength of 3 V/m; 2.0 - 2.7 GHz for radiated field strength of 1 V/m. Tested per EN61326.

HART digital

No effect on the values that are being given if using HART digital signal.

Tested per EN61326.

Magnetic-field interference

HART analog

Output error less than $\pm 0.025\%$ of span at 30 A/m (rms). Tested per EN61326.

Series mode noise rejection

HART analog

Output error less than $\pm 0.025\%$ of span at 1 V rms, 60 Hz.

Common mode noise rejection

HART analog

Output error less than $\pm 0.025\%$ of span at 30 V rms, 60 Hz.

Power supply effect

HART analog

Less than 0.005% of span per volt

Physical specifications

Note

Certificate of compliance for MR0175/ISO15156 requires Q15 as a separate line item.

Electrical connections

 $^{1}/_{2}$ –14 NPT or M20 3 1.5 conduit threads; screw terminals provided for 4–20 mA and pulse output connections; communicator connections permanently fixed to terminal block.

Non-wetted materials

Housing

Low-copper aluminum (FM Type 4X, CSA Type 4X, IP66)

Paint

Polyurethane

Cover O-rings

Buna-N

Temperature sensor (MTA option)

Type-N Thermocouple

Process-wetted materials

Meter body and flanges

CF-8M cast stainless steel.

Sensor material

CF-3M cast stainless steel.

Gasket

Graphite with 316 stainless steel insert

Process connections

Mounts between the following flange configurations:

ASME B16.5 (ANSI): Class 150, 300

EN 1092-1 PN16, 40 Type B1

Mounting

Integral (standard)

Electronics are mounted on meter body.

Remote (optional)

Electronics may be mounted remote from the meter body. Interconnecting coaxial cable available in nonadjustable 10, 20, and 30 ft (3.0, 6.1, and 9.1 m) lengths. Consult factory for non-standard lengths up to 75 ft (22.9 m). Remote mounting hardware includes a pipe mount bracket with one u-bolt.

Temperature limitations for integral mounting

The maximum process temperature for integral mount electronics is dependent on the ambient temperature where the meter is installed. The electronics must not exceed 185 °F (85 °C).

Product Certifications

For detailed approval certification information and installation drawings, please see document number 00825-VA00-0011:

Rosemount™ 8600 Series Vortex Flowmeter Approval Document.

Pipe length requirements

The vortex meter may be installed with a minimum of ten diameters (D) of straight pipe length upstream and five diameters (D) of straight pipe length downstream.

Rated Accuracy is based on the number of pipe diameter from an upstream disturbance. No K-factor correction is required if the meter is installed with 35 D upstream and 10 D downstream.

Tagging

The flowmeter will be tagged at no charge. All tags are stainless steel. The standard tag is permanently attached to the flowmeter. Character height is 1/16-in. (1.6 mm). A wired-on tag is available on request. Wire on tags can contain five lines with up to 28 characters per line.

Flow calibration information

Flowmeter calibration and configuration information is provided with every flowmeter. For a certified copy of flow calibration data, Option Q4 must be ordered in the model number.

Dimensional drawings

Figure 1. Flanged-Style Flowmeter—Line Sizes 1- through 8-in. (25 through 200 mm)




Diagram illustrated without MTA Option




Diagram illustrated with MTA Option




Table 14. Flanged-Style Flowmeter—Line Sizes 1- through 2-in. (25 through 50 mm)

Nominal size in. (mm)	Flange rating	Face-to-face A in. (mm)	Diameter B in. (mm)	C in. (mm)	Weight ⁽¹⁾ lb (kg)
1 (25)	ANSI 150 ANSI 300	5.9 (150) 6.7 (170)	0.95 (24,1) 0.95 (24,1)	9.6 (244) 9.6 (244)	13 (5.9) 15.4 (7,0)
, ,	PN 16/40	6.1 (156)	0.95 (24,1)	9.6 (244)	14.8 (6.7)
1 1/2 (40)	ANSI 150 ANSI 300	5.9 (150) 7.1 (180)	1.49 (37,8) 1.49 (37,8)	8.1 (250) 8.1 (250)	15.7 (7.1) 21.4 (9.7)
	PN 16/40	7.1 (180)	1.49 (37,8)	8.1 (250)	18.7 (8.5)
2 (50)	ANSI 150 ANSI 300	6.7 (170) 7.1 (180)	1.92 (48,8) 1.92 (48,8)	10 (254) 10 (254)	20.5 (9.3) 24.5 (11.1)
. /	PN 16/40	6.7 (170)	1.92 (48,8)	10 (254)	22.7 (10.3)

^{1.} Add 0.2 lb (0,1 kg) for display option.

Table 15. Flanged-Style Flowmeter—Line Sizes 3- to 6-in. (80 mm to 150 mm) (Refer to Figure 1)

Nominal size in. (mm)	Flange rating	Face-to-face A in. (mm)	Diameter B in. (mm)	C in. (mm)	Weight ⁽¹⁾ lb (kg)
3 (80)	ANSI 150 ANSI 300	7.5 (190) 8.8 (224)	2.87 (72,9) 2.87 (72,9)	10.7 (271) 10.6 (268)	33.1 (15,0) 41.4 (18,8)
, ,	PN 16/40	7.9 (200)	2.87 (72,9)	10.6 (268)	34.4 (15.6)
4 (100)	ANSI 150 ANSI 300	7.5 (190) 8.7 (220)	3.79 (96,3) 3.79 (96,3)	11.1 (281) 11.1 (281)	42.8 (19.6) 63.1 (28.6)
	PN 16 PN 40	7.5 (190) 8.7 (220)	3.79 (96,3) 3.79 (96,3)	11.1 (281) 11.1 (281)	42.8 (19,6) 43.4 (19.7)
C (1F0)	ANSI 150 ANSI 300	9.8 (250) 10.6 (270)	5.7 (144,8) 5.7 (144,8)	12.1 (307) 12.1 (307)	69.9 (31.7) 161.8 (73.4)
6 (150)	PN 16 PN 40	9.8 (250) 10.6 (270)	5.7 (144,8) 5.7 (144,8)	12.1 (307) 12.1 (307)	69.9 (31.7) 130.5 (59.2)


^{1.} Add 0.2 lb (0,1 kg) for display option.

Table 16. Flanged-Style Flowmeter—Line Size 8-in. (200 mm) (Refer to Figure 3)

Nominal size in. (mm)	Flange rating	Face-to-face A in. (mm)	Diameter B in. (mm)	Cin. (mm)	Weight ⁽¹⁾ lb (kg)
	ANSI 150	9.8 (250)	7.55 (191,8)	13.1 (332)	104.9 (47.6)
	ANSI 300	11.4 (290)	7.55 (191,8)	13.1 (332)	161.8 (73.4)
8 (200)	PN 16	9.8 (250)	7.55 (191,8)	13.1 (332)	104.9 (47.6)
	PN 40	12.2 (310)	7.55 (191,8)	13.1 (332)	130.5 (59.2)

^{1.} Add 0.2 lb (0,1 kg) for display option.

Figure 2. Remote Mount Transmitters



Note:


Consult factory for SST installation. Dimensions are in inches (millimeters).

A. Display option

B. Terminal cover

C. 1/2-14 NPT (for remote cable conduit)

Figure 3. Flanged Style Remote Mount Flowmeters—Line Sizes 1- to 8-in. (25 mm to 200 mm)



Nota.

Dimensions are in inches (millimeters).

A. 1/2-14 NPT (for remote cable conduit)

Table 17. Remote Mount, Flanged Style Sensor Flowmeter Dimensions

Nominal size in. (mm)	E flange style in. (mm)
1 (25)	8.3 (210)
1? (40)	8.5 (216)
2 (50)	8.7 (220)
3 (80)	9.3 (237) - ANSI150/PN16 9.1 (234) - ANSI300/PN40
4 (100)	9.7 (247)
6 (150)	10.8 (273)
8 (200)	11.7 (298)

Ordering information

Table 18. Rosemount 8600 Vortex Flowmeter Ordering Information

The Standard offering represents the most common models and options. These options should be selected for best delivery. The Expanded offering is subject to additional delivery lead time.

Table 18. Rosemount 8600 Vortex Flowmeter Ordering Information

The Standard offering represents the most common models and options. These options should be selected for best delivery. The Expanded offering is subject to additional delivery lead time.

Conduit entry and housing material		
1	¹ / ₂ -14 NPT – Aluminum Housing	
2	M20 3 1.5 – Aluminum Housing	
Transmitter output		
D	4-20 mA digital electronics (HART protocol)	
Р	4-20 mA digital electronics (HART protocol) with scaled pulse	
Calibration		
1	7 Point Flow Calibration	

Options

MultiVariable op	otions				
MTA	MultiVariable output with Integral Temperature Sensor				
Hazardous locat	ions certifications				
E3	NEPSI Flameproof				
13	NEPSI Intrinsic Safety				
N3	NEPSI Type N				
K3	NEPSI Flameproof, Intrinsic Safety, Type N				
E1	ATEX Flameproof				
l1	ATEX Intrinsic Safety				
N1	ATEX Type-n				
K1	ATEX Flameproof, Intrinsic Safety				
E7	IECEx Flameproof				
17	IECEx Intrinsic Safety				
N7	IECEx Type n				
E6	CSA (C/US) Explosion-proof, Dust Ignition-Proof, and Division 2				
16	CSA (C/US) Intrinsically Safe				
K6	CSA (C/US) Explosion-proof, Dust Ignition-Proof, Intrinsically Safe, and Division 2				
	Display type				
M5	LCD display				
	Other options				
PD	Pressure Equipment Directive (PED)				

Table 18. Rosemount 8600 Vortex Flowmeter Ordering Information

The Standard offering represents the most common models and options. These options should be selected for best delivery. The Expanded offering is subject to additional delivery lead time.

	Remote electronics			
R10	Remote electronics with 10 ft (3,0 m) cable			
R20	Remote electronics with 20 ft (6,1 m) cable			
R30	Remote electronics with 30 ft (9,1 m) cable			
R33	Remote electronics with 33 ft. (10 m) cable			
R50	Remote electronics with 50 ft (15,2 m) cable			
RXX ⁽²⁾	Remote electronics with customer-specified cable length (up to 75 ft (23 m) maximum)			
Transient protection				
T1	Transient protection terminal block			
Alarm mode				
C4	NAMUR alarm and saturation values, high alarm			
CN	NAMUR alarm and saturation values, low alarm			
Ground screw assembly				
V5	External ground screw assembly			
Advanced PlantWeb™ Diagnostics				
DS1	Internal Flow Simulation			
Certification options				
Q4	Calibration data sheet per ISO 10474 3.1B and EN 10204 3.1			
Q8	Material traceability certification per ISO 10474 3.1B and EN 10204 3.1			
Q76	Certification of Positive Material Identification			
QBR	India Boiler Regulation (IBR)			
	MC certification			
CM	China Metrology Cert			
RM	Russian Metrology Cert			

Table 18. Rosemount 8600 Vortex Flowmeter Ordering Information

 $The Standard\ of fering\ represents\ the\ most\ common\ models\ and\ options.\ These\ options\ should\ be\ selected\ for\ best\ delivery.$ The Expanded offering is subject to additional delivery lead time.

	Quick Start Guide (QSG) language options (default is English)	
YM	Chinese (Mandarin)	
YR	Russian	
YA	Danish	
YC	Czech	
YD	Dutch	
YF	French	
YG	German	
YB	Hungarian	
YI	Italian	
YW	Swedish	
YS	Spanish	
YP	Portuguese	
	Typical Model Number: 8600 F 020 S A1 N 1 D 1 M5	

On 1-in. (25 mm) to 3-in. (80 mm) line sizes the dimensions for PN16 and PN40 flanges are identical and therefore all flanges are marked PN40
 XX is a customer specified length in feet.

00813-0100-4860, Rev BE

Emerson Automation Solutions

7070 Winchester Circle Boulder, Colorado USA 80301 T: +1 800-522-6277 T: +1 303-527-5200 F: +1 303-530-8459 Mexico: 52 55 5809 5300 Argentina: 54 11 4837 7000

Brazil: 55 15 3413 8147 Chile: 56 2 2928 4800

Emerson Automation Solutions

Central Europe: +41 41 7686 111 Eastern Europe: +41 41 7686 111 Dubai: +971 4 811 8100 Abu Dhabi: +971 2 697 2000 France: 0800 917 901 Germany: +49 (0) 2173 3348 0 Italy: 8008 77334

The Netherlands: +31 (0) 70 413 6666 Belgium: +32 2 716 77 11 Spain: +34 913 586 000

U.K.: 0870 240 1978 Russian/CIS: +7 495 981 9811

Emerson Automation Solutions

Australia: (61) 3 9721 0200 China: (86) 21 2892 9000 India: (91) 22 6662 0566 Japan: (81) 3 5769 6803 South Korea: (82) 31 8034 0000 Singapore: (65) 6 363 7766

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount, 8600, 8700, 8800 marks are marks of one of the Emerson Automation Solutions family of companies. All other marks are property of their respective owners.



^{©2019} Rosemount, Inc. All rights reserved.