


STAY CURRENT with Best-In-Class Vibration Technology

Exclusive Trade-Up Offer
Significant Discount
AMS 2140



CSI 2130



AMS 2140

AMS 2140

Keeping pace with today's digital transformation can be a challenge, but it is even harder when your existing technology is already out of date. Now you can catch up and move forward!

For a limited time, Emerson is offering an exclusive opportunity to **upgrade your existing CSI 2130 Machinery Health Analyzers to the AMS 2140** through the Stay Current program – at a significant discount!

Analyzers: Trade-up your existing CSI 2130 analyzers for AMS 2140 analyzers.



Stay Current - How does it work?

What: Trade-in CSI 2120 or 2130 for standard 4-ch AMS 2140 Trade-Up for a significant discount.

- The AMS 2140 Trade-up unit does not include wireless option or accessory items like accelerometers, magnets, or accelerometer cables (these may be purchased additionally)
 - Equivalent firmware to your CSI 2130
 - Equivalent hazardous rating to your CSI 2130
- 1-year AMS 2140 product support included
- AMS Machinery Manager product support
- Product Support reactivation fee waived

Operating Systems, Software and Platform Support	CSI 2130	AMS 2140
Windows Server 2022 Windows Server 2019, Windows Server 2016, Windows 11, or Windows 10	No	Yes
Dashboard, larger database, increased AL sets, etc.	Not available	Available in current release of AMS Machinery Manager

Analyzer Features	CSI 2130	AMS 2140
Simultaneous Channels plus Phase	2	4
Four-channel Route	No	Yes
Four-channel Simultaneous Display	No	Yes
Four-channel Transient	No	Yes
Four-channel ODS/Modal	No	Yes
Four-channel Volts/Displacement	No	Yes
Weight	4.5lbs	10% Lighter (3.95lbs)
Thickness	1.88"	20% Thinner (1.5")
Screen Size (measured diagonally)	7.1"	6% Larger (7.5")
Touchscreen	No	Yes
Screen Brightness	13x Dimmer	13x Brighter
Battery Life	5-8 hrs	100% More (10+ hrs)
Lithium-Ion Battery	No	Yes
Wireless Communication	No	Yes
Bluetooth Wireless Headphones	No (wired)	Yes
Backlit Keypad	No	Yes
Data Collection Speed	~30% Slower	~30% Faster
Triax Collection	Muxed	Simultaneous
Auto Light Sensor	No	Yes
Built-in Stand	No	Yes
External Battery Charger	No	Yes
Quick Connect Shoulder Strap	No	Yes

©2024, Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. The AMS logo is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while diligent efforts were made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

Contact Us

🌐 www.emerson.com/ams