

# Shell Ethylene Plant Increases Availability and Improves Efficiency Using Rosemount Dual Vortex Flowmeters on Steam Measurements

## RESULTS

- Improved plant efficiency by 2%
- Reduced Maintenance Cost
- Increased plant availability



*Rosemount's non – clog design vortex meter reduces maintenance costs while improving plant efficiency.*

## APPLICATION

The Shell Moerdijk ethylene plant mixes Light Distillate Feedstock (LDF) - such as naphtha or ethane - and steam to heat the mixture to temperatures sufficient to crack the LDF into basic feedstock such as ethylene.

Dual steam flow measurements are required for advanced process control, and the plant safety instrumented system (SIS).

## CUSTOMER

Shell Chemical Moerdijk Ethylene Plant - one of the largest ethylene plants in Europe

## CHALLENGE

Shell Chemicals was looking for a more reliable steam flow measurement in order to improve operations and increase plant uptime. In addition they needed built in redundancy with an independent measurement for process control, and the safety system instrumented system. The installed DP flow based system was not providing the reliability they needed.

The ethylene production process operates at high temperatures and as part of the process carbon and coke deposits are created which get re-circulated with the process water and steam. The particles, when recycled in the steam, would constantly block the impulse lines of the installed DP flow based measurement system decreasing measurement reliability.

A monthly schedule of cleaning each flowmeter had been established to overcome this problem, to remove these deposits and ensure measurement reliability. As a result, the plant experienced high maintenance cost, and was unable to optimize their production performance. In addition, plant availability was reduced. All of these factors combined to reduce plant profitability.



*A Rosemount 8800 Dual Vortex installed.*

**ROSEMOUNT**

For more information:  
[www.rosemount.com](http://www.rosemount.com)

## SOLUTION

Shell decided to first undertake a three month trial with a Rosemount 8800 dual vortex flowmeter on one of the furnace lines. The flowmeter provided a reliable measurement with no problems and no cleaning required. Following the success of the trial, all twenty furnaces were scheduled to be equipped with the Rosemount dual vortex flowmeters. Unlike other manufacturer's vortex flowmeters, the Rosemount dual vortex flowmeter has an all-welded body design with no crevices, process seals, or pockets where particles might collect and cause measurement error or failure. In addition, as a dual sensor unit, the 8800 provides two separate flow measurements, enabling one sensor to provide the process control signal, and the other to be used in the SIS loop.

The first eight furnaces have now been in operation for over 8 years. During this time none of the units needed to be removed for cleaning eliminating the monthly required maintenance cost and improving plant availability. With the improved measurement and ability to better control the process, a 2% improvement in plant efficiency has been realized. Finally, the dual sensor unit provided reduced installation cost by eliminating the need for two separate meters with the required upstream and downstream piping.

## RESOURCES

### Emerson Process Management Chemical Industry

<http://www2.emersonprocess.com/en-US/plantweb/customerproven/Pages/Chemical.aspx>

### Rosemount 8800 Series Vortex Flowmeter

<http://www2.emersonprocess.com/en-US/brands/rosemount/Flow/Vortex-Flowmeters/Pages/index.aspx>

**“Rosemount dual vortex meters provide two flow measurements for process control and safety instrumented systems reducing installed cost.”**



The Rosemount 8800 Dual Vortex

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which can be found at [www.rosemount.com/terms\\_of\\_sale](http://www.rosemount.com/terms_of_sale). We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

The Emerson logo is a trade mark and service mark of Emerson Electric Co. Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. PlantWeb is a registered trademark of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.

#### Emerson Process Management

**Rosemount Incorporated**  
8200 Market Boulevard  
Chanhausen, MN 55317 USA  
[www.rosemount.com](http://www.rosemount.com)  
Tel (USA) +1 800 522 6277  
Tel (International) +1 (3952) 906-8888  
Fax +1 (952) 906-8889

#### Emerson Process Management

Blegistrasse 23  
P.O. Box 1046  
CH 6341 Baar  
Switzerland  
Tel +41 (0) 41 768 6111  
Fax +41 (0) 41 768 6300

#### Emerson FZE

P.O. Box 17033  
Jebel Ali Free Zone  
Dubai UAE  
Tel +971 4 811 8100  
Fax +971 4 886 5465

#### Emerson Process Management Asia Pacific Private Limited

1 Pandan Crescent  
Singapore 128461  
T (65) 6777 8211  
F (65) 6777 0947  
Enquiries@AP.EmersonProcess.com

#### Emerson Process Management Latin America

**Multipark Office Center**  
Multipark Office Center  
Turrubares Building, 3rd & 4th floor  
Guachipelin de Escazu, Costa Rica  
T+(506) 2505-6962  
[international.mmcam@emersonprocess.com](mailto:international.mmcam@emersonprocess.com)

**ROSEMOUNT**<sup>®</sup>

For more information:  
[www.rosemount.com](http://www.rosemount.com)



**EMERSON**<sup>™</sup>  
Process Management