

Both of these are customized.

One of them saves you money.



Featuring a highly configurable modular design, increased flow and relief performance, and reduced ownership costs, the Emerson CS800IQ regulator is miles ahead of the competition. Accelerate training, simplify installation, reduce maintenance, and easily shift between a wide range of overpressure protection options. Choose your own configuration, trim, body size and application, for a perfect fit — no matter where the road takes you. Take the CS800IQ for a test drive — visit fishercommercialservice.com for an interactive demonstration.



D351941X012 Product Advertisement © 2011 Emerson Process Management Regulator Technologies, Inc. All rights reserved.
Fisher, Emerson Process Management, and the Emerson Process Management design are marks of the Emerson Process Management group of companies.

EMERSON. CONSIDER IT SOLVED.™