# Fisher<sup>™</sup> EH and EHA Control Valves

### EH (globe)

■ EHS (NPS 1-1/2x1 through 8x6), ■ EHD (NPS 2 through 20), and ■ EHT (NPS 2 through 16x12)

### EHA (angle)

■ EHAS (NPS 3 through 6), ■ EHAD (NPS 3 through 8), and ■ EHAT (NPS 3 through 8)

## **EH Series Valves**

These valves are specially designed for high-pressure applications. Fisher EH valve configurations incorporate proven techniques in flow-stream contouring for higher capacities and in valve trim design for reliability in severe applications.

The temperature limits of EHT valves can be extended above 232°C (450°F) by using PEEK (PolyEtherEtherKetone) anti-extrusion rings in combination with a spring-loaded PTFE seal. The PEEK anti-extrusion rings expand to close off the clearance gap between the plug and the cage where the PTFE seal may extrude at high temperatures and pressures. The temperature limits are extended to 316°C (600°F) for non-oxidizing service and to 260°C (500°F) for oxidizing service.

Unless otherwise noted, all NACE references are to NACE MR0175-2002. Contact your <u>Emerson sales</u> <u>office</u> for information on NACE MR0175/ISO 15156 or NACE MR0103.

## Features

 Improved Cage Design—Drilled-hole cages, offering excellent strength and additional resistance to destructive vibration, are standard. Special materials of construction are readily available.



Fisher ET Valve with 685 Piston Actuator

X1083-1



Fisher EHT Valve with 585C Actuator

 Piping Economy—The availability of expanded end connections on EH valves may eliminate the need for line swages while accommodating oversized piping arrangements.



FISHER

www.Fisher.com

- O-ring Seat Ring Gasket Construction—Use of O-ring construction provides excellent shut-off with minimal seat ring installation torques for temperatures up to 232°C (450°F). O-ring construction is standard on EHT valves. The flat sheet seat ring gasket construction is available for elevated design temperatures and/or NACE constructions where a suitable O-ring material is not available.
- Increased Pressure/Temperature Ratings—Steel EH and EHA valves with buttwelding end connections have Intermediate Standard Ratings. With nondestructive testing, these valves can conform to ASME Intermediate Special Ratings, which allow even higher pressure/temperature applications. See table 7 for specific ratings.
- Long Trim Life—Hardened materials of construction for the cage, valve plug, cage guiding, and other trim parts are standard for all applications, providing excellent wear resistance. In all applications, rugged cage guiding provides increased valve plug stability. Increased stability results in reduced vibration and other mechanical stresses, which contributes to long trim life.
- Control of Low Flow Rates/Tight Shut-off— Micro-Form or Micro-Flute valve plugs (figure 5 or 6) provide superb rangeability in high-pressure, low-flow applications. A choice of several restricted port diameters helps match valve capacity to required flow, helps provide necessary control with full travel, and helps prevent throttling near the seat.
- 1. For EHA valves only, and in low-flow applications where cavitation damage may occur, the Micro-Flat

style valve plug can be used. For low-flow applications where cavitation damage may occur and the minimum required  $C_v$  is equal to or greater than 0.05, Cavitrol III with Micro-Flat trim can be used in both EH and EHA valves. Please contact your <u>Emerson sales office</u> for more information.

- 2. For soot-blower applications, a special trim design is available to address noise, vibration, tight shutoff, and thermal cycling which is seen in this application. Please contact your Emerson Automation Solutions sales office for more information.
- High-Temperature, Class V Shutoff—Use of the metal C-seal (see figure 17) permits Class V shutoff up to 593°C (1100°F) for up to 4-3/8 inch port in CL2500 rated valves and 5-3/8 inch port in CL1500 rated valves. The metal Bore Seal will permit Class V shutoff up 593°C (1100°F) for 2-7/8 inch ports and larger.
- Excellent Stem Sealing—HIGH-SEAL packing systems provide excellent sealing to conserve valuable or hazardous process fluid and to protect against the emission of hazardous or polluting fluids to atmosphere. This system (figure 1) features graphite packing material and heavy-duty live loading.
- High Capacity—Careful consideration of aerodynamic and hydrodynamic principles in the design of the flow stream passages results in 30 to 40 percent higher capacity than conventional valves with comparable port sizes and travels.

(continued on page 6)

#### **Table of Contents**

EH Series Valves 1
Features 1
Specifications
NPS 1-1/2 x 1 through 6 Globe Valves, NPS 3
through 8 Angle Valves 8
Trims (NPS 1-1/2 x 1 through 6 Globe Valves 9
NPS 8 through 14 Globe Valves
Principle of Operation
(NPS 8 through 14 Globe Valves)
NPS 20 Globe Valves 12

Custom Design Capability (NPS 20 Globe Valves)	13
C-seal Trim Description	14
Bore Seal Description	15
Fisher TSO (Tight Shutoff) Trim Capabilities	16
Trim Selection Guidelines	19
Material Selection Guidelines	20
Pressure/Temperature Limits	27
Installation	30
Dimensions	31

#### Specifications

#### **Available Configurations**

#### See table 1

**Common Characteristics:** EH valves are single-port, high-pressure, globe-style valves with metal seats, cage guiding, and push- down- to- close valve plug action. EHA valves are angle versions of EH valves EHD/EHAD: Uses a balanced valve plug<sup>(1)</sup> with graphite valve plug piston rings; also, see tables 4 and 5 EHS/EHAS: Uses an unbalanced valve plug. For low-flow applications, smaller valve sizes are available with specialized valve plug designs. See tables 4<sup>(1)</sup> and 5 EHT/EHAT: Uses a balanced valve plug<sup>(1)</sup> with a pressure-assisted PTFE valve plug seal ring; also, see tables 4 and 5

#### NPS 20 Valve Rating

■ Intermediate Standard Class 2185 (per ASME B16.34) or ■ other ratings available per customer specifications

#### Valve Sizes

■ Globe Valves: Tables 4 and 6

Angle Valves: Table 5

#### End Connection Styles<sup>(2)</sup>

Buttwelding Ends (BWE): See table 6 for all available ASME B16.25 schedules that are compatible with ASME B16.34 pressure/temperature ratings Flanged Ends: ■ CL900, ■ CL1500, or ■ CL2500 ■ ring-type joint (RTJ) or ■ raised-face (RF) flanges according to ASME B16.5. Flanged ends for EHA valves are available in CL900 and 1500 only Socketweld Ends (SWE): See table 6 for those valve sizes available with socketweld end connections according to ASME B16.11 that are compatible with ASME B16.34

#### Maximum Inlet Pressures and Temperatures<sup>(2,3)</sup>

Consistent with applicable CL900, 1500, or 2500 pressure/temperature ratings (for EH valves) according to ASME B16.34 unless limited by individual temperature limits shown in the Material Temperature Capabilities specification<sup>(7)</sup> or in figure 20.

In addition, both steel EH and EHA valves with BWE connections have increased pressure/ temperature ratings as shown in table 7

#### Maximum Pressure Drops<sup>(3)</sup>

Valve With Standard Cage: See figures 20, 21, and 22 Valve With Cavitrol<sup>™</sup> III Cage: 149 bar (2160 psi) for two-stage cage and 207 bar (3000 psi) for three-stage cage. Consult\_Fisher Bulletin 80.2:030, Fisher Cavitrol III One-, Two-, and Three-Stage Trims (D100196X012) for more information Valve With DST Trim:

■ 103 bar (1500 psi) for three-stage trim,

■ 207 bar (3000 psi) for four-stage trim, and

■ 289 bar (4200 psi) for six-stage trim

Consult Fisher bulletin 80.2:021, Fisher Dirty Service Anti-Cavitation Trim (DST) (<u>D102310X012</u>) for more information

With Whisper Trim<sup>M</sup> III and Whisper NXG Trim Cage: 0.999  $\Delta P/P_1$  maximum for levels A1 through D3 With WhisperFlo<sup>M</sup> Trim: Levels X, Y, and Z: 0.999  $\Delta P/P_1$  maximum

Levels X, Y, and Z:  $0.999 \Delta P/P_1$  maximu

#### **Construction Materials**

All Except NPS 20 Valve Body and Bonnet: ■ WCC steel, ■ LCC steel, ■ WC9 chrome-moly steel, C12A chrome-moly alloy, or ■ CF8M (316 SST or 316H SST for service above 538°C [1000°F]) *Trim:* Trim materials are listed in table 10 and 11. Special materials for trim and valve body are available. Please consult your Emerson sales office Other Parts: See tables 12 and 13 Yoke Temperature Limit (NPS 8 to 20 Valves): Standard bonnet with cast iron yoke is limited to 537°C (1000°F) NPS 20 Valve Valve Body and Bonnet: SA 217 Grade WC9 steel Cage: Cast M152 SST Valve Plua: CF8M (316 stainless steel) with allov 6 seat and quide Seat Ring: CF8M with CoCr-A (allov 6) seat or N06600 with CoCr-A seat Seat Ring Bolting: N07718 Valve Stem: SA 286 Grade 660 Condition 2 stainless steel or **o**ther materials upon request Piston Rings: Graphite Cage & Seat Ring Gaskets: Silver-plated N04400 Body/Bonnet Bolting: ■ B7/2H, ■ B16/Gr-7 Packing Rings: Carbon/graphite composition, graphite. and zinc Packing Box Bushing: Graphite Packing Box Flange, Studs, and Nuts: S31600 (316 stainless steel) (other materials are available on request) Packing Springs: G61500 (6150 steel), ■ S17700 (17-7 stainless steel), or ■ N07718

#### **Shutoff Classifications**

#### See table 9

For NPS 20 valves, one-half of Class IV leakage (0.005% of valve capacity at full travel) per ANSI/FCI 70-2 and IEC 60534-4

- continued -

#### Specifications (continued)

#### Material Temperature Capabilities<sup>(3)</sup>

EHD/EHAD and EHS/EHAS: Up to 593°C (1100°F) unless limited by selection of standard trim materials (table 10 and 11 and figures 20, 21, and 22), Cavitrol III, Whisper NXG Trim and Whisper Trim III trim materials (table 10), or other parts (table 12)

EHT/EHAT: Up to 316°C (600°F) unless limited by selection of standard trim materials (tables 10 and 11 and figures 20, 21, and 22), Cavitrol III, Whisper NXG Trim, and Whisper Trim III trim materials (table 10), or other parts (tables 12 and 13)

#### **Flow Characteristic**

Standard Cage: ■ Equal percentage, ■ modified equal percentage<sup>(4)</sup>, or ■ linear Micro-Form Valve Plug (for EHS and EHAS only): ■ Equal percentage or ■ modified equal percentage<sup>(4)</sup>. Micro-Flute Valve Plug (for EHS and EHAS only): ■ Equal percentage or ■ modified equal percentage<sup>(4)</sup> Micro-Flat Valve Plug (EHAS only): ■ Linear Cavitrol III, Whisper NXG Trim, Whisper Trim III, or WhisperFlo: ■ Linear Special cages: Special characterized flow characteristic

cages are available. Please consult your <u>Emerson sales</u> office

#### **Flow Direction**

Standard Cage

- EHD: Normal flow down<sup>(8)</sup>
- $\blacksquare$  EHS: Normal flow up<sup>(5)</sup>
- $\blacksquare$  EHT: Normal flow down<sup>(8)</sup>
- EHAD: Normal flow down
- EHAS: Normal flow up
- EHAT: Normal flow down

Cavitrol III Cage: Flow down

Whisper NXG Trim or Whisper Trim III cage: Flow up

WhisperFlo Trim: Flow up

For NPS 20 Valves: ■ Flow up through seat ring and out through cage openings (for standard and Whisper cages)

#### **Flow Coefficients**

See Fisher Catalog 12 section 1

#### Noise Levels

See Fisher Catalog 12, section 3 for noise predictions methods

#### NPS 20 Valve Maximum Flow Coefficient

Approximately 92,000  $\rm C_g$  or 2600  $\rm C_v$  for modified equal percentage characteristics

#### Port Diameters

See tables 17 and 18 for NPS 1 through 6 for NPS 1 through 6

NPS 8 and 10x8 Valves

*CL1500:* 178 mm (7 inch) port diameter *CL2500:* 137 mm (5.375 inch) port diameter **NPS 12, 14, and 14x12 Valves** *CL1500:* 254 mm (10 inch) port diameter **NPS 16x12 Valves** *CL1500:* 254 mm (7 inch) port diameter *CL2500:* 254 mm (10 inch) port diameter *CL2500:* 254 mm (10 inch) port diameter **NPS 20 Valves:** 355.6 mm (14 inches)

#### Valve Plug Travel and Stem Diameters<sup>(9)</sup>

See tables 14, 17, and 18

**5 Inch** H<sup>(10)</sup> **Boss Diameter:** 31.8 mm (1.25 inches) stem diameter

7 Inch Boss Diameter: 50.8 mm (2 inches) stem diameter

NPS 20 Valves: Valve Plug Travel: 85.7 mm (9.125 inches) Valve Stem Diameter: 50.4 mm (2 inches)

#### **Bonnet Style**

■ Standard bonnet (figures 3 and 4) for all valve sizes, standard bonnet with cast iron yoke is limited to 537°C (1000°F)

■ Optional Style 1 extension bonnet for NPS 1 and 2 globe valves, see figure 24

#### Packing Arrangements

■ Single, ■ double, and ■ leakoff standard packing arrangements, or optional ■ HIGH-SEAL packing systems; see Fisher Bulletin 59.1:061, ENVIRO-SEAL<sup>™</sup> and HIGH-SEAL Packing Systems for Sliding-Stem Valves (<u>D101633X012</u>)

- continued -

#### Specifications (continued)

Yoke Boss Diameters for Actuator Mounting See table 19	V shutoff for EHT above 232°C (450°F) to 316°C (600°F) by using PEEK anti-extrusion rings, ■ Class V
NPS 8 and 10 CL2500 Valves: 127 mm (5 inch H <sup>(10)</sup> ) yoke boss diameter All Other Sizes and Ratings: ■ 127 mm (5 inch H <sup>(10)</sup> ) or ■ 178 mm (7 inch) yoke boss diameter NPS 20 Valve: 178 mm (7 inches)	shutoff for EHD up to 593°C (1100°F) using C-seal trim or Bore Seal (refer to table 9, ■ lubricator/isolating valve for packing lubrication, and ■ liner with integral seat ring (EHA Series valves only)
Approximate Weight See tables 20 and 21	Options for NPS 20 Valve
<ul> <li>Optional Safety Instrumented System Classification</li> <li>■ EHD, EHS, and EHT: SIL3 capable for NPS 1-1/2 through 20 - certified by exida Consulting LLC</li> <li>■ EHAD, EHAS, and EHAT: SIL3 capable for NPS 3 through 8 - certified by exida Consulting LLC</li> <li>Options</li> <li>■ Flat sheet seat ring gasket constructions<sup>(6)</sup>, ■ driver for removing and installing of seat ring retainer, ■ Class</li> </ul>	<ul> <li>Tool Kit: Includes tools useful during maintenance [3 sets of lifting eyes, 2 hoist rings, flushing plate with either ■ two O-rings for use when flushing fluid is 149°C (300°F) or less or ■ two silver-plated N04400 gaskets for use when flushing fluid is over 149°C (300°F), valve stem lifting nut, lapping fixture and handle, and tamping tools]</li> <li>Special Cage Characterization: Standard, Cavitrol, or Whisper Trim cage openings as necessary to provide the required installed flow characteristic</li> </ul>

pressure drops. See figures 7 and 12. Diverter cone valve plug construction is also used for this of the analysis of the analy

## Features (continued)

- Long Thermal-Cycle Life—The seat ring design minimizes operational stresses, thereby reducing chances of distortion and resultant leakage caused by temperature cycling. The hung cage design allows thermal expansion of the cage without affecting the seat ring gasket loading.
- Operational Economy—Balanced trim constructions reduce forces acting on the valve plug, reducing actuator thrust requirements and permitting the use of smaller actuators. This makes the NPS 8 -14 EH Series valves economical for high-pressure, high-flow service. Actuator selection for NPS 20 valves can be made from electromechanical or electrohydraulic styles that use readily available power sources.
- Reliability—All aspects of the control valve (material selection, trim components, packing, and control accuracy) are designed, built, and tested to assure performance and reliability. Extensive metallurgical evaluation results in state-of-the-art cage, valve plug, and stem materials that help ensure trim life and dependable performance.
- Control Accuracy—The NPS 20 cage and valve plug deliver accurate control of high pressure and high capacity flow. Each cage has milled openings and is flow tested for the required flow characteristic.
   With precise cage openings, accurate installed characteristics result; valves in parallel have the same flow at the same plug position. The cone-shaped plug reduces fluid turbulence, ensure plug stability, and aids positioning accuracy.
- Easy Maintenance—The bonnet lifts off to allow trim access. The separate seat ring and cage allow parts removal and maintenance. The globe configuration reduces the uneven trim wear and resultant maintenance downtime normally associated with slant configurations. Installation with the stem vertical above the bonnet also makes trim removal and installation easy.
- Control Flexibility—Special cage characterization (standard, Whisper Trim, or Cavitrol trim) can be supplied to satisfy almost any combination of flow and noise or cavitation abatement. Cage

characterization and efficient flow passages provide close control for low flow, high pressure drop and high flow, low pressure drop conditions. A choice of actuator styles allows wide selection of power and control capabilities.



#### Figure 2. Seat Ring Gasket Constructions



NOTES:

1 Preferred for all other body constructions where temperature allows.

#### Table 1. Availability Chart

Valve Size, NPS <sup>(1)</sup>	CL1500	CL1500 Intermediate	CL2500	CL2500 Intermediate				
1-1/2 x 1			EHS	EHS				
2 x 1			EHS					
2				EHD, EHS, EHT				
3 x 2			EHD, EHS, EHT	EHD, EHS, EHT				
3		EHAD, EHAS, EHAT EHAD, EHS, EHT EHAD, EHAS, EHAT		EHD, EHS, EHT EHAD, EHAS, EHAT				
4 x 3			EHD, EHS, EHT					
4		EHAD, EHAS, EHAT	EHD, EHS, EHT EHAD, EHAS, EHAT	EHD, EHS, EHT EHAD, EHAS, EHAT				
6 x 4		EHD, EHS, EHT						
6		EHAD, EHAS, EHAT	EHD, EHS, EHT EHAD, EHAS, EHAT	EHD, EHS, EHT EHAD, EHAS, EHAT				
8 x 6			EHD, EHS, EHT					
8	EHD, EHT	EHD, EHT EHAD, EHAT	EHD, EHT EHAD, EHAT	EHD, EHT				
10 x 8	EHD, EHT	EHD, EHT	EHD, EHT	EHD, EHT				
12	EHD, EHT	EHD, EHT	EHD, EHT	EHD, EHT				
14			EHD, EHT					
14 x 12	EHD, EHT	EHD, EHT	EHD, EHT	EHD, EHT				
16 x 12			EHD, EHT					
20	EHD		EHD <sup>(2)</sup>					
1. Two numbers indicate end connection by nominal valve size. For example, 3 x 2 indicates 3 inch end connection with NPS 2 valve size.								

Table 2. Liquid Flow Coefficients, C<sub>v</sub>, at Maximum Travel with Equal Percentage Cage (Modified Equal Percentage Characteristic) (NPS 8 through 14 Valves)<sup>(1)</sup>

VALVE	PRESSURE	VALVE S	IZE, NPS			
DESIGN	RATING	8 and 10x8	12 and 14x12			
EHD, EHT	CL1500	912	1830			
	CL2500	584	1010			
1. See Fisher Catalog 12 for additional sizing data.						

#### Figure 3. NPS 3 Fisher EH Valve with 657 Actuator



W3387

Figure 4. Fisher EHD Valve Body Assembly



W3379-1

### NPS 1-1/2 x 1 through 6 Globe Valves NPS 3 through 8 Angle Valves

EH Series valves (figure 3) offer higher capacities, rugged cage guiding, hardened trim materials, and are available with special trims for noise attenuation and cavitation abatement. An EH valve package can be created for specific service conditions from a variety of special features, including oversized ends, intermediate ratings, special trim materials, and special trim configurations.

Because of flow capacity and severe service capabilities, both EH and EHA valves are used for many high-pressure applications in process industries such as power generation, hydrocarbon production, chemical processing, and refining.

The EHD (figure 4) uses a balanced valve plug and is well suited for general applications where extremely tight shutoff is not required.

The EHS (figures 5 and 6) has an unbalanced valve plug and provides up to Class V shutoff.

The EHT has a balanced valve plug and offers up to Class V shutoff with process temperatures below  $232^{\circ}C$  ( $450^{\circ}F$ ).

EHA valves — EHAD, EHAT, and EHAS — are angle versions of the EH valve.

EH valves are available in CL2500 ratings. EHA valves are available in CL2500. Because these valves feature a thicker body wall, both EH and EHA valves are available with intermediate ratings. See the Features section in this bulletin.

EHA valves provide many of the same features available with EH valves. One important feature is the availability of special trims for aerodynamic noise attenuation, for cavitating liquid service, and for sour service. W5042-1

### Trims (NPS 1-1/2 x 1 through 6 Globe Valves)

Figure 5. Fisher EHS Trim with Micro-Form Valve Plug



Figure 6. Fisher EHS Trim with Micro-Flute Valve Plug



Figure 7. Diverter Cone Plug Used in NPS 6 Fisher EHD and EHT Valves (Flow Up Only)



W5043-1

NOTE: Diverter cone valve plug used for flowing △P> 207 bar (3000 psi) or for Whisper Trim III and Whisper NXG trim Level A, B, or C cages.



#### Figure 8. Fisher EHD Valve Assembly (NPS 8 through 14 Globe Valves)

### Figure 9. NPS 8 Fisher EH Valve with Welded Pipe Expanders and 585C Actuator



### NPS 8 through 14 Globe Valves

EH Series control valves (figure 9) are large, high-pressure globe valves that incorporate proven techniques in flow-stream contouring and in seat ring and valve plug design. These features, along with rugged cage guiding and hardened trim materials, make the EH Series valves reliable high-capacity valves.

These valves are used for many high-pressure applications in the power, process, oil production, chemical, refining, and other industries. The EHD valve (figure 8) is well-suited to general applications where extremely tight shutoff is not required, and the EHT valve (figure 10) offers up to Class V shutoff for applications with relatively low process temperatures.

### Principle of Operation (NPS 8 through 14 Globe Valves)

EHD and EHT valves, shown in figures 8 and 10, are balanced valve designs. When the valves are opening or closing, pressure registers on top of the valve plug through the balancing holes in the plug. The force of the pressure on top of the plug balances the force of the pressure on the bottom of the plug to reduce the actuator force required.

Figure 10. Fisher EHT Trim (NPS 8 through 14 Globe Valves)



Figure 11. Fisher EHD Trim with Whisper Trim III Level D Cage (NPS 8 through 14 Globe Valves)



Figure 12. Diverter Cone Valve Plug Used in Fisher EHD and EHT Valves (NPS 8 through 14 Globe Valves, Flow Up Only)



DIVERTER CONE VALVE PLUG USED IN BOILER FEEDWATER SERVICE FOR FLOWING  $\triangle P$ > 1000 PSI (69 BAR) AND IN OTHER APPLICATIONS FOR FLOWING  $\triangle P$ > 138 BAR (2000 PSI) OR FOR WHISPER TRIM III AND WHISPER NXG TRIM LEVEL A, B, OR C CAGES

Figure 13. Seat Ring Gasket Constructions (NPS 8 through 14 Globe Valves)

W4430-



SPIRAL WOUND GASKET CONSTRUCTION (STANDARD CONSTRUCTION FOR HIGH TEMPERATURE APPLICATIONS)



W4428-1



#### Figure 14. Sectional of NPS 20 Fisher EHD Control Valve Assembly

### NPS 20 Globe Valves

The NPS 20 EHD control valve (figure 15) is a large, high-pressure, single-port, globe valve designed to closely and dependably control high-pressure, high-temperature media in the power and hydrocarbon industries. For example, NPS 20 EHD control valves are used in sliding pressure systems to control high-pressure steam in fossil-fueled power plants.

Advanced, yet successfully field-proven, the NPS 20

EHD control valve usually incorporates special design features to satisfy specific customer requirements. For example, figure 14 illustrates a specially characterized cage. Both Whisper Trim cage holes and large cage windows provide the customer-required flow characteristic. Additionally, the drilled Whisper Trim holes in the cage provide noise abatement.

Standard construction details such as the cone-shaped valve plug and stem assembly, separate seat ring, and HIGH-SEAL packing arrangement are also shown in figure 14.

Figure 15. NPS 20 Fisher EHD Valve with **Electromechanical Actuator** 





## Figure 16. Custom Design Sequence

### **Custom Design Capability** (NPS 20 Globe Valves)

A3350

Sliding pressure systems, as well as other control systems, have specific performance characteristics that require special control valve constructions. These special constructions must perform dependably and provide accurate system operation and plant reliability.

As shown in figure 16, the basic NPS 20 EHD valve configuration can be designed to meet customer specifications. Special cage characterization and actuator/valve response characteristics can be designed and then confirmed through exhaustive testing and evaluation. Flow testing of these large valves takes place at the Emerson Innovation Center, Fisher Technology, the largest facility of its kind in the world.

The final control valve assembly provides reliable, dependable performance. This performance delivers controllability for not only the control valve but also the plant control system, sliding pressure or otherwise.

#### Figure 17. C-seal Trim



NOTES:

🕞 Reverse the orientation of the C-seal plug seal for proper shutoff when valve is used in a process with different fluid flow direction.

## **C-seal Trim Description**

With C-seal trim, a balanced valve can achieve high-temperature, Class V shutoff. Because the C-seal

plug seal is formed from metal (N07718 nickel alloy) rather than an elastomer, a valve equipped with the C-seal trim can be applied in processes with a fluid temperature of up to 593°C (1100°F).



### **Bore Seal Description**

The Bore Seal (figure 18) is available for the EHD only and employs a variation of the proven C-seal trim with enhancements for use with the larger port EH hung cage. The Bore Seal is required for Class V shutoff applications where the service temperature exceeds  $316^{\circ}C$  ( $600^{\circ}F$ ). See table 3 for availability and temperature limits.

The Bore Seal employs a metal C-shaped seal ring that

Table 3. Bore Seal Availabilit	v and Temperatu	e Limits (	(EHD only	v)
ruble of bore sear, tranabilit	y ana remperata	C LIIIICS		,,



is secured to the outside diameter of the valve plug. When the valve plug comes into contact with the seat ring to close the valve, the Bore Seal is compressed against the cage wall, thereby blocking a secondary leakage path that exists between the plug and cage wall. When the valve plug is not in contact with the seat ring (i.e. valve open), the Bore Seal is not engaged and the piston rings that are also secured to the outside diameter of the plug assume the role of blocking this secondary leakage path.

VALVE		TRIM	VALVE BODY	TEMPERA	FURE LIMIT	ANSI/FCI/IEC	
(PRESSURE CLASS)	VALVE SIZE, NPS	DESIGNATION <sup>(1)</sup>	MATERIAL	°C	°F	SHUTOFF CLASS	
		40	WCC	-29 to 427	-20 to 800		
EHD (CL1500-CL2500)		49	WC9	-29 to 593	-20 to 1100		
	4 and 6	50		20 to 427	20 to 000		
	4 anu o	60	WCC/WC9	-29 10 427	-2010800		
			62	WCC	-29 to 427	-20 to 800	
		03	WC9	-29 to 593	-20 to 1100	v	
		75	WCC/WC9	-29 to 427	-20 to 800		
	0.10.12	05	WCC	315 to 427	600 to 800		
	8, 10, 12, and 14	8, 10, 12, and 14 95	WC9	315 to 593	600 to 1100		
		96	WCC/WC9	-29 to 427	-20 to 800	1	
1 See tables 11 and 13 f	or materials	•			•	•	

#### Figure 19. Typical Balanced TSO (Tight Shutoff) Trim



### Fisher TSO (Tight Shutoff) Trim Capabilities

TSO trim consists of a protected soft seat plus PEEK anti-extrusion rings with a spring-loaded PTFE plug seal. Used only in flow down applications, TSO trim offers unparalleled shutoff integrity, resulting in long plug and seat life.

See figure 19 and tables 8 and 9. For additional information contact your <u>Emerson sales office</u>.

	AVAILABLE CONFIGU	JRATIONS	VALVE SIZES (NPS) AND PRESSURE RATING					
Valve	Valve Plug	Cage	1-1/2 x 1, 2 x 1	2	3x2	3, 4 x 3	4,6x4	6,8x6
Design	Style	Style	CL2500	CL3273	CL2500	CL2500	CL2500	CL2500
	Micro-Form	Quick-Opening <sup>(2)</sup>	Х	Х	Х			
		Standard <sup>(3)</sup>		Х	Х	Х	Х	Х
EHS	Standard	Whisper Trim III, Whisper NXG Trim		х	х	х	х	х
	Standard	Cavitrol III: 2-stage 3-stage	X	 X	 X			
EHT		Standard <sup>(3)</sup>			Х	Х	Х	Х
	Chan dand	Whisper Trim III Whisper NXG Trim			х	Х	х	х
	Standard	Cavitrol III: 2-stage 3-stage			X	x x	x x	x x
		Standard <sup>(3)</sup>			Х	Х	Х	Х
EHD S	Standard	Whisper Trim III Whisper NXG Trim			х	х	x	х
X—Indicates available construction. 1. Two numbers indicate end connection by nominal valve size. For example, 3 x 2 indicates 3 inch end connection with NPS 2 valve size. 2. Linear cage used on NPS 2 and 3 x 2 valves. 3. Standard cages are equal percentage, modified equal percentage, and linear cages.								

#### Table 4. Available Globe Valve Configurations and Valve Sizes<sup>(1)</sup> (NPS 1-1/2 x 1 through 6 Globe Valves)

	AVAILABLE CONFIGURATIONS			VALVE SIZES (NPS) AND PRESSURE RATING		
Valve	Valve Plug	Cage	1-4	<b>6</b> <sup>(4)</sup>		
Design	Style	Style	CL2500	CL3230		
	Micro-Form	Quick-Opening <sup>(1)</sup>	χ(3)			
	Micro-Flute	Quick-Opening				
		Standard <sup>(2)</sup>	Х	Х		
EHAS	Standard	Whisper Trim III Whisper NXG Trim	Х	Х		
		Cavitrol III: 2-stage 3-stage				
		Standard <sup>(2)</sup>	X	Х		
EHAT	Standard	Whisper Trim III Whisper NXG Trim	Х	Х		
		Cavitrol III: 2-stage	X	Х		
		3-stage	Х	Х		
	Standard <sup>(:</sup>		X	Х		
EHAD	Standard	Whisper Trim III Whisper NXG Trim	Х	x		
X—Indicates available construction 1. Linear cage used on NPS 2 and 2. Standard cages are equal perce	n. 3 valves. entage, modified equal percentage, and	d linear cages.				

#### Table 5. Available Angle Valve Configurations and Valve Sizes (NPS 1 through 6 Angle Valves)

Not available in NPS 4 and larger.
 Intermediate CL3230. Contact your <u>Emerson sales office</u>.

#### Table 6. Globe Valve Sizes and End Connection Styles<sup>(1)</sup> (NPS 1-1/2 x 1 through 6 Globe Valves)

VALVE	CL2500 <sup>(2)</sup>								
SIZE,		BWE		CIM/E	DTI	DE			
NPS	SCH 80	SCH 160	SCH XXS	SVVE	кіј	кг			
1-1/2 x 1	Х		Х	Х	Х	Х			
2 x 1	Х		Х	Х	Х	Х			
2(3)			Х						
3 x 2	Х		Х		Х	Х			
3	Х		Х		Х	Х			
4 x 3	Х		Х		Х	Х			
4	Х		Х		Х	Х			
6 x 4	Х		Х		Х	Х			
6	Х		Х		Х	Х			
8 x 6	Х	Х			Х	Х			

X—Indicates available construction. 1. EN (or other) ratings and end connections can usually be supplied; consult your <u>Emerson sales office</u>. 2. For valve ratings of EH Series valves with BWE connections, refer to separate bulletin. Increased Pressure/Temperature Ratings for EH Series and EW Series Steel Valves (D100075X012 or <u>D100076X012</u>). 3. Intermediate CL3273 only.

#### Table 7. Increased Pressure/Temperature Ratings for Steel Fisher EH Series Globe Valves with Buttwelding End Connections<sup>(1)</sup>

VALVE SIZE,	CL1500	CL2500						
NPS	Intermediate Rating (ASME B16.34)	Intermediate Rating (ASME B16.34)						
1		3862 <sup>(2)</sup>						
1-1/2 x 1		3021						
2		3273						
3		2932						
4		3294						
6		2987						
8	1866	2943						
10x8	1568	2522						
12	1650	2940						
14 x 12	1650	2754						
1. See Fisher bulletin 59.1:026 ( <u>D100075X012</u> ) for additional information.								

#### Table 8. Port Diameters, Valve Plug Travel, Yoke Boss Diameters for TSO (Tight Shutoff) Trim

					PORT DIAMETER					
VALVE DESIGN	TRIM	IVIAX TRAVEL		TOKE DUSS SIZE		Nominal		Actual TSO		100% TRAVEL(1)
		mm	Inch	mm	Inch	mm	Inch	mm	Inch	
EHT NPS 6	CAV III 3-Stage CL2500	95.3	3.75	90 127	3-9/16 5	111	4.375	106	4.1875	0%
EHT NPS 6	Std CL2500	76.2	3	90 127	3-9/16 5	111	4.375	106	4.1875	5% (linear) 5% (equal %)
1. This column lists th	1. This column lists the percent reduction of published maximum C <sub>v</sub> of the trim listed in the TRIM column.									

#### Table 9. Shutoff Classifications per ANSI/FCI 70-2 and IEC 60534-4

Valve Design		Port Diame	eter, mm (inch)	ANSI/FCI Leakage Class		
		47.6 mm (1.8	75 in) and smaller	ll		
		58.7 mm (2.3125 inch) to 92.1 mm (3.625 in)		II—Standard		
EHD/EHAD EHD/EHAD EHD (CL1500) EHD (CL2500) EHS, EHAS, EHT, E EHS, EHAS, EHT, E	)			III—Optional		
		Port Diameter, mm (inch)           47.6 mm (1.875 in) and smaller           58.7 mm (2.3125 inch) to 92.1 mm (3.625 in)           111.1 mm (4.375 in) and larger           C-Seal - 73.0 (2.875 in) to 111.1 mm (4.375 in) ports           Bore Seal - 136.5 (2.875 in) to 177.8 mm (7 in) ports           Port Diameter, mm (inch)         Cage Style           177.8 (7)         Eq. %, Mod. Eq. % Linear (std. cage)           2         254 (10)           Linear (Whisper III, A1, B3, C3)           Linear (Cav III, 2-stage)           2         Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Cav III, 2-stage)           111.1 (4.375)         Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Cav III, 2- and 3-stage)           136.5 (5.375)         Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Whisper III, A1, B3, C3)           Linear (Cav III, 2- and 3-stage)         Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Whisper III, A1, B3, C3, D3)           111.1 (4.375)         Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Whisper III, A1, B3, C3, D3)           Linear (Cav III, 2- and 3-stage)         Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Whisper III, A1, B3, C3, D3)           All         Cavitrol III           All         See table 8           See table 8         See table 8	III—Standard			
				IV-Optional		
EHD		C-Seal - 73.0 (2.875 in) t	0 1 1 1.1 mm (4.375 in) ports	V—Standard		
		Bore Seal - 136.5 (2.875	in) to 177.8 mm (7 in) ports	IV—Optional		
	Valve Size, NPS	Port Diameter, mm (inch)	Cage Style	ANSI/FCI Leakage Class		
EHD	8 10x8	177.8 (7)	Eq. %, Mod. Eq. %	V - Standard to 593°C (1100°F) (for port diameters from 177.8 (7 inch) through 254 mm		
(CL1500)	12 14 x 12	254 (10)	Linear (Whisper III, A1, B3, C3)	(10 inch) with optional Bore Seal); IV - Optional		
	4 6 x 4	73 (2.875)	Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Whisper III, A1, B3, C3)	V - Standard to 593°C (1100°F) (for port		
			Linear (Cav III, 2-stage)	diameters from 73 through 111.1 mm [2.875		
EHD (CL2500)	6 8 x 6	111.1 (4.375)	Eq. %, Mod. Eq. %, Linear (std. cage), Linear (Whisper III, A1, B3, C3, D3)	through 4.375 inches] with optional C-seal trim); IV - Optional		
			Linear (Cav III, 2- and 3-stage)			
	8 10x8	136.5 (5.375)	Eq. %, Mod. Eq. %, Linear (std.	V - Standard to 593°C (1100°F) (for port diameters from 136.5 through 177.8 mm [5.375		
	12 14x12	177.8 (7)	C3, D3)	through 7-inches] with optional Bore seal); IV - Optional		
EHS, EHAS, EHT	, EHAT	All	Cavitrol III	V		
EHS, EHAS, EHT	, EHAT	All	Std or w/ Micro-Form or w/ Micro-Flute	IV—Standard, V—Optional		
EHT w/ TSO (Tight Shutoff)		See table 8	See table 8	TSO - Optional TSO is not an ASME leakage class. Valves with TSO trim are factory tested to a more stringent Fisher test requirement of no leakage at time of shipment. Test medium is water. Specify service $\Delta P$ when ordering. Test procedure is ANSI/FCI Class V test procedure B.		
EHT w/ PEEK <sup>(1)</sup> Anti Rings	-Extrusion	15.9 (5/8) to 254 (10)	All	IV to 316°C (600°F) or V to 316°C (600°F)		

### Trim Selection Guidelines for NPS 1-1/2 x 1 through 6 Globe Valves

Please refer to the following descriptions as a guideline for the selection of appropriate trims:

- Trim 49--Trim 49 is the standard trim for C12A valve body materials and should only be used with C12A valve body materials. C12A should only be used when the pressure and temperature capabilities for WC9 valve body materials are not acceptable.
- Trim 50--Trim 50 is the standard trim for carbon steel and alloy steel body materials and is recommended for general and severe service applications up to 427°C (800°F). Typical applications for Trim 50 include services in water, boiler feedwater, non-sour hydrocarbons, and steam. The S41600 (416 stainless steel)

heat-treated plug and seat ring have a hardness similar to CoCr-A (Alloy 6).

- Trim 53--Trim 53 should be used in all high temperature applications between 427°C (800°F) and 566°C (1050°F) unless chlorides are present. The presence of chlorides could lead to stress corrosion cracking of the CA28MWV (422 stainless steel) cage.
- Trim 54--Trim 54 is the standard trim for stainless steel body materials. It should be used where hard-faced trim is specified.
- Trim 56--Trim 56 should be used for sour service.
- Trim 57--Trim 57 shall be used for boiler feedwater service when limits exceed those specified for Trim 50.

Care should be taken when specifying this trim in small sizes for applications where chlorides are present due to stress corrosion cracking problems with S44004 (440C stainless steel).



#### Figure 20. Pressure/Temperature Limits for CL2500 Valves (NPS 1-1/2 x 1 through 6 Globe)

NOTE:

Do not exceed the maximum pressure and temperature for the pressure rating of the body material and valve size used. Refer to tables 4 and 5 for pressure/temperature limits of the trim used. Intermediate pressure/temperature ratings are found in separate bulletin, Increased pressure/temperature ratings for EH AND EW series steel valves.

### Material Selection Guidelines

Please use these numbered steps as a guideline for the selection of materials:

3. Determine the pressure/temperature rating of the valve size and material required. Inlet pressure and temperature must always be limited by the applicable ASME pressure/temperature rating.

4. Select the desired valve style from the Available Configurations specification and from the shutoff classifications listed in table 9.

5. Select desired materials from tables 10, 11, 12, and 13 and figures 20, 21, and 22. The temperature capabilities determined from figures 20, 21, and 22 may be further limited by the temperature capabilities of materials selected from tables 10, 11, 12, and 13. Refer to figures 20, 21, and 22 to determine pressure drop limits of the body-trim combinations selected.

Inlet pressure and temperature must always be limited by the applicable ASME pressure/ temperature rating. Contact your <u>Emerson sales office</u> for special materials for temperatures exceeding the following maximum limits: EHD valve [593°C (1100°F)] and the EHT valve [232°C (450°F)].

#### Table 10. Trim Material Combinations (NPS 1-1/2 x 1 through 6 Globe Valves)

			SEAT RING		VALVE BODY	OPERATING /ALVE BODY TEMPERATURE RANGE		SOUR
DESIGNATION	VALVE PLUG	CAGE	SEAT RING	RETAINER	MATERIAL <sup>(6)</sup>	Degrees Celsius	Degrees Fahrenheit	SERVICE (NACE)
			WITH ST	ANDARD CAGE				
50	S41600 (416 SST) heat-treated <sup>(1)</sup> S44004 (440C SST) heat-treated for Micro-Flute valve plugs	S17400 (17-4PH SST) H1075 heat- treated	S41600 heat-treated	S17400 H1150D heat-treated chrome coat	WCC, WC9	-29 to 427	-20 to 800	No
53(2,4)	S31600 (316 SST) with CoCr-A (Alloy 6) seat and guide	S42200 (422 SST) nitrided	Alloy 6	N07718 heat-treated chrome coat	WC9	427 to 566	800 to 1050	No
54	S31600 with CoCr-A seat and quide	CF8M (316 SST) chrome coat	Alloy 6	N07718 heat-treated chrome coat	WCC, WC9 CF8M	-29 to 427 -73 to 593	-20 to 800 -100 to 1100	Yes
56(3)	S31600	CF8M	Alloy 6	S17400 H1150D	WCC, WC9	-29 to 149	-20 to 300	Ves
	seat and guide	ENC	Alloy o	heat-treated chrome coat	CF8M	-40 to 149	-40 to 300	
57(3)	S44004 heat-treated	S17400 H1075 heat-treated	S44004 heat-treated	S17400 H1150D heat-treated chrome coat	WCC, WC9	0 to 232	32 to 450	No
49(4, 5)	F22 with CoCr-A seat and guide	F22 nitrided	Alloy 6	N07718 heat-treated chrome coat	C12A	-29 to 593	-20 to 1100	No
			WITH CAVI	TROL III TRIM CAGE				
58(3)	S44004 heat-treated	CB7CU-1 H1075 heat-treated	S44004	S17400 H1150D heat-treated chrome coat	WCC, WC9	0 to 232	32 to 450	No
59(3)	S31600 with CoCr-A seat and guide	CB7CU-1 H1150D heat-treated	Alloy 6	S17400 H1150D heat-treated chrome coat	WCC, WC9	-29 to 232	-20 to 450	Yes
			WITH WHI	SPER TRIM III CAGE	•			
60	S41600 heat-treated S17400 H900 SST heat-treated for NPS 6 EH only	CB7CU-1 H1075 heat-treated	S41600 heat-treated	S17400 H1150D heat-treated chrome coat	WCC, WC9	-29 to 427	-20 to 800	No
	S31600	S42200 nitrided		N07718	WCC	-29 to 427	-20 to 800	
61 <sup>(4)</sup>	with CoCr-A seat and guide	F22 nitrided for NPS 6 EH only	Alloy 6	heat-treated chrome coat	WC9	-29 to 566	-20 to 1050	No
62 <sup>(3)</sup>	S31600 with CoCr-A seat and quide	CB7CU-1 H1150D beat-treated	Alloy 6	S17400 H1150D heat-treated	CF8M	-46 to 399	-50 to 750	Yes
63 <sup>(4, 5)</sup>	F91 with CoCr-A seat and guide	S42200 nitrided	Alloy 6	chrome coat N07718 heat-treated chrome coat	C12A	-29 to 593	-20 to 1100	No

-continued-

#### Table 10. Trim Material Combinations (NPS 1-1/2 x 1 through 6 Globe Valves) (cont.)

WITH WHISPER NXG CAGE											
9800 No											
y 450											
y 450											
- - -											

S17400 H900 stainless steel heat-treated is used when a diverter cone valve plug is specified for port diameters equal to and larger than 4.375 inches.
 This trim designation not available with the O-ring seat ring gasket construction due to temperature limitations.
 This trim designation uses the O-ring seat ring gasket construction. See table 12 for O-ring temperature limits. For temperatures greater than 232°C (450°F), flat sheet seat ring gasket with HTS1 seal ring option (up to 316°C (600°F) is available. Consult your <u>Emerson sales office</u>.
 This trim sfor use in EHD and EHS constructions only.
 Trims 49 and 63 use \$41000 stem instead of the standard \$31600 material. \$41000 is limited to 538°C (1000°F). For temperatures greater than 538°C (1000°F), \$42200 stem is used.
 Support the standard \$31600 material. \$41000 is limited to 538°C (1000°F). For temperatures greater than 538°C (1000°F), \$42200 stem is used.
 If using valve body/trim combinations other than those listed, consult your Emerson sales office.

#### Table 11. Trim Material Combinations (NPS 8 through 14 Fisher EHD and EHT)

TRIM	VALVE PLUG	VALVE PLUG	CAGE	SFAT RING	SEAT RING CAP	VALVE BODY	OPER/ TEMPERATI	ATING URE RANGE			
DESIGNATION		STEM	0.101		SCREWS	MATERIAL(5)	°C	°F			
	EHD and EHT Valve with Standard Cage										
75	S42000 (420 SST)	S20910	CA6NM	S17400 H1075 heat-treated	S17400	WCC, WC9	-29 to 427	-20 to 800			
~~	S31600	620010	\$31600	S31600	S66286	CF8M	-198 to 593	-325 to 1100			
//	with CoCr-A (alloy 6) seat and guide	520910	chrome coat	with CoCr-A seat	(660 SST)	WCC, WC9	-29 to 204	-20 to 400			
70	S31600 with CoCr-A	\$20010	CA6NM	N06600	N07719	WCC	-29 to 427	-20 to 800			
79	seat and guide	320910	chrome coat	with CoCr-A seat	1107716	WC9	-29 to 566	-20 to 1050			
EHD and EHT Valve with Standard Cage for Sour Service											
0.2(1)	S31600 with CoCr-A	\$20010	\$31600	N06600	N07719	WCC, WC9	-29 to 204	-20 to 400			
02(1)	seat and guide	320910	ENC	with CoCr-A seat	1107716	CF8M	-198 to 343	-325 to 650			
			All Valves v	with Whisper Trim III Ca	ges						
05(3)	F22 with CoCr-A	S41000	WC9/	F22	N07718	WCC	315 to 427	600 to 800			
33.07	seat and guide	heat treated <sup>(2)</sup>	nitrided	with CoCr-A seat	107718	WC9	315 to 593	600 to 1100			
96	S17400 with CoCr-A seat and guide	S17400 H1150D	CB7CU-1 H1075	S17400 with CoCr-A seat	S17400	WCC, WC9	-29 to 427	-20 to 800			
		All V	alves with Whis	per Trim III Cages for So	our Service <sup>(4)</sup>						
97	S17400 with CoCr-A	S17400	S17400	S17400	\$17400		-29 to 343	-20 to 650			
57	seat and guide	H1150D dbl	H1150D ENC	with CoCr-A seat	517400	WCC, WC3	-23 (0 343	-2010000			
1. Limit to 149° 2. S41000 is limi 3. This trim is for	C (300°F) when using N04400 ted to 538°C (1000°F). For te r use in FHD constructions on	0 gasket material. emperatures greater lv.	than 538°C (1000°	°F), an S42200 stem is used.							

Trim Storm Stor Storm S

# Table 12. Construction Materials and Temperature Capabilities for Parts Other than Body and Trim (NPS $1-1/2 \times 1$ through 6 Globe Valves)

DAPT		MATERIAL	TEMPERATURE CAPABILITIES			
PA	ĸı	IVIATERIAL	Degrees Celsius	Degrees Fahrenheit		
		S31600 (316 stainless steel)	-198 to 427	-325 to 800		
		S31600/chromium coating	427 to 593	800 to 1100		
		S20910 <sup>(1)</sup>	-198 to 593	-325 to 1100		
Valve pl	ug stem	S20910/chromium coating	427 to 593	800 to 1100		
		S41000	-29 to 538	-20 to 1000		
		S42200	-29 to 593	-20 to 1100		
			-46 to 427 (to 482 for	-50 to 800 (to 900 for		
EHD/EHAD piston ring		Graphite (FMS 17F27)	nonoxidizing service)	nonoxidizing service)		
			-46 to 537 (to 593 for	-50 to 1000 (to 1100 for		
		Graphite (FMS 17F39)	nonoxidizing service)	nonoxidizing service)		
FHT/FHA	[ seal ring	N10276 with glass and moly-filled PTFF	-73 to 232	-100 to 450		
EHT/FHAT seal (	ing backup ring	Same as base material of valve plug	See table 10	See table 10		
Entry En aver Sean	Backup ring	541600 (416 SST)	-29 to 427	-20 to 800		
	buckup mig	\$30200 (302 SST)				
Spring-	Retaining ring	N07750 <sup>(1)</sup>	-254 to 593	-425 to 1100		
loaded EHT valve	Seal ring	R30003 (with glass and moly-filled PTFE)	-73 to 232(7)	-100 to 450(7)		
plug seal	Anti-extrusion		75 to 252 7	10010 45000		
	ring	PEEK (PolyEtherEtherKetone)	-73 to 316	-100 to 600		
Cane	lasket	S31600/Graphite <sup>(1)</sup>	-254 to 427 (to 593 for	-425 to 800 (to 1100 for		
euge :	Jushee	ss root a prince	nonoxidizing service)	nonoxidizing service)		
	O-ring	Nitrile <sup>(5)</sup>	-29 to 107 <sup>(8)</sup>	-20 to 225 <sup>(8)</sup>		
	seat ring	Ethylene-propylene <sup>(6)</sup>	-40 to 232	-40 to 450		
Seat ring gasket	gasket <sup>(1)</sup>	Fluorocarbon (not for water or steam service) <sup>(5)</sup>	-23 to 204	-10 to 400		
	Flat sheet seat	\$31600/Craphite(1)	-254 to 427 (to 593 for	-425 to 800 (to 1100 for		
	ring gasket	55 TOO/Graphite v	nonoxidizing service)	nonoxidizing service)		
			-29 to 427 (WCC, WC9)	-20 to 800 (WCC, WC9)		
	Studs	Steel SA193-B7 NCF2 (all body materials)	-46 to 343 (LCC)	-50 to 650 (LCC)		
	Nuts	Steel SA194-2H NCF2 (all body materials)	-48 to 232 (CF8M [316 and	-55 to 450 (CF8M [316 and		
			316H])	316HJ)		
	Studs	Steel SA193-B7 NCF2 (WC9 body mat'l)	-29 to 454	-20 to 850		
	Nuts	Steel SA194-7 NCF2(WC9 body mat'l)				
	Studs	Steel SA193-B16 (WC9 and C12A body mat'ls)	-29 to 510	-20 to 950		
	Nuts	Steel SA194-7 (WC9 and C12A body mat'ls)				
	Studs	304 stainless steel SA320-B8 (CF8M [316, 316H body mat'ls])	-198 to 66	-325 to 150		
	Nuts	304 stainless steel SA194-8 (CF8M [316, 316H body mat'ls])		525 to 150		
	Studs	316 SST SA193-B8M <sup>(3)</sup> (CF8M [316, 316H body mat'l])	-198 to 66	-325 to 150		
	Nuts	316 SST SA194-8M (CF8M [316, 316H body mat'l])	.50 10 00	525 to 150		
	Studs	316 SST SA193-B8M chrome coat <sup>(4)</sup> (CF8M [316, 316H body mat'ls])	-198 to 66	-325 to 150		
Body-to-	Nuts	316 SST SA194-8M (CF8M [316, 316H body mat'ls])		525 10 150		
bonnet bolting <sup>(2)</sup>	Studs	SST SA453 GR660 with Belleville washers (CF8M[316, 316H, body mat'ls]	-29 to 427	-20 to 800		
g	Nuts	Steel SA194-7 NCF2 (CF8M [316, 316H body mat'ls]	23 to 127	2010000		
	Studs	SST SA453 GR660 rupture tested with Belleville washers (CF8M[316,				
		316H, body mat'ls]	427 to 537	801 to 1000		
	Nuts	Steel SA194-7 NCF2 (CF8M [316, 316H body mat'ls]				
	Studs	SST SA453 GR660 for sour service <sup>(1)</sup> with Belleville washers (CF8M[316,				
		316H, body mat'ls]	-29 to 427	-20 to 800		
	Nuts	Steel SA194-7M NCF2 <sup>(1)</sup> (CF8M [316, 316H body mat'ls]				
	Studs	SST SA453 GR660 rupture tested for sour service <sup>(1)</sup> with Belleville washers				
		(CF8M[316, 316H, body mat'ls]	427 to 537	801 to 1000		
	Nuts	Steel SA194-7M NCF2 <sup>(1)</sup> (CF8M [316, 316H body mat'ls]				
	Studs	N07718 SST (SB037)	-29 to 566 (WC9)	-20 to 1050 (WC9)		
	Nuts	Steel SA 194-7	-29 to 593 (C12A)	-20 to 1100 (C12A)		
	Studs	Steel SA193-B7M NCF2 for sour service <sup>(1)</sup> (CF8M [316 body mat'l])	-46 to 232	-50 to 450		
	Nuts	Steel SA194-2HM NCF2 for sour service() (CF8M [316 body mat'l])		-5010450		
		PTFE V-ring	-40 to 232	-40 to 450		
		Graphite ribbon/filament (oxidizing service to 700°F)	-254 to 537	-425 to 1000		
Pac	king	Graphite ribbon (high-temperature oxidizing service)	371 to 593	700 to 1100		
		HIGH-SEAL packing system (see Fisher Bulletin 59.1:061, ENVIRO-SEAL	See bulletin 59.1:061	See bulletin 59.1:061		
		and HIGH-SEAL Packing Systems for Sliding-Stem Valves (D101633X012))				

-continued-

# Table 12. Construction Materials and Temperature Capabilities for Parts Other than Body and Trim (NPS $1-1/2 \times 1$ through 6 Globe Valves) (continued)

DAPT	MATEDIAL	TEMPERATURE CAPABILITIES						
PARI	WATERIAL	Degrees Celsius	Degrees Fahrenheit					
Packing follower, spring, or lantern ring	\$31600	-254 to 593	-425 to 1100					
Packing box ring	S31600	-254 to 593	-425 to 1100					
De dia e flavena e trada e a suta	Steel	-29 to 427	-20 to 800					
Packing hange, studs, of huts	S31600	-29 to 593	-20 to 1100					
1. Complies with NACE MR0175-2002, NACE MR0175-2003, NACE MR0103, and NACE MR0175/ISO 15156.     2. Valve body materials with which these bolting materials may be used are shown in parentheses.     3. Class 1 (annealed).     4. Class 2 (strain hardened).     5. For use with all O-ring seat ring constructions with Cavitrol III trim.     6. For use with all O-ring seat ring constructions with Cavitrol III trim.     7. If ured with PEFK are to expression from PEFK but to any be used up to 216°C (500°E) for page or up to 260°C (500°E) for exidizing consistence.								

#### 8. Temperature range per DS52 Group 2.

## Table 13. Construction Materials and Temperature Capabilities for Parts Other than Body and Trim (NPS 8 through 14 Fisher EHD and EHT)

NATERAL         °C         °F           Standard gasket construction         Cage gasket         Silver-plated N04400         -254 to 593         -425 to 1100           Standard gasket construction         Metal seat ring gasket         Graphite filled spiral wound N06600         -254 to 593         -425 to 1100           Metal seat ring gasket         Graphite filled spiral wound N06600         -254 to 593         -425 to 1100           O-ring seat ring gasket         Metal seat ring gasket         Graphite filled spiral wound N06600         -254 to 593         -425 to 1100           O-ring seat ring gasket         Ethylene-propylene         -40 to 232         -40 to 450           Fluorocarbon         -23 to 204         -10 to 400           Sour service gasket construction         Cage gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           Sour service gasket construction         Cage gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         S31600/Graphite <sup>(1)</sup> -254 to 107         -20 to 225           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225	DART		ΜΑΤΕΡΙΑΙ	TEMPERATURE CAPABILITIES			
Standard gasket constructionCage gasketSilver-plated N04400-254 to 593-425 to 1100Standard gasket constructionCage gasketS31600/Graphite(1)-254 to 427 (to 593 for nonoxidizing service)-425 to 800 (to 1100 f nonoxidizing service)Metal seat ring gasketGraphite filled spiral wound N06600-254 to 593-425 to 1100O-ring seat ring gasketGraphite filled spiral wound N06600-254 to 593-425 to 1100O-ring seat ring gasketEthylene-propylene-40 to 232-40 to 450Fluorocarbon-23 to 204-10 to 400-29 to 107-20 to 300Sour service gasket constructionCage gasketS31600/Graphite(1)-254 to 427 (to 593 for nonoxidizing service)-425 to 800 (to 1100 f nonoxidizing service)Sour service gasket constructionO-ring seat ring gasketS31600/Graphite(1)-254 to 427 (to 593 for nonoxidizing service)-425 to 800 (to 1100 f nonoxidizing service)O-ring seat ring gasketS31600/Graphite(1)-254 to 427 (to 593 for nonoxidizing service)-425 to 800 (to 1100 f nonoxidizing service)O-ring seat ring gasketS1600/Graphite(1)-254 to 427 (to 593 for nonoxidizing service)-425 to 205 for nonoxidizing service)O-ring seat ring gasketS1600/Graphite(1)-29 to 107-20 to 225O-ring seat ring gasketFluorocarbon-23 to 149-10 to 300	FA	IK I	MATERIAL	°C	°F		
Standard gasket construction         Cage gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           Standard gasket construction         Metal seat ring gasket         Graphite filled spiral wound N06600         -254 to 593         -425 to 1100           O-ring seat ring gasket         Mitrile         -29 to 107         -20 to 225           O-ring seat ring gasket         Ethylene-propylene         -40 to 232         -40 to 450           Fluorocarbon         -23 to 204         -10 to 400           Sour service gasket construction         Cage gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           Sour service gasket construction         Cage gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           O-ring seat ring gasket         Fluorocarbon         -23 to 149         -10 to 300			Silver-plated N04400	-254 to 593	-425 to 1100		
Standard gasket construction         Metal seat ring gasket         Graphite filled spiral wound N06600         -254 to 593         -425 to 1100           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           O-ring seat ring gasket         Ethylene-propylene         -40 to 232         -40 to 450           Fluorocarbon         -23 to 204         -10 to 400           Sour service gasket construction         Cage gasket         Sil600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 f nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           Fluorocarbon         -23 to 149         -10 to 300	Standard gasket construction	Cage gasket	S31600/Graphite <sup>(1)</sup>	-254 to 427 (to 593 for nonoxidizing service)	-425 to 800 (to 1100 for nonoxidizing service)		
Construction         Nitrile         -29 to 107         -20 to 225           O-ring seat ring gasket         Ethylene-propylene         -40 to 232         -40 to 450           Fluorocarbon         -23 to 204         -10 to 400           Sour service gasket construction         Cage gasket         Tin-plated N04400         -29 to 149         -20 to 300           O-ring seat ring gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           Fluorocarbon         -23 to 149         -10 to 300		Metal seat ring gasket	Graphite filled spiral wound N06600	-254 to 593	-425 to 1100		
O-ring seat ring gasket         Ethylene-propylene        40 to 232        40 to 450           Fluorocarbon        23 to 204         -10 to 400           Sour service gasket construction         Cage gasket         Tin-plated N04400        29 to 149         -20 to 300           O-ring seat ring gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           Fluorocarbon         -23 to 149         -10 to 300			Nitrile	-29 to 107	-20 to 225		
Fluorocarbon         -23 to 204         -10 to 400           Sour service gasket construction         Cage gasket         Tin-plated N04400         -29 to 149         -20 to 300           O-ring seat ring gasket         Nitrile         -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225		O-ring seat ring gasket	Ethylene-propylene	-40 to 232	-40 to 450		
Sour service gasket construction         Cage gasket         Tin-plated N04400         -29 to 149         -20 to 300           O-ring seat ring gasket         0-ring seat ring gasket         Nitrile         -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225			Fluorocarbon	-23 to 204	-10 to 400		
Sour service gasket construction         Cage gasket         S31600/Graphite <sup>(1)</sup> -254 to 427 (to 593 for nonoxidizing service)         -425 to 800 (to 1100 for nonoxidizing service)           O-ring seat ring gasket         Nitrile         -29 to 107         -20 to 225           Fluorocarbon         -23 to 149         -10 to 300			Tin-plated N04400	-29 to 149	-20 to 300		
Oring seat ring gasket         Nitrile         -29 to 107         -20 to 225           Fluorocarbon         -23 to 149         -10 to 300	Sour service gasket	Cage gasket	S31600/Graphite <sup>(1)</sup>	-254 to 427 (to 593 for nonoxidizing service)	-425 to 800 (to 1100 for nonoxidizing service)		
O-ring seat ring gasket Fluorocarbon -23 to 149 -10 to 300	construction		Nitrile	-29 to 107	-20 to 225		
		O-ring seat ring gasket	Fluorocarbon	-23 to 149	-10 to 300		
Graphite (FMS 17F27)     -46 to 427     -50 to 800       (to 900 for nonoxidizing service     (to 900 for nonoxidizing service)	EHD piston ring		Graphite (FMS 17F27)	-46 to 427 (to 482 for nonoxidizing service	-50 to 800 (to 900 for nonoxidizing service)		
Graphite (FMS 17F39) -46 to 537 -50 to 1000 (to 593 for nonoxidizing (to 1100 for nonoxidizing service) nonoxidizing service)			Graphite (FMS 17F39)	-46 to 537 (to 593 for nonoxidizing service)	-50 to 1000 (to 1100 for nonoxidizing service)		
EHD Bore Seal         N07718         -198 to 593         -325 to 1100	EHD Bore Seal		N07718	-198 to 593	-325 to 1100		
EHT seal ring         PTFE with N10276 Spring         -73 to 232         -100 to 450	EHT se	eal ring	PTFE with N10276 Spring	-73 to 232	-100 to 450		
EHT seal ring retaining ring         \$30200 (302 stainless steel)         -254 to 593         -425 to 1100	EHT seal ring r	retaining ring	S30200 (302 stainless steel)	-254 to 593	-425 to 1100		
Backup ring         \$41600 (416 SST)         -29 to 427         -20 to 800		Backup ring	S41600 (416 SST)	-29 to 427	-20 to 800		
Spring-loaded EHT valve         Retaining ring         \$30200 (302 SST)         -254 to 593         -425 to 1100	Spring-loaded EHT valve	Retaining ring	S30200 (302 SST)	-254 to 593	-425 to 1100		
plug seal Seal ring R30003 (with glass and moly-filled PTFE) -73 to 232 <sup>(3)</sup> -100 to 450 <sup>(3)</sup>	plug seal	Seal ring	R30003 (with glass and moly-filled PTFE)	-73 to 232 <sup>(3)</sup>	-100 to 450 <sup>(3)</sup>		
Anti-extrusion rings PEEK (PolyEtherEtherKetone) -73 to 316 -100 to 600		Anti-extrusion rings	PEEK (PolyEtherEtherKetone)	-73 to 316	-100 to 600		
PTFE V-ring -46 to 232 -50 to 450			PTFE V-ring	-46 to 232	-50 to 450		
PTFE/composition -73 to 232 -100 to 450			PTFE/composition	-73 to 232	-100 to 450		
Graphite ribbon filament     -18 to 371 (to 537 for nonoxidizing service)     0 to 700 (to 1000 for nonoxidizing service)	Decl	lein a	Graphite ribbon filament	-18 to 371 (to 537 for nonoxidizing service)	0 to 700 (to 1000 for nonoxidizing service)		
Graphite Ribbon (high temperature oxidizing service) 371 to 649 700 to 1200	Packing		Graphite Ribbon (high temperature oxidizing service)	371 to 649	700 to 1200		
HIGH-SEAL (see Bulletin 59.1:061, HIGH-SEAL Packing Systems for Sliding-Stem Valves (D101633X012) for information			HIGH-SEAL (see Bulletin 59.1:061, HIGH-SEAL Packing Systems for Sliding-Stem Valves (D101633X012) for information)				
Packing follower, spring, or lantern ringS31600 (316 stainless steel)-254 to 593-425 to 1100	Packing follower, sp	oring, or lantern ring	S31600 (316 stainless steel)	-254 to 593	-425 to 1100		
S17400 -101 to 427 -150 to 800	Dacking	boy ring	S17400	-101 to 427	-150 to 800		
S31600 -254 to 593 -425 to 1100	racking	box mig	\$31600	-254 to 593	-425 to 1100		

# Table 13. Construction Materials and Temperature Capabilities for Parts Other than Body and Trim (NPS 8 through 14 Fisher EHD and EHT) (continued)

DADT		MATER		TEMPERATURE CAPABILITIES					
P/	4K I	IVIATER	UAL	°C	°F				
	Studs	Steel SA 193-B7 NCF2	All body materials	-29 to 427 (steel bodies)	-20 to 800 (steel bodies)				
	Nuts	Steel SA 194-2H NCF2	All body materials	-48 to 232 (SST bodies)	-55 to 450 (SST bodies)				
	Studs	Steel SA 193-B7 NCF2	WC9 and C5	20 to 492	20 to 000				
	Nuts	Steel SA 194-7 NCF2	body materials	-2910482	-2010 900				
	Studs	Steel SA 193-B16	WC9 and C5	20 to 502	20 to 1100				
	Nuts	Steel SA 194-7	body materials	-29 10 593	-20101100				
	Studs	304 Stainless steel SA320-B8	CF8M (316 SST)	109 to 66	225 to 150				
	Nuts	316 stainless steel SA194-8	body materials	-198 10 00	-325 to 150				
Body-to-bonnet bolting <sup>(1)</sup>	Studs	316 stainless steel SA193-B8M <sup>(2)</sup>	CF8M and CF8M (316H)	100 - 55	225 to 150				
	Nuts	316 stainless steel SA194-8M	body materials	-198 to 66	-323 (0 130				
	Studs	316 stainless steel SA194-B8M		100 to CC	225. 450				
	Nuts	316 stainless steel SA194-B8	CF8M body materials	-198 to 66	-325 to 150				
	Studs	Steel SA 193-B7M NCF2	For sour service <sup>(4)</sup>	49 1 222	FF ( 450				
	Nuts	Steel SA 194-2HM NCF2	CF8M body material	-48 to 232	-55 to 450				
	Studs	SST SA453 GR660 with Belleville washers	CF8M and CF8M (316H)	-29 to 427	-20 to 800				
	Nuts	Steel SA194-7 NCF2	Douy materials						
	Studs	SST SA453 GR660 rupture tested with Belleville washers	CF8M and CF8M (316H)	427 to 537	801 to 1000				
	Nuts	Steel SA194-7 NCF2	body materials						
	Studs	SST SA453 GR660 with Belleville washers	For sour service <sup>(4)</sup> CF8M and CF8M (316H) body	-29 to 427	-20 to 800				
	Nuts	Steel SA194-7M NCF2	materials						
	Studs	SST SA453 GR660 rupture tested with Belleville washers	For sour service <sup>(4)</sup> CF8M and CF8M (316H) body	427 to 537	801 to 1000				
	Nuts	Steel SA194-7M NCF2	materials		001101000				
1. Valve body materials wit 2. Class 1 (annealed). 3. If used with PEEK anti-ext 4. Complies with NACE MR	INULS         Steel SA 194-7/M INCL?         Indeenals           1. Valve body materials with which these bolting materials may be used are shown in parentheses.         1. Class 1 (annealed).         1. If used with PEEK anti-extrusion rings, PTFE/carbon seal ring may be used up to 316°C (600°F) for non-oxidizing service or up to 260°C (500°F) for oxidizing service.           3. If used with PEEK anti-extrusion rings, PTFE/carbon seal ring may be used up to 316°C (600°F) for non-oxidizing service or up to 260°C (500°F) for oxidizing service.           4. Complex with NACE MR0175-2002, NACE MR0175-1003, NACE MR0175/150 15156.								

#### Table 14. Valve Plug Travel<sup>(1)</sup> (NPS 8 through 14 Valves)

		EHD, EHT						
CAGE STYLE		Valve Size, NPS						
	PRESSURE RATING	8	, 10	12,	14			
		mm	Inches	mm	Inches			
Linear	CL1500	76	3	102	4			
	CL2500	64	2.5	76	3			
5 ID (1)	CL1500	76	3	102	4			
Equal Percentage	CL2500	64	2.5	76	3			
Madified Freed Demonstrate (1)	CL1500	89	3.5	114	4.5			
Modified Equal Percentage(*)	CL2500	76	3	89	3.5			
Whisper Trim III Case	CL1500	178	7	184	7.25			
whisper Trim III Cage	CL2500	146	5.75	178	7			
1. Valves using an equal percentage ca	ige may be travelled an addition	nal 13 mm (0.05 inch) if desire	ed to obtain additional capacity	; flow characteristic becomes mo	odified equal percentage.			

#### Table 15. Flowing Pressure Drop Limits for NPS 6 CL2500 Fisher EHD/EHT and NPS 8 CL2500 EHAD/EHAT Valves (Without Cavitrol III, Whisper Trim III, or Whisper NXG Trim)

			MAXIMUM FLOWING PRESSURE DROP					
PRESSURE RATING	FLOW	STEM SIZE mm (INCHES)		Bar	PSI			
	MEDIA	51 Elli Sizz, init (itterizs)	Flowing	Flowing up with Diverter Cone	Flowing	Flowing up with Diverter Cone		
CL2500	All except boiler	19.1 mm (3/4 inch)	69		1000			
		50.8 mm (1-inch)	69		1000			
	leeuwatei	31.7 mm (1-1/4 inch)	138	431	2000	6250		
	Boiler feedwater	31.7 mm (1-1/4 inch)	69	431	1000	6250		

Figure 21. Pressure/Temperature Limits for Trim Material Combinations (NPS 1-1/2 x 1 through 6 Globe Valves) (also see table 15)



NOTES:

▲ For recommended service applications, See table 15.

 $\overline{2}$ O-ring construction limited to 232°C (450°F), laminated graphite construction limited to 427°C (800°F) for oxidizing service and 593°C (1100°F) for non-oxidizing service.

CF8M (316 SST) valve bodies are available for use with trim 60 up to 232°C (450°F).  $|\frac{3}{4}\rangle$ 

CF8M valve bodies are available for use with trim 61 up to 232°C (450°F).

5 Trim 49 and 63 are only good down to -29°C (-20°F).

#### Table 16. Flowing Pressure Drops Limits for Fisher EHD and EHT Valves (Without Cavitrol III, Whisper Trim III, or Whisper NXG Trim) (NPS 8 to 14 Valves)

	VALVE STEM CONNECTOR SIZE MAXIMUM FLOWING F		FPRESSURE DROP BAR (PSID)		
FLOW MEDIA	mm (inch)	Flowing Down	Flowing Up with Diverter Cone		
All except boiler feedwater	50.8 mm (2-inch)	138 (2000)	259 (3750)		
Boiler feedwater	50.8 mm (2-Inch)	69 (1000)	259 (3750)		



#### Figure 22. Pressure/Temperature Limits for CL1500 and 2500 Valves (NPS 8 through 14 Valves)

NOTES:

1. Do not exceed the maximum pressure and temperature for the pressure rating of the valve material and valve size used. Refer to figure 10 for pressure/ temperature limits of the trim used. Intermediate class pressure/temperature ratings are found in separate bulletin, Increased pressure/temperature ratings for EH series and EW series steel valve bodies (D100075X012 or D100076X012).

	PRESS- URE	FLOW CHARACTERISTIC	VALVE DESIGN AND	PORT D	IAMETER	VALVE PLUG TRAVEL		ILVE PLUG VALVE STEM DIAMETER		
SIZE, NPS	RATING		PLUGSTYLE	mm	Inches	mm	Inches	mm	Inches	
				6.4	0.25	19	0.75	12.7	1/2	
			EHS w/Micro-Flute	9.5	0.375	19	0.75	12.7	1/2	
		Equal percentage		12.7	0.5	19	0.75	12.7	1/2	
		Equal percentage		6.4	0.25	19	0.75	12.7	1/2	
$1.1/2 \times 1$			EHS w/Micro-Form	12.7	0.5	19	0.75	12.7, 19.1	1/2, 3/4	
2x1	CL2500			19.1	0.75	19	0.75	12.7, 19.1	1/2, 3/4	
			EHS w/Micro-Form	12./	0.5	22	0.875	12.7, 19.1	1/2, 3/4	
		Modified equal percentage		19.1	0.75	22	0.875	12.7, 15.1	1/2, 3/4	
			EHS w/Micro-Flute	9.5 12.7	0.375	22	0.75	12.7	1/2	
		Lincon (Cavitral III, 2 stage)	FLIC	12.7	0.5	22	1.25	12.7	1/2 2/4	
		Linear (Cavitroi III, 2-stage)	EHS	15.9	0.625	32	1.25	12.7, 19.1	1/2, 3/4	
		Equal percentage	EHS W/MICFO-FORM	25.4	1 5	22	0.875	12.7, 19.1, 25.4	1/2, 3/4, 1	
			EHS, EHD, EHT	38.1	1.5	22	0.875	12.7, 19.1(1), 25.4(1)	1/2, 3/4(1), 1(1)	
2(2)		Trim III, Whisper NXG Trim, level A1)	EHS, EHD, EHT	38.1	1.5	38	1.5	12.7, 19.1 <sup>(1)</sup> , 25.4 <sup>(1)</sup>	1/2, 3/4 <sup>(1)</sup> , 1 <sup>(1)</sup>	
3 x 2	CL2500	Linear	EHS, EHD, EHT	38.1	1.5	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1	
		Madified a surplus and a surplus	EHS w/Micro-Form	25.4	1	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1	
		Modified equal percentage	EHS, EHD, EHT	38.1	1.5	29	1.125	12.7, 19.1 <sup>(1)</sup> , 25.4 <sup>(1)</sup>	1/2, 3/4(1), 1(1)	
		Linear (Cavitrol III, 2-stage)	EHT	31.8	1.25	51	2	12.7, 19.1	1/2, 3/4	
		Linear (Cavitrol III, 3-stage)	EHS	15.9	0.625	51	2	12.7, 19.1	1/2, 3/4	
		Equal percentage	EHS, EHD, EHT	58.7	2.3125	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1	
		Modified equal percentage								
3, 4 x 3	CL2500	Linear (cage style: Whisper Trim III, Whisper NXG Trim, level A1, B1)	EHS, EHD, EHT	58.7	2.3125	38	1.5	12.7, 19.1, 25.4	1/2, 3/4, 1	
		Linear (Cavitrol III, 3-stage)	EHT	33.3	1.3125	64	2.5	12.7, 19.1 25.4	1/2, 3/4, 1	
		Linear (Cavitrol III, 2-stage)	EHT	47.6	1.875	64	2.5	12.7, 19.1 25.4	1/2, 3/4, 1	
		Equal percentage	EHS, EHD, EHT	73	2.875	38	1.5	19.1, 25.4	3/4, 1	
		Modified equal percentage								
4, 6 x 4	CL2500	Linear (cage style: Whisper Trim III, Whisper NXG Trim, level A1, B1, B3)	EHS, EHD, EHT	73	2.875	51	2	19.1, 25.4	3/4, 1	
		Linear (Cavitrol III, 3-stage)	EHT	58.7	2.3125	70	2.75	19.1, 25.4	3/4, 1	
		Linear (Cavitrol III, 2-stage)	EHT	73	2.875	70	2.75	19.1, 25.4	3/4, 1	
		Equal percentage	EHS, EHD, EHT	111.1	4.375	51	2	19.1, 25.4, 31.8	3/4, 1, 1-1/4	
		Modified equal percentage	EHS, EHD, EHT	111.1	4.375	76	3	19.1, 25.4, 31.8	3/4, 1, 1-1/4	
6, 8 x 6	CL2500	Linear (cage style: Whisper Trim III, Whisper NXG Trim, level B3, C3, D3)	EHS, EHD, EHT	111.1	4.375	76	3	25.4, 31.8	1, 1-1/4	
		Linear (cage style: Cavitrol III, 2- and 3-stage)	EHT	111.1	4.375	95	3.75	19.1, 25.4, 31.8	3/4, 1, 1-1/4	
1. Available 2. EHS Inter	only with EF	IS valve body. 273 only.								

#### Table 17. Additional Globe Valve Specifications (NPS 1-1/2 x 1 through 6 Globe Valves)

	PRESS- URE	FLOW CHARACTERISTIC	VALVE DESIGN AND	P DIA	ort Meter	VALVE PLUG TRAVEL		VALVE STEM DIAMETER	
RATING			PLOGSTILE	mm	Inches	mm	Inches	mm	Inches
				6.4	0.25	19	0.75	12.7	1/2
			EHAS w/Micro-Flute	9.5	0.375	19	0.75	12.7	1/2
		Equal Descent		12.7	0.5	19	0.75	12.7	1/2
		Equal Percent		6.4	0.25	19	0.75	12.7	1/2
			EHAS w/Micro-Form	12.7	0.5	19	0.75	12.7, 19.1	1/2, 3/4
1&2	CL2500			19.1	0.75	19	0.75	12.7, 19.1	1/2, 3/4
				9.5	0.375	22	0.75	12.7	1/2
		Madified Favol Damaget	EHAS W/WICFO-Flute	12.7	0.5	22	0.75	12.7	1/2
		Modified Equal Percent	EHAS w/Micro-Form	12.7	0.5	22	0.875	12.7, 19.1	1/2, 3/4
				19.1	0.75	22	0.875	12.7, 19.1	1/2, 3/4
		Linear(Cavitrol III, 2-stage)	EHAS	15.9	0.625	32	1.25	12.7, 19.1, 25.4	1/2, 3/4, 1
	E	EHAS w/Micro-Form	25.4	1	22	0.875	12.7, 19.1, 25.4	1/2, 3/4, 1	
		Equal Percent	EHAS, EHAD, EHAT	38.1	1.5	22	0.875	12.7, 19.1, 25.4	1/2, 3/4, 1
		Madified Favol Damaget	EHAS w/Micro-Form	25.4	1	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1
		Modified Equal Percent	EHAS, EHAD, EHAT	38.1	1.5	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1
2	CL 2500	Linear	EHAS, EHAD, EHAT	38.1	1.5	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1
2	CL2500	Linear(Cavitrol III, 2-stage)	EHAT	31.8	1.25	51	2	12.7, 19.1	1/2, 3/4
		Linear(Cavitrol III, 3-stage)	EHAS	15.9	0.625	51	2	12.7, 19.1	1/2, 3/4
		Linear(cage style: Whisper Trim III, Whisper NXG Trim, level A1)	EHAS, EHAD, EHAT	38.1	1.5	38	1.5	12.7, 19.1, 25.4	1/2, 3/4, 1
		Equal Percent	EHAS, EHAD, EHAT	58.7	2.3125	29	1.125	12.7, 19.1, 25.4	1/2, 3/4, 1
		Modified Equal Percent	EHAS, EHAD, EHAT	58.7	2.3125	38	1.5	12.7, 19.1, 25.4	1/2, 3/4, 1
		Linear(Cavitrol III, 2-stage)	EHAT	33.3	1.3125	64	2.5	12.7, 19.1, 25.4	1/2, 3/4, 1
4	CL2500	Linear(Cavitrol III, 3-stage)	EHAT	47.6	1.875	64	2.5	12.7, 19.1, 25.4	1/2, 3/4, 1
		Linear(cage style: Whisper Trim III, Whisper NXG Trim, level A1)	EHAS, EHAD, EHAT	58.7	2.3125	38	1.5	12.7, 19.1, 25.4	1/2, 3/4, 1
c	CL 2500	Modified Equal Percent	EHAD	92.1	3.625	51	2	31.8	1-1/4
σ	CL2500	Linear(Cavitrol III, 3-stage)	EHAD	73	2.875	102	4	31.8	1-1/4
1. Available	e only with EH	IAS valve body.							

#### Table 18. Additional Angle Valve Specifications (NPS 1 through 6 Angle Valves)

#### Table 19. Globe Valve Yoke Boss and Valve Stem Diameter Combinations<sup>(1)</sup> (NPS 1-1/2 x 1 through 6 Globe Valves)

	STANDARD DIAMETERS				OPTIONAL DIAMETERS			
VALVE SIZE, NPS	mm		Inches		mm		Inches	
	Stem	Yoke Boss	Stem	Yoke Boss	Stem	Yoke Boss	Stem	Yoke Boss
1-1/2 x 1, 2 x 1	12.7	71	1/2	2-13/16	19.1	90	3/4	3-9/16
2, 3 x 2	12.7 19.1	71 90	1/2 3/4	2-13/16 3-9/16	25.4	127	1	5
3, 4 x 3	19.1	90	3/4	3-9/16	12.7 25.4	71 127	1/2 1	2-13/16 5
4, 6 x 4	19.1	90	3/4	3-9/16	25.4	127	1	5
6,8x6	25.4 31.8	127 127	1 1-1/4	5 5H	19.1	90	3/4	3-9/16
1. See table 17 for valve ste	m diameters availabl	e for specific constru	ction.					

		GLOBE	VALVES		ANGLE VALVES				
		CL2	500		CL2500				
VALVE SIZE, NPS	kg		lbs		k	kg		lbs	
	Flg	SWE and BWE	Flg	SWE and BWE	Flg	SWE and BWE	Flg	SWE and BWE	
1					73.1	53.5	161	118	
1-1/2 x 1		46		101					
2					98	66.2	216	146	
2 x 1	78	47	173	104					
3 x 2	161	94	355	207					
3	223	163	492	359	181	99.3	399	219	
4 x 3	265	162	585	357					
4	338	243	745	536		203.2		448	
6 x 4	526	257	1160	567					
6	785	544	1731	1199		496.2		1094	
8 x 6	955	558	2106	1231					
8									

### Table 20. Approximate Weights (Valve and Bonnet Assemblies) (NPS 1-1/2 x 1 through 6 Globe and NPS 1 through 6 Angle Valves)

Table 21. Approximate Weights (Valve Assembly and Bonnet) (NPS 8 through 14 Valves)

VALVE		CL1500				CL2500			
SIZE,	BWE		Flg		BWE		Flg		
NPS	kg	lbs	kg	lbs	kg	lbs	kg	lbs	
8	1400	3100	1700	3700	1900	4100	2200	4700	
10	1500	3300	1900	4100	2000	4400			
12	3400	7300	3900	8600	3400	7600			
14	3400	7300			3400	7600			

### Installation

The valve must be installed so flow through the valve matches the flow direction arrow on the valve body. Consideration should be given to installing an upstream strainer, especially if the valve uses a multi-orifice Whisper Trim III, Whisper NXG Trim, or Cavitrol III cage.

For NPS 8 and larger valves, the recommended installation position is with the valve in a horizontal

pipeline and the actuator vertical above the valve. Other orientations may result in shortened trim life and difficulty with field maintenance.

Overall dimensions are shown in figures 23, 24, 25, 26, and 27. Face-to-face dimensions are in compliance with ANSI/ISA-S75 for valves smaller than NPS 8. For NPS 8 and larger valves, face-to-face dimensions are longer than industry standards for valves of this size and rating. Actual end connection dimensions conform to ASME B16.25 for buttwelding ends and to ASME B16.5 for flanged ends.





NOTE:

For dimensions of valves with DIN (or other) end connections, consult your <u>Emerson sales office</u>.

Table 22. NPS 1-1/2 x 1	I through 6 Globe Valve Dimensions with Standard Bonnet
	- (1)

		ł	<b>Ą</b> (1)		
VALVE SIZE NPS		CL	2500		
	BWE	SWE	RF	RTJ	
		mm		•	
1-1/2 x 1	318	318	337	340	
2 x 1	318	318	349	353	
2 <sup>(2)</sup>	400				
3 x 2	400		435	442	
3	498		498	505	
4 x 3	498		518	527	
4	575		575	584	
6 x 4	6x4 575		660	673	
6	6 819		819	832	
8 x 6	819		857	873	
		Inches		•	
1-1/2 x 1	12.50	12.50	13.25	13.38	
2 x 1	12.50	12.50	13.75	13.88	
2 <sup>(2)</sup>	15.75				
3 x 2	15.75		17.12	17.38	
3	19.62		19.62	19.88	
4 x 3	19.62		20.38	20.75	
4	22.62		22.62	23.00	
6 x 4	22.62		26.00	26.50	
6	32.25		32.25	32.75	
8 x 6	32.25		33.75	34.38	
1. RF—raised-face flanges; RTJ—ring-t 2. Intermediate CL3273 only.	ype joint flanges; BWE—buttwelding e	ends; SWE—socketweld ends.			

			B <sup>(1)</sup>						
VALVE SIZE NPS		C	L2500						
	BWE SWE		RF	RTJ					
	mm								
1-1/2 x 1	159	159	168	170					
2 x 1	159	159	175	176					
2(2)	200								
3 x 2	200		217	221					
3	249		249	253					
4 x 3	249		259	264					
4	273		273	278					
6 x 4	6x4 273		325	331					
6	6 397		397						
8 x 6	397	416		424					
		Inches	•						
1-1/2 x 1	6.25	6.25	6.62	6.69					
2 x 1	6.25	6.25	6.88	6.94					
2(2)	7.88								
3 x 2	7.88		8.56	8.69					
3	9.81		9.81	9.94					
4 x 3	9.81		10.19	10.38					
4	10.75		10.75	10.94					
6 x 4	10.75		12.81	13.06					
6	15.62		15.62	15.88					
8 x 6	15.62		16.38	16.69					
1. RF—raised-face flanges; RTJ—ring 2. Intermediate CL3273 only.	-type joint flanges; BWE—buttweldin	g ends; SWE—socketweld ends.	•						

Table 23. NPS 1-1	/2 x 1 through 6 Globe	Valve Dimensions with	Standard Bonnet

Table 24. NPS 1-1/2 x 1 through 6 Globe Valve Dimensions with Standard Bonnet

	G		D					
VALVE		CL2500						
SIZE	CL2500	Y	oke Boss Diameters, mm (Inch	ies)				
NI S		71 (2-13/16)	90 (3-9/16)	127 (5)				
		mm						
1-1/2 x 1	78	249	256					
2 x 1	78	249	256					
2(1)	108	303	310	343				
3 x 2	108	303	310	343				
3	145	335	335	371				
4 x 3	145	335	335	371				
4	168		348	406				
6 x 4	168		348	406				
6	229		408	445				
8 x 6	229		408	445				
		Inches						
1-1/2 x 1	3.06	9.81	10.06					
2 x 1	3.06	9.81	10.06					
2(1)	4.35	11.94	12.19	13.50				
3 x 2	4.35	11.94	12.19	13.50				
3	5.69	13.19	13.19	14.62				
4 x 3	5.69	13.19	13.19	14.62				
4	6.62		13.69	16.00				
6 x 4	6.62		13.69	16.00				
6	9.00		16.06	17.50				
8 x 6	9.00		16.06	17.50				
1. Intermediate CL3273 only.	•	•	•	-				

#### Figure 24. Dimension D for Style 1 Extension Bonnet

(A, B, and G Dimensions Listed in Figure 23 Do Not Change When Extension Bonnet is Used) (also see table 25)



18A5906-C A3002-2

Table 25. Dimension D for Style 1 Extension Bonnet (A, B, and G Dimensions Listed in Figure 23 Do Not Change When Extension Bonnet is Used)

GLOBE			D				
VALVE SIZE,	PRESSURE RATING	Yoke Boss Diameter, mm (Inches)					
NPS		71 (2-13/16)	90 (3-9/16)	127 (5)			
		mm					
1-1/2 x 1, 2 x 1	CL2500	391	406				
2	CL3273	427	443	502			
3 x 2	CL2500	427	443	502			
		Inches					
1-1/2 x 1, 2 x 1	CL2500	15.38	16.00				
2	CL3273	16.81	17.44	19.75			
3 x 2	CL2500	16.81	17.44	19.75			



Figure 25. NPS 1 through 6 Angle Valve CL2500 Dimensions with Standard Bonnet and Style 1 Extension Bonnet (also see table 26)

Table 26, NPS 1	through 6 Angle	Valve CL2500	<b>Dimensions</b> wit	n Standard Bonnet
	un ougn o <i>i</i> ingi			i Standard Donnet

	DDECCUDE		A				D			
VALVE SIZE,	RATING	A, mm				Std. Bonnet				
NI S	KATING	BWE	SWE	RF	RTJ	BWE	SWE	RF	RTJ	
1	CL2500	153.9	153.9	153.9	153.9	256.5	392.2	408.1	408.1	
2	CL2500	225.6	225.6	225.6	227.1	408.1	408.1	250.0	256.5	
3	CL2500	289.1			292.1	308.9			308.9	
4	CL2500	336.6				334.8				
6	CL3230 <sup>(1)</sup>	374.7				451.7				
				Inc	hes					
1	CL2500	6.06	6.06	6.06	6.06	10.097	15.440	16.065	16.065	
2	CL2500	8.88	8.88	8.88	8.94	16.065	16.065	9.844	10.097	
3	CL2500	11.38			11.5	12.162			12.162	
4	CL2500	13.25				13.182				
6	CL3230 <sup>(1)</sup>	14.75				17.782				
1. NPS 6 is an in	termediate CL3230	).								

Figure 26. Dimensions (NPS 8 through 14 Fisher EHD and EHT Valves) (also see tables 27, 28, and 29)



For dimensions of valves with EN (or other) end connections, consult your Emerson sales office.

#### Table 28. Dimensions (NPS 8 through 14 Fisher EHD and EHT Valves)

VALVE	A <sup>(1,2)</sup>								
SIZE, NPS	CL900		CL1500			CL2500			
	RF	RTJ	BWE	RF	RTJ	BWE	RF	RTJ	
mm									
8	1137	1140	1194	1194	1203	1295	1295	1311	
10	1168	1172	1245	1245	1254	1346			
12	1715	1718	1803	1803	1819	1778			
14	1727	1739	1829			1803			
Inches									
8	44.75	44.88	47.00	47.00	47.38	51.00	51.00	51.62	
10	46.00	46.13	49.00	49.00	49.38	53.00			
12	67.50	67.62	71.00	71.00	71.62	70.00			
14	68.00	68.38	72.00			71.00			

#### Table 29. Dimensions (NPS 8 through 14 Fisher EHD and EHT Valves)

VALVE	B <sup>(1,2)</sup>								
SIZE, NPS	CL900		CL1500			CL2500			
			BWE	RF	RTJ	BWE	RF	RTJ	
mm									
8	429	430	457	457	462	508	508	516	
10	445	446	483	483	487	533			
12	794	795	838	838	846	838			
14	800	805	851			851			
Inches									
8	16.88	16.94	18.00	18.00	18.19	20.00	20.00	20.31	
10	17.50	17.56	19.00	19.00	19.19	21.00			
12	31.25	31.31	33.00	33.00	33.31	33.00			
14	31.50	31.69	33.50			33.50			
<ol> <li>Face-to-face dimensions for these valves are not standard dimensions due to the lack of industry standards for valves of this size and rating.</li> <li>BWE—buttwelding ends; RF—raised-face flanges; RTI—ring-type joint flanges.</li> </ol>									

# Table 27. Dimensions (NPS 8 through 14 Fisher EHD and EHT Valves)

VALVE	Γ	)	G				
SIZE, NPS	CL900 and 1500	CL2500	CL900 and 1500	CL2500			
mm							
8, 10	684	665	363	370			
12, 14	702	724	452	437			
Inches							
8, 10	26.94	26.19	14.31	14.56			
12, 14	27.62	28.50	17.81	17.19			

#### Figure 27. Dimensions (NPS 20 Fisher EHD Valve)



Neither Emerson, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher, Cavitrol, Whisper Trim, WhisperFlo, and ENVIRO-SEAL are marks owned by one of the companies in the Emerson business unit of Emerson Electric Co. Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Marshalltown, Iowa 50158 USA Sorocaba, 18087 Brazil Cernay, 68700 France Dubai, United Arab Emirates Singapore 128461 Singapore

www.Fisher.com

