

# ControlWave<sup>®</sup> PAC Resistance Temperature Detector Module and Thermocouple Module

The Resistance Temperature Detector (RTD) module and the Thermocouple (TC) module allow the ControlWave<sup>®</sup> PAC to accurately monitor a wide range of temperatures.

## RTD Module

The Resistance Temperature Detector (RTD) provides four isolated inputs. The RTD module monitors the temperature signal from an RTD sensor within a fixed range. The RTD module provides four channels for measuring the resistance of 2-wire, 3-wire, or 4-wire 100-ohm platinum RTD sensors. The RTD module determines the RTD type (2, 3, or 4-wire) by the position of a jumper on the terminal block.

Each channel contains signal conditioning circuitry, a 24-bit Analog to Digital Converter (ADC), and current limiter for over-voltage protection. Each channel provides electrical isolation of 500 Vdc (channel to channel/system bus) and surge protection.

## TC Module

The TC module (also referred to as the Low-Level Analog Input or LLAI module) provides six individually isolated differential inputs for thermocouples or  $\pm 10$  mV inputs, plus one prewired cold junction compensation (CJC) input for temperature compensation at the terminal block.

Each channel contains a 24-bit Analog to Digital Converter (ADC), and an over-voltage protection. Each channel provides

electrical isolation of 500 Vdc (channel to channel/system bus) and surge protection.

The module provides CJC at the terminal block with a factory installed CJC board and built-in RTD sensor.

The CJC board is factory installed on local or remote terminal blocks and is electrically isolated

## Local or Remote Terminations


I/O modules available are factory configured for either local terminations that consist of one 40-point terminal block assemblies or remote terminations that consist of 4 DIN-rail mountable terminal block mass termination headers. Terminations are pluggable and accept a maximum wire size of 14 AWG (American Wire Gauge).

I/O modules are designed to maximize usability while minimizing installation, maintenance, and system downtime costs. A pull down door provides front panel wiring terminal access for technicians. The bezel and the terminations can be easily removed from the I/O module to make wiring even easier.

Remote terminations provide a convenient alternative to the standard direct connect termination. Remote terminations allow a concentration of electrical connections from one or more controllers to be located in a single area. For more information on remote terminations or terminal blocks, refer to Product Data Sheet CWPAC.

## ControlWave PAC Resistance Temperature Detector Module

### Field Wiring Terminals



Input	
Quantity	4
Type	2, 3, or 4 wire RTD
Connector	Terminal block or remote termination
Resolution	16-bit
Voltage Input Impedance	9.6 kΩ
Channel Data Acquisition	50 μs
Conversion Time	3-wire: 266 ms 4-wire: 200 ms for all 4 inputs
Input Accuracy	+/- 0.5°C at 25°C +/- 1.0°C at -40°C to 70°C
Common Mode Rejection	120 db
Normal Mode Rejection	80 db
Electrical Isolation	500 Vdc channel to channel and channel to bus
Surge Suppression	12 Vdc transorb between signal and ground
Status Indicator	Normal, Over/Under Range, and module OK/FAIL LEDs
Power	
Input Voltage Range	Powered from Backplane
Physical	
Dimensions	177.8 mm H x 46.2 mm W x 165.1 mm D (7 in. H x 1.82 in. W x 6.5 in. D)



Common Mode Rejection	120 db
Normal Mode Rejection	80 db
Electrical Isolation	500 Vdc channel to channel and channel to bus
Surge Suppression	180 Vdc transorb between signal and ground
Status Indicator	Normal, Over/Under Range, and module OK/FAIL LEDs
Cold Junction Compensation	RTD sensor on terminal block
<b>Power</b>	
Input Voltage Range	Powered from Backplane
<b>Physical</b>	
Dimensions	177.8 mm H x 46.2 mm W x 165.1 mm D (7 in. H x 1.82 in. W x 6.5 in. D)
Weight	0.66 kg (1.45 lb)
Wiring	Up to 14 American Wire Gauge (AWG) local termination or optional remote termination
<b>Environmental</b>	
Same as the ControlWave PAC in which it is installed	
<b>Approvals</b>	
Same as the ControlWave PAC in which it is installed	

## Headquarters:

**Emerson Process Management**

Remote Automation Solutions  
6005 Rogerdale Road  
Houston, TX 77072 U.S.A.  
T +1 281 879 2699 | F +1 281 988 4445  
[www.EmersonProcess.com/Remote](http://www.EmersonProcess.com/Remote)

## Europe:

**Emerson Process Management**

Remote Automation Solutions  
Emerson House  
Kirkhill Drive Kirkhill Industrial Estate  
Aberdeen UK AB21 0EU  
T +44 1224 215700 | F +44 1224 215799  
[www.EmersonProcess.com/Remote](http://www.EmersonProcess.com/Remote)

## North American/Latin America:

**Emerson Process Management**

Remote Automation Solutions  
6005 Rogerdale Road  
Houston TX USA 77072  
T +1 281 879 2699 | F +1 281 988 4445  
[www.EmersonProcess.com/Remote](http://www.EmersonProcess.com/Remote)

## Middle East/Africa:

**Emerson Process Management**

Remote Automation Solutions  
Emerson FZE  
P.O. Box 17033  
Jebel Ali Free Zone – South 2  
Dubai U.A.E.  
T +971 4 8118100 | F +971 4 8865465  
[www.EmersonProcess.com/Remote](http://www.EmersonProcess.com/Remote)

## Asia-Pacific:

**Emerson Process Management**

Remote Automation Solutions  
1 Pandan Crescent  
Singapore 128461  
T +65 6777 8211 | F +65 6777 0947  
[www.EmersonProcess.com/Remote](http://www.EmersonProcess.com/Remote)

© 2007-2012 Remote Automation Solutions, a business unit of Emerson Process Management. All rights reserved.

Bristol, Inc., Bristol Canada, BBI SA de CV and Emerson Process Management Ltd, Remote Automation Solutions division (UK), are wholly owned subsidiaries of Emerson Electric Co. doing business as Remote Automation Solutions, a business unit of Emerson Process Management. FloBoss, ROCLINK, Bristol, Bristol Babcock, ControlWave, TeleFlow, Helicoid, OpenEnterprise, and METCO are trademarks of Remote Automation Solutions. AMS, PlantWeb and the PlantWeb logo are marks of Emerson Electric Co. The Emerson logo is a trademark and service mark of the Emerson Electric Co. All other marks are property of their respective owners.

The contents of this publication are presented for informational purposes only. While every effort has been made to ensure informational accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. Remote Automation Solutions reserves the right to modify or improve the designs or specifications of such products at any time without notice. All sales are governed by Remote Automation Solutions' terms and conditions which are available upon request. Remote Automation Solutions does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Remote Automation Solutions product remains solely with the purchaser and end-user.