

M21 Transmitter

Single Channel Universal Gas Monitoring

The Millennium II (M21) single channel universal transmitters have been engineered from the ground-up to include the innovative features that managers and operators in the field demand, while providing rock solid day-to-day operation, even in the most extreme conditions. The Millennium II redefines what you expect from a fixed gas detection solution.

- Universal transmitter — compatible with all sensor types (infrared, catalytic bead, and electrochemical)
- Wide voltage range allows for greater stability and system compatibility
- Lowest power consumption available

Universal Transmitter

The transmitter can be fitted with a wide range of toxic or combustible gas sensors. Sensors are pre-calibrated and easily connected to the transmitter which recognizes a newly fitted sensor, automatically uploading the sensor's specific configuration profile.

Digital Communications

Sensor and transmitter continuously communicate digitally, giving you the confidence of stable, accurate protection with fast response times even over long separation distances.

Easy To Use Menus

English, French, Portuguese, or Spanish display languages included. The full text menu makes installation, operation, and calibration simple. No manual necessary!



M21 (SS & AL) shown with SX3 Series Sensors

- Full diagnostics with event and data logging
- Intuitive menu system provides operators with non-intrusive set-up and calibration interface
- Field selectable gas curves and ranges
- Long range (+2,000 ft/600 m) sensor separation

Superior OLED Display

The only full graphic OLED display available, easy to read in all ambient lighting conditions.

Analog, Relay, Modbus RS485 RTU & HART®

Multiple communication protocols are available combined with relays to allow the M21 Transmitter to work seamlessly with your system.

Field-proven Sensor Innovations

All of our sensors are engineered to be fast and reliable with field-proven performance in the harshest industrial conditions possible. These include a full range of fast response Electrochemical toxic gas sensors. For combustible gas detection, poison resistant Catalytic Bead technology with *SensorGuard*, which greatly prolongs sensor life and Infrared sensor technology utilizing a dual beam design with no mirrors that can become contaminated (“fogged up”) or misaligned.

Specifications


Table 1 - Millennium II M21 Single Channel Transmitter

Electrical	
Power Consumption	2.4 W @ 24 VDC (average - varies by sensor types/quantities)
Voltage Range	10.5–32.0 VDC (HART®: 18–32 VDC)
EMC Compliance	EN 50270:2006 per EMC directive 2004/108/EC
Display	Organic LED (OLED), Power/Status LED's
Environmental	
Temperature	-67 °F to +185 °F (-55 °C to +85 °C) - Stainless steel -58 °F to +185 °F (-50 °C to +85 °C) - Stainless steel - North American explosion-proof certification -40 °F to +185 °F (-40 °C to +85 °C) - Aluminum
Relative Humidity	0–95 % RH non condensing
Ingress Protection	IP66 (Aluminum), IP67 (Stainless Steel), IP64 (with sensors) Type 4X
Mechanical	
Enclosure Material	Cast Aluminum (A359) or Stainless Steel (SS316)
Conduit Opening	¾" NPT (3X)
Outputs	Standard: Analog 4–20 mA Optional: Four 5 A Form C Relays, and RS 485 Modbus® RTU, and HART®
Certifications	<p>North American Class I, Division 1, Groups BCD T5 Class I, Zone 1, AEX/Ex d IIB+H2 T5 -50 °C ≤ Ta ≤ +85 °C NEMA Type 4X/IP67 FM6320, ANSI/ISA 12.13.01, CSA 22.2 No. 152:2006</p> <p>IECEX Ex d IIB+H2 T5 Gb IECEX DNV 12.0014 (Aluminum) IP66, controller only IECEX FMG 12.0006X (Stainless Steel) IP 67, controller only IEC 60079-0: 2007-10 & IEC 60079-1: 2007-04</p> <p>Inmetro Ex d IIB+H2 T5 Gb IP67</p>
Sensors	Combustible Gases: SC3 Series Infrared and Catalytic Bead Toxic Gases: ST3 Series Electrochemical
Warranty	3 years
Mounting	Surface Mount/Pipe Mount/Duct Mount
Weight	Aluminum: 5.5 lbs (2.5 kg), Stainless steel: 7.0 lbs (3.2 kg)

Ordering Information	
M21-A	Single Channel - Analog
M21-AR	Single Channel - Analog & Relay
M21-AD	Single Channel - Analog & Modbus
M21-ARD	Single Channel - Analog & Relay & Modbus
M21-AH	Single Channel - Analog & HART®
M21-AHR	Single Channel - Analog & HART® & Relay
Enclosures Available: Aluminum (-A) Stainless Steel (-S)	
Ordering Matrix Example: M21-AH-S (Transmitter - Output - Enclosure Material)	

Special Features
<ul style="list-style-type: none"> ■ Current loop test jacks for each channel on faceplate ■ Non-intrusive one man calibration (magnetic switch) ■ Field selectable toxic gas ranges ■ Redundant menu access via push buttons ■ Sensor enable/disable option from menu (Cl1, Div2) ■ Alarm relays configurable/assignable to any channel ■ Displayed event logging (980 events) ■ Easily retrieve last calibration data from sensor ■ Four languages - English, French, Spanish, Portuguese
Accessories
<ul style="list-style-type: none"> ■ Mounting Bracket Complete With Hardware ■ Sun Shade/Deluge Protection ■ Duct Mount and Hardware Kit

Figure 1 - Millennium II M21 Single Channel Transmitter Dimensions



	A	B	C	D	E					
Aluminum Housings	6.3	160	5.6	142	5.4	137	9.7	246	6.0	152
Stainless Steel Housings	5.9	150	5.1	130	4.6	117	8.9	226	6.0	152
	F	G	H	I						
Aluminum Housings	5.7	145	2.6	66	2.9	74	4.1	103		
Stainless Steel Housings	5.8	147	2.6	66	2.9	74	3.9	100		

Accessories

Table 2 - Accessories

Accessories	
UDM-001	Universal duct mount assembly with 1 m inlet sampling pipe - Stainless Steel
UDM-002	Universal duct mount assembly with 1.5 m inlet sampling pipe - Stainless Steel
UDM-003	Universal duct mount assembly - Stainless Steel
UDM-EX1	1 m extension - for use with UDM-001 and UDM-002 - Stainless Steel
UDM-EX2	1.5 m extension - for use with UDM-001 and UDM-002 - Stainless Steel
UN-MK-31	1" Pipe Mounting kit c/w stainless steel mounting bracket and hardware
UN-MK-32	2" Pipe Mounting kit c/w stainless steel mounting bracket and hardware
UN-MK-33	3" Pipe Mounting kit c/w stainless steel mounting bracket and hardware
HPT-001	HART® Communicator port, mounts directly to Millennium II transmitter
SSK-51	1" Pipe Mounted Sun shade kit/rain guard - Stainless steel - includes UN-MK-31 Mounting Kit
SSK-52	2" Pipe Mounted Sun shade kit/rain guard - Stainless steel - includes UN-MK-32 Mounting Kit
SSK-53	3" Pipe Mounted Sun shade kit/rain guard - Stainless steel - includes UN-MK-33 Mounting Kit

EmersonProcess.com/FlameGasDetection



YouTube.com/user/RosemountAnalytical



Analyticexpert.com



Twitter.com/Rosemount_News



Facebook.com/Rosemount

Americas

Emerson Process Management
6021 Innovation Blvd.
Shakopee, MN 55379
USA
T + 1 866 347 3427
F + 1 952 949 7001
Safety.CSC@Emerson.com

Europe

Emerson Process Management AG
Neuhofstrasse 19a P.O. Box 1046
CH-6340 Baar
Switzerland
T + 41 (0) 41 768 6111
F + 41 (0) 41 768 6300
Safety.CSC@Emerson.com

Middle East & Asia

Emerson Process Management
Emerson FZE
Jebel Ali Free Zone
Dubai, UAE
P.O. Box 17033
T + 971 4 811 8100
F + 971 4 886 5465
Safety.CSC@Emerson.com

Asia Pacific

Emerson Process Management
1 Pandan Crescent
Singapore 128461
Singapore
T + 65 777 8211
F + 65 777 0947
Safety.CSC@Emerson.com

©2016 Emerson Process Management. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. All other marks are the property of their respective owners.

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.