




Speed Accessory Packages for the AMS 2140 Machinery Health Analyzer



When your application calls for accurate speed measurements, Emerson offers two packages for getting the job done. For more information on these items, contact your local Emerson representative.

Part Number	Photo	Name and Description
A0404B40		<p>404B Tachometer with Turck Cable for AMS 2140</p> <p>The 404B Infrared phototach is a self-contained, reflective sensor. The phototach is relatively immune to ambient light sources, making it ideal for outdoor use in areas where reflected light and glare cause conventional phototachs to malfunction. It provides direct readings up to 20,000 RPM at distances up to 3 feet. Distance may vary with RPM. For convenience, the 404B can be powered directly from a AMS 2140 Machinery Health Analyzer with the cable provided in this A0404B40 package. The optional 408 battery pack, which comes with the A0404P40 package, may also be used with the 404B for extended usage. Standard Accessories: Phototach probe, cable for connecting to AMS 2140 tach input, ball and swivel magnetic mount, storage case, and reflective tape.</p>
A0404P40		<p>Cable 404B Power Tachometer with Turck & BNC</p> <p>The 404P Infrared phototach is a self-contained, reflective sensor. The phototach is relatively immune to ambient light sources, making it ideal for outdoor use in areas where reflected light and glare cause conventional phototachs to malfunction. It provides direct readings up to 20,000 RPM at distances up to 3 feet. Distance may vary with RPM. The A0404P40 package includes the A404B phototach kit with an external power supply. Standard Accessories: Phototach probe, power supply, cable for connecting to AMS 2140 tach input, ball and swivel magnetic mount, storage case, and reflective tape.</p>

©2017, Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

Emerson
Reliability Solutions
 835 Innovation Drive
 Knoxville, TN 37932 USA
 ☎ +1 865 675 2400

🌐 www.emerson.com/ams