

Introducing QuickShip Everyday for Europe

QuickShip Everyday for Isolation Valves

Fast by default - free by design - for everyday items you need

With the rapid changes in today's business environment, you can't afford to slow down—especially when it comes to product repair and replacement.

What if you could:

- Get the items you need with shorter lead times?
- Reduce the impact of potential late-stage project changes?
- Backfill spares and build inventory faster?

Emerson's **QuickShip Everyday** delivers all that and for no additional cost.

The QuickShip Everyday program provides market-leading production and shipment services designed to reduce lead time on commonly-ordered parts and products, ensuring fast, convenient and reliable delivery.

QuickShip Everyday leverages Emerson's reliable network of global manufacturing locations and local fulfillment centers to ensure rapid shipment of parts and final-assembly products for no additional premium.

QuickShip is a world-class fulfillment program that allows for fast shipment of parts and products to maximize speed and responsiveness. It leverages our global infrastructure, local presence and commitment to service to help you avoid downtime, stay on schedule, respond to the unexpected, and control cost in today's challenging environments.

Put Emerson's wealth of resources and expertise to work for you to resolve all your part and product shipping needs, no matter the circumstances.

For more information, visit
www.Emerson.com/QuickShip.

QuickShip Everyday for Isolation Valves

The **QuickShip** isolation valves configurable stock available in Europe includes the following products:




Model	OptiSeal	Figure 320/322	Figure 990	CompoSeal
Size (DN)	50 - 300	50 - 300	50 - 300	40 - 300
Body	Cast Iron	Ductile Iron	Cast Iron	Composite XP 1600
Disc	Stainless Steel	Stainless Steel	Stainless Steel	Composite XP 1620
Seat	PTFE EPDM	EPDM NBR	PTFE-EPDM EPDM	EPDM
Stem	Stainless Steel	Stainless Steel	Stainless Steel	Stainless Steel

Model	Series GR	K-LOK® Series 36/37	Figure 85
Size (DN)	20 - 600	50 - 300	40 - 300
Body	Ductile Iron	Carbon Steel Stainless Steel	Stainless Steel Carbon Steel
Disc	SS NialBz	Stainless Steel	Stainless Steel Carbon Steel
Seat	EPDM NBR	RTFE	EPDM NBR
Stem	Stainless Steel	Stainless Steel	Stainless Steel

QuickShip Everyday for Isolation Valves

The **QuickShip** isolation valves configurable stock available in Europe includes the following products:



Model	KTM Series RA	KTM Series EB7	Vanessa Series 30,000	Neotecha NeoSeal
Size (DN)	8 - 100	15 - 100	80 - 600	40 - 300
Body	CS EN 1.0619 SS EN 1.4408	SS A351 CF8M CS A216 WCB	SS EN 1.4408 CS EN 1.0619 CS A216 WCC	Ductile Iron
Ball / Disc	SS EN 1.4408	SS 316	SS EN 1.4408 CS EN 1.0619 CS A216 WCC	Stainless Steel lined with PFA
Seat	TFM 1600	TFE-PFA TFE-FPA	Stellite 21	PTFE
Stem	SS Duplex	SS 316	Stainless Steel Nitronic 50	Stainless Steel

QuickShip Everyday for Isolation Valves

Isolation Valves in the **QuickShip** program can be configured with a selection of pneumatic and electric actuators, selected switchboxes, positioners, and solenoid valves. Contact your local Emerson representative for details of available options and specifications.

<h3>Keystone™ Actuators</h3> <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  <p>Figure 89 Pneumatic Actuator</p> </div> <div style="text-align: center;">  <p>Figure 778 Electric Actuator</p> </div> </div>		
<h3>Keystone™ Gears and Handles</h3> <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  <p>Figure 427 Gear Operator</p> </div> <div style="text-align: center;">  <p>Composite Handles</p> </div> <div style="text-align: center;">  <p>Metal Handles</p> </div> </div>	<h3>Keystone™ Solenoid Valves</h3> <div style="text-align: center;">  <p>F791A</p> </div>	
<h3>TopWorx™ Switchboxes</h3> <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  <p>TVA</p> </div> <div style="text-align: center;">  <p>TVL</p> </div> <div style="text-align: center;">  <p>TXP</p> </div> <div style="text-align: center;">  <p>TVF</p> </div> </div>		<h3>El-O-Matic™ Positioners</h3> <div style="text-align: center;">  <p>Posiflex F10 / F20</p> </div>

QuickShip Terms

Contact your local sales representative for details.

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any product remains solely with the purchaser and end user.

Keystone, KTM, Neotecha, Vanessa, TopWorx are marks owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Automation Solutions, Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.