

8

7

6

5

4

3

2



1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

Sensor Terminals:

Sensor Types:

CMF010	T075	F025	H025
CMF025	T100	F050	H050
CMF050	T150	F100	H100
CMF100		F200	H200
CMF200			
CMF300	(excluding CMF300A)		



NOTE: PREPARE CABLE PER THE INSTRUCTIONS PROVIDED WITH THE CABLE.

3500 IS CONNECTOR

	c	a	
	2	2	
YELLOW	4	4	BLACK (DRAINS)
VIOLET	6	6	ORANGE
GREEN	8	8	WHITE
BLUE	10	10	GRAY
BROWN	12	12	RED
	14	14	
	16	16	
	18	18	
	20	20	
	22	22	
	24	24	
	26	26	
	28	28	
	30	30	
	32	32	

D

D

C

C

B

B

A

A

8

7

6



5

4

3

2

1

		 MICRO MOTION, INC. BOULDER, COLORADO	
 THIRD ANGLE PROJECTION		WIRING, 3500 TO CMF/T/F/H	
NAME	DATE	SIZE	DWG. NO.
DRAWN: DJS	11/13/97	D	EW-3300523
CHKD.: RBG	12/30/97	SCALE: NONE	DO NOT SCALE DRAWING
APVD.: RBG	12/30/97	SHEET 1 OF 1	

COPYRIGHT 2005 MICRO MOTION, INC. ALL RIGHTS RESERVED