

8

7

6

5

4

3

2



1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

Sensor Terminals:


Sensor Types:

- CMF010 F025 H025
- CMF025 F050 H050
- CMF050 F100 H100
- CMF100 F200 H200
- CMF200
- CMF300 (excluding CMF300A)



Note: Prepare cable per Transmitter Cable Prep Instructions which is provided with the Cable.

Model RFT9739D or RFT9739E Terminals



D

D

C

C

B

B

A

A

8

7

6



5

4

3

2

1

		 MICRO MOTION, INC. BOULDER, COLORADO	
 THIRD ANGLE PROJECTION		WIRING, RFT9739D/E TO CMF/F/H	
NAME	DATE	SIZE	DWG. NO.
DRAWN JLA	8/6/96	D	EW-3001325
CHKD. JLA	9/17/96		REV. F
APVD. JLA	9/17/96	SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1

COPYRIGHT 2005 MICRO MOTION, INC.
ALL RIGHTS RESERVED