

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

D


D

Sensor Terminals:

Sensor Models:


DH025	DL025	DS150
DH038	DL050	DS300
DH100	DL065	
DH150	DL100	
DH300	DL200	

- | | |
|-------|--------|
| ⊗ 1 ⊗ | Brown |
| ⊗ 2 ⊗ | Red |
| ⊗ 3 ⊗ | Orange |
| ⊗ 4 ⊗ | Yellow |
| ⊗ 5 ⊗ | Green |
| ⊗ 6 ⊗ | Blue |
| ⊗ 7 ⊗ | Violet |
| ⊗ 8 ⊗ | Gray |
| ⊗ 9 ⊗ | White |



Note: Prepare cable per Transmitter Cable Prep Instructions which is provided with the Cable.

Model RFT9739D or RFT9739E Terminals



C

C

B

B

A

A

8

7

6

5

4

3

2

1

		MICRO MOTION, INC. BOULDER, COLORADO	
THIRD ANGLE PROJECTION		WIRING, RFT9739D/E TO DH/DL/DS	
NAME	DATE	SIZE	DWG. NO.
TAJ	12/11/91	D	EW-3001327
CHKD.	CC	SCALE	DO NOT SCALE DRAWING
APVD.			SHEET 1 OF 1

COPYRIGHT 2005 MICRO MOTION, INC.
ALL RIGHTS RESERVED