

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

D


D

Sensor Terminals:

Sensor Models:


DH025	DL025	DS150
DH038	DL050	DS300
DH100	DL065	
DH150	DL100	
DH300	DL200	

- | | |
|---|--------|
| 1 | Brown |
| 2 | Red |
| 3 | Orange |
| 4 | Yellow |
| 5 | Green |
| 6 | Blue |
| 7 | Violet |
| 8 | Gray |
| 9 | White |



Note: Prepare cable per Transmitter Cable Prep Instructions which is provided with the Cable.

Model RFT9739R Terminals



C

C

B

B

A

A

8

7

6



5

4

3

2

1

		 MICRO MOTION, INC. BOULDER, COLORADO	
		WIRING, RFT9739R TO DH/DL/DS	
 THIRD ANGLE PROJECTION			
NAME	DATE	SIZE	DWG. NO.
DRAWN TAJ	12/11/91	D	EW-3002368
CHKD. CC			REV. D
APVD.		SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1

COPYRIGHT 2005 MICRO MOTION, INC. ALL RIGHTS RESERVED